




DESCRIPTION: .085" RIBBON SOLDER CUP



	A	B	C	D	E
14	1.729	.992	.476	.602	1.417
24	43.92	25.20	12.10	15.30	35.99
36	2.154	1.417	.476	.602	1.842
50	54.71	36.00	12.10	15.30	46.79
	2.665	1.925	.476	.602	2.352
	67.69	48.90	12.10	15.30	59.74
	3.259	2.538	.476	.602	2.947
	82.78	64.47	12.10	15.30	74.85

111-XXX-203-001

SERIES _____
POSITIONS _____
014
024
036
050

GENDER _____
2 = FEMALE

TERMINATION _____
3 = SOLDER CUP

SHELL PLATING _____
3 = NICKEL

HARDWARE OPTIONS _____
00 = NO HARDWARE

PLATING OPTIONS _____
01 = GOLD FLASH

MATERIALS:

INSULATOR: GLASS-FILLED THERMOPLASTIC
UL RATED 94V-0

CONTACTS: COPPER ALLOY

ELECTRICALS:

CONTACT CURRENT RATING: 5 AMPS

DIELECTRIC WITHSTANDING VOLTAGE: AC 1200 R.M.S.

INSULATION RESISTANCE: 1000 mohms MINIMUM AT 500V DC

CONTACT RESISTANCE: 30 mOHMS MAXIMUM

OPERATING TEMPERATURE: -55°C TO +125°C



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

DATE:
8-23-98

CHECKED:
PAM JENKINS

DATE:
8-24-98

SCALE:

SHEET

OF

1

1

REV

5

DWG NO.

111-XXX-203-001

NorComp