

High Temperature Grease

Product Code: HTG

PRODUCT DESCRIPTION

This specialised high temperature grease, supplied in tubes, is for use in many mechanical and electrical applications.

PRODUCT USE

HTG is suitable for use in many applications where good lubrication and consistent performance at elevated temperatures is required.

Examples of this are photocopier drive systems, laser printer and thermal printer gears etc. and heavy industrial machinery which runs continuously. Lubricating the chains on reflow and flow soldering machines are another suitable application.

FEATURES

- * Wide operating temperature range.
- * Excellent lubricating and thermal properties.
- * Safe on most thermoplastics.
- * Contains good anti-rust and anti-wear additives.
- * Water resistant
- * Low evaporation weight loss
- * Conveniently packed in 50ml tubes.

TYPICAL PROPERTIES

Form:	Brown Grease
Viscosity (Base Oil, 40°C):	465 cSt
Flash Point:	230°C
Pour Point:	<-10°C
Drop Point:	>250°C
Temperature Range:	-20°C to +200°C
Thermal Conductivity	0.4W/mK
Dielectric strength	35kV/mm

DIRECTIONS FOR USE


Apply to both surfaces sparingly.

TECHNICAL
DATA
SHEET



Copyright
Electrolube
2003

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



High Temperature Grease – Page 2

PACKAGING

50ml Tube

ORDER CODE

HTG50T

TECHNICAL
DATA
SHEET



**Copyright
Electrolube
2003**
All information is
given in good
faith but without
warranty.
Properties are
given as a guide
only and should
not be taken as a
specification.
Electrolube
cannot be held
responsible for
the performance
of its products
within any
application
determined by
the customer,
who must satisfy
themselves as to
the suitability of
the product.

