

HTZ260G Series

$$I_{F(AV)} = 4.7 \text{ A}$$


$$V_{RRM} = 22400 \text{ V}$$

High Voltage Diode Rectifier Module

LARONTROL
Electronic Devices

Type Number	Repetitive Peak	Minimum Avalanche Voltage $V_{(BR)R}$
HTZ260G22K	22400	23800
HTZ260G19K	19600	21000
HTZ260G16K	16800	18200
HTZ260G14K	14000	15400

CIRCUIT DIAGRAM



The circuit diagram shows a full-bridge rectifier with a center tap. The input is AC, and the output is DC. The reverse voltage across the series diodes is labeled V_{RRM} . The center tap is labeled "Centre Tap".



CURRENT RATINGS - AIR COOLED

$I_{F(AV)}$	Mean forward current	Half wave resistive load $T_{amb} = 35^{\circ}\text{C}$	4.7	A
I_F	Continuous (direct) forward current	$T_{amb} = 35^{\circ}\text{C}$	5.8	A
$R_{th(j-a)}$	Thermal resistance junction to ambient		1.8	$^{\circ}\text{C/W}$

CURRENT RATINGS - OIL COOLED

$I_{F(AV)}$	Mean forward current	Half wave resistive load $T_{oil} = 60^{\circ}\text{C}$	6.0	A
I_T	Continuous (direct) forward current	$T_{oil} = 60^{\circ}\text{C}$	7.5	A
$R_{th(j-o)}$	Thermal resistance junction to oil		0.97	$^{\circ}\text{C/W}$

SURGE RATINGS

I^2t	I^2t for fusing	10 ms half sine $T_{vj} = 150^{\circ}\text{C}$	200	A^2sec
I_{FSM}	Surge (non-repetitive) forward current	$T_{vj} = 150^{\circ}\text{C}$	200	A

TEMPERATURE AND FREQUENCY RATINGS

T_{vj}	Virtual junction temperature	Forward (conducting)	180	$^{\circ}\text{C}$
		Reverse (blocking)	180	$^{\circ}\text{C}$
T_{stg}	Storage temperature range		-40 to 100	$^{\circ}\text{C}$
f	Frequency range		20 to 400	Hz


CHARACTERISTICS $T_{case} = 25^{\circ}\text{C}$ unless otherwise stated

V_{FM}	Forward voltage	At 12 Amps peak	max 16	V
I_{RM}	Peak reverse current	At V_{RRM} , $T_{case} = 150^{\circ}\text{C}$	max 0.5	mA

Dimensioned Outlines

Dimensions shown are maximum in mm

Weight typ.: 1,7 Kg



IXYS reserves the right to change limits, test conditions and dimensions.

ZG

Issue 1 June 1998

Distributed by

USA
3540 Bassett Street
Santa Clara, CA 95054
Phone: (408) 982-0700
FAX: (408) 496-0670

EUROPE
IXYS Semiconductor GmbH
Lampertheim Germany
Phone: +49.6206.503.0
Fax: +49.6206.503.627

IXYS
www.IXYS.net

HTZ260G Series

$$I_{F(AV)} = 4.7 \text{ A}$$

$$V_{RRM} = 22400 \text{ V}$$

High Voltage Diode Rectifier Module

LARONTROL
Electronic Devices

