

Surface Mount Directional Couplers

50Ω

5 to 1000 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Pin Connections

INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
NOT USED*	5,6

*pins 5&6 must be isolated

Outline Drawing



Outline Dimensions (inch/mm)


AT790-1	A	B	C	D	E	F	G	H	J	K	wt.
	.150	.150	.150	.050	.030	.025	.028	.050	.160	.030	grams
	3.81	3.81	3.81	1.27	0.76	0.64	0.71	1.27	4.06	0.76	.10

AT1030	A	B	C	D	E	F	G	H	J	K	L	wt.
	.166	.150	.155	.050	.037	.025	.012	.060	.184	.030	.004	grams
	4.22	3.81	3.94	1.27	0.94	0.64	0.30	1.52	4.67	0.76	0.10	.10

Reflow Solder Assembly

Silver-bearing solder (Sn/Pb/Ag 62/36/2%) is recommended; however, tin-lead eutectic (Sn/Pb 63/37%) may be used. For temperature profiles, see Application Note AN-40-004

Demo Board MCL P/N: TB-278 Suggested PCB Layout (PL-150)



Features

- very flat coupling
- very broadband, multi octave
- temperature stable, BLUE CELL™ base
- all welded construction
- leads attached for better solderability
- micro-miniature coupler
- protected by U.S. Patent 6,140,887 & 6,784,521

Applications

- VHF/UHF receivers/transmitters
- cellular

NEW!
DBTC-12-4 DBTC-12-4L



No Leads

BLUE CELL™



Leads

CASE STYLE: AT790-1
PRICE: \$1.99 ea. QTY (25)
\$1.69 ea. QTY (1000)

CASE STYLE: AT1030
PRICE: \$2.14 ea. QTY (25)
\$1.84 ea. QTY (1000)

Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS* (dB)						DIRECTIVITY (dB)						VSWR** (:1)	POWER INPUT, W	
			L		M		U		L		M		U				
	f _L -f _U	Nom.	Max. Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.		Min.	Typ.
5-1000	12.2±0.5	±0.9	0.9	1.8	0.7	1.3	1.1	1.6	33	22	21	14	15	—	1.20	0.5	1.0




* Includes theoretical coupled power loss of 0.27 dB at 12 dB coupling. L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]

**For coupled port VSWR above 500 MHz, 1.5:1 typ.

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	0.88	12.07	34.34	19.19	23.31	17.81
10.00	0.79	11.96	34.86	21.25	27.96	19.68
50.00	0.73	11.90	35.53	22.99	35.09	21.01
100.00	0.75	11.93	37.41	22.94	34.58	21.11
500.00	0.85	11.99	25.82	22.00	26.19	18.96
600.00	0.88	11.99	22.32	21.56	25.58	17.94
800.00	0.95	12.03	17.75	20.94	25.46	15.62
900.00	1.00	12.07	16.15	20.79	26.14	14.55
1000.00	1.06	12.13	14.74	20.48	26.70	13.43

BLUE CELL™ is protected by U.S. Patents.



Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. F
M89619
DBTC-12-4
DBTC-12-4L
WZ/TD/CP
040225
ED-8954/1
ED-8954A