

Duplex Singlemode 8.3/125 Fiber Patch Cable (LC/ST), 5M (16-ft.)

MODEL NUMBER: **N368-05M**



Description

Tripp Lite's 5-meter (15ft), singlemode duplex fiber optic LC/ST patch cable is manufactured from 8.3/125 zipcord fiber. The cable has LC connectors on one end, ST connectors on the other, a PVC jacket, and is FDDI and OFNR rated. Duplex singlemode fiber is most commonly used in LAN applications.

Features

- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 5-meter (15ft) Connectors: 2 LC and 2 ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	8.3/125
Intended Application	Computer Networking (Fiber)

Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

Applications

- Networking equipment that requires singlemode fiber optic patch cables

System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with LC/SCconnectors

Package Includes

- 5-meter (15ft) Duplex Singlemode Fiber Patch Cable, LC/ST



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Type	SINGLEMODE 8.3/125 FIBER OPTIC
Model Type	LC/ST
INPUT	
Cable Length (m)	5
UPC ASSIGNMENT	
Unit Carton UPC#	037332134820
PHYSICAL	
Color	Yellow
Style	Fiber Optic
CONNECTIONS	
Connector A	LC
Connector B	ST
Number of Connectors	4
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.