

## DMOS 100mA Low-Dropout Regulator

### FEATURES

- **NEW DMOS TOPOLOGY:**  
Ultra Low Dropout Voltage:  
60mV typ at 100mA  
Output capacitor NOT required for stability
- **FAST TRANSIENT RESPONSE**
- **VERY LOW NOISE:** 23 $\mu$ Vrms
- **HIGH ACCURACY:**  $\pm 1.5\%$  max
- **HIGH EFFICIENCY:**  
 $I_{GND} = 500\mu A$  at  $I_{OUT} = 100mA$   
Not Enabled:  $I_{GND} = 10nA$
- **2.5V, 2.8V, 2.85V, 3.0V, 3.3V, 5.0V, AND  
ADJUSTABLE OUTPUT VERSIONS**
- **OTHER OUTPUT VOLTAGES AVAILABLE  
UPON REQUEST**
- **FOLDBACK CURRENT LIMIT**
- **THERMAL PROTECTION**
- **SMALL SURFACE-MOUNT PACKAGES:**  
SOT23-5 and SO-8

### APPLICATIONS

- **PORTABLE COMMUNICATION DEVICES**
- **BATTERY-POWERED EQUIPMENT**
- **PERSONAL DIGITAL ASSISTANTS**
- **MODEMS**
- **BAR-CODE SCANNERS**
- **BACKUP POWER SUPPLIES**


### DESCRIPTION

The REG101 is a family of low-noise, low-dropout linear regulators with low ground pin current. Its new DMOS topology provides significant improvement over previous designs, including low dropout voltage (only 60mV typ at full load), and better transient performance. In addition, no output capacitor is required for stability, unlike conventional low-dropout regulators that are difficult to compensate and require expensive low ESR capacitors greater than 1 $\mu$ F.


Typical ground pin current is only 500 $\mu$ A (at  $I_{OUT} = 100mA$ ) and drops to 10nA when not in enabled mode. Unlike regulators with PNP pass devices, quiescent current remains relatively constant over load variation and under dropout conditions.

The REG101 has very low output noise (typically 23 $\mu$ Vrms for  $V_{OUT} = 3.3V$  with  $C_{NR} = 0.01\mu F$ ), making it ideal for use in portable communications equipment. Accuracy is maintained over temperature, line, and load variations. Key parameters are tested over the specified temperature range ( $-40^{\circ}C$  to  $+85^{\circ}C$ ).

The REG101 is well protected—internal circuitry provides a current limit that protects the load from damage. Thermal protection circuitry keeps the chip from being damaged by excessive temperature. The REG101 is available in the SOT23-5 and the SO-8 packages.



NR = Noise Reduction



NOTE: (1) Optional.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Supply Input Voltage, $V_{IN}$                      | –0.3V to 12V      |
| Enable Input Voltage, $V_{EN}$                      | –0.3V to $V_{IN}$ |
| Feedback Voltage, $V_{FB}$                          | –0.3V to 6.0V     |
| NR Pin Voltage, $V_{NR}$                            | –0.3V to 6.0V     |
| Output Short-Circuit Duration                       | Indefinite        |
| Operating Temperature Range ( $T_J$ )               | –55°C to +125°C   |
| Storage Temperature Range ( $T_A$ )                 | –65°C to +150°C   |
| Lead Temperature (soldering, 3s, SOT23-5, and SO-8) | +240°C            |

NOTE: (1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability.



## ELECTROSTATIC DISCHARGE SENSITIVITY

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## PACKAGE/ORDERING INFORMATION<sup>(1)</sup>



| PRODUCT          | $V_{OUT}^{(2)}$                                                                                                                                  |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| REG101xx-yyy/zzz | <p>XX is package designator.</p> <p>YYYY is typical output voltage (5 = 5.0V, 2.85 = 2.85V, A = Adjustable).</p> <p>ZZZ is package quantity.</p> |

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at [www.ti.com](http://www.ti.com).

(2) Output voltages from 2.5V to 5.1V in 50mV increments are available; minimum order quantities apply. Contact factory for details and availability.

## PIN CONFIGURATIONS

Top View



NOTE: (1) For REG101A-A: voltage setting resistor pin. All other models: noise reduction capacitor pin.  
 (2) Both pin 1 and pin 2 must be connected.  
 (3) Both pin 7 and pin 8 must be connected.

# ELECTRICAL CHARACTERISTICS

**Boldface** limits apply over the specified temperature range,  $T_J = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .







At  $T_J = +25^{\circ}\text{C}$ ,  $V_{IN} = V_{OUT} + 1\text{V}$  ( $V_{OUT} = 2.5\text{V}$  for REG101-A),  $V_{ENABLE} = 1.8\text{V}$ ,  $I_{OUT} = 2\text{mA}$ ,  $C_{NR} = 0.01\mu\text{F}$ , and  $C_{OUT} = 0.1\mu\text{F}^{(1)}$ , unless otherwise noted.

| PARAMETER                                            | CONDITION                                                                                                                                           | REG101NA<br>REG101UA              |                                    |                             | UNITS                |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|------------------------------------|-----------------------------|----------------------|
|                                                      |                                                                                                                                                     | MIN                               | TYP                                | MAX                         |                      |
| <b>OUTPUT VOLTAGE</b>                                |                                                                                                                                                     |                                   |                                    |                             |                      |
| Output Voltage $V_{OUT}$                             |                                                                                                                                                     |                                   |                                    |                             | V                    |
| REG101-2.5                                           |                                                                                                                                                     |                                   | 2.5                                |                             | V                    |
| REG101-2.8                                           |                                                                                                                                                     |                                   | 2.8                                |                             | V                    |
| REG101-2.85                                          |                                                                                                                                                     |                                   | 2.85                               |                             | V                    |
| REG101-3.0                                           |                                                                                                                                                     |                                   | 3.0                                |                             | V                    |
| REG101-3.3                                           |                                                                                                                                                     |                                   | 3.3                                |                             | V                    |
| REG101-5                                             |                                                                                                                                                     |                                   | 5                                  |                             | V                    |
| REG101-A                                             |                                                                                                                                                     | 2.5                               |                                    | 5.5                         | V                    |
| Reference Voltage $V_{REF}$                          |                                                                                                                                                     |                                   | 1.267                              |                             | V                    |
| Adjust Pin Current $I_{ADJ}$                         |                                                                                                                                                     |                                   | 0.2                                | 1                           | $\mu\text{A}$        |
| Accuracy                                             |                                                                                                                                                     |                                   | $\pm 0.5$                          | $\pm 1.5$                   | %                    |
| <b>Over Temperature vs Temperature</b> $dV_{OUT}/dT$ |                                                                                                                                                     |                                   | <b>50</b>                          | <b><math>\pm 2.2</math></b> | %                    |
| Includes Line and Load                               |                                                                                                                                                     |                                   | $\pm 0.8$                          | $\pm 2.0$                   | %                    |
| <b>Over Temperature</b>                              | $I_{OUT} = 2\text{mA}$ to $100\text{mA}$ , $V_{IN} = (V_{OUT} + 0.4\text{V})$ to $10\text{V}$<br>$V_{IN} = (V_{OUT} + 0.6\text{V})$ to $10\text{V}$ |                                   |                                    | <b><math>\pm 2.7</math></b> | %                    |
| <b>DC DROPOUT VOLTAGE</b> <sup>(2)</sup> $V_{DROP}$  |                                                                                                                                                     |                                   |                                    |                             | mV                   |
| For all models                                       | $I_{OUT} = 2\text{mA}$                                                                                                                              |                                   | 4                                  | 10                          | mV                   |
| <b>Over Temperature</b>                              | $I_{OUT} = 100\text{mA}$                                                                                                                            |                                   | 60                                 | 100                         | mV                   |
|                                                      | <b><math>I_{OUT} = 100\text{mA}</math></b>                                                                                                          |                                   |                                    | <b>130</b>                  | mV                   |
| <b>VOLTAGE NOISE</b> $V_n$                           |                                                                                                                                                     |                                   |                                    |                             | $\mu\text{Vrms}$     |
| Without $C_{NR}$                                     | $f = 10\text{Hz}$ to $100\text{kHz}$<br>$C_{NR} = 0$ , $C_{OUT} = 0$                                                                                |                                   | $23\mu\text{Vrms/V} \cdot V_{OUT}$ |                             | $\mu\text{Vrms}$     |
| With $C_{NR}$ (all fixed voltage models)             | $C_{NR} = 0.01\mu\text{F}$ , $C_{OUT} = 10\mu\text{F}$                                                                                              |                                   | $7\mu\text{Vrms/V} \cdot V_{OUT}$  |                             | $\mu\text{Vrms}$     |
| <b>OUTPUT CURRENT</b>                                |                                                                                                                                                     |                                   |                                    |                             |                      |
| Current Limit <sup>(3)</sup> $I_{CL}$                |                                                                                                                                                     | 130                               | 170                                | 220                         | mA                   |
| <b>Over Temperature</b>                              |                                                                                                                                                     | <b>110</b>                        |                                    | <b>240</b>                  | mA                   |
| Short-Circuit Current $I_{SC}$                       |                                                                                                                                                     |                                   | 60                                 |                             | mA                   |
| <b>RIPPLE REJECTION</b>                              |                                                                                                                                                     |                                   |                                    |                             |                      |
| $f = 120\text{Hz}$                                   | $I_{OUT} = 100\text{mA}$                                                                                                                            |                                   | 65                                 |                             | dB                   |
| <b>ENABLE CONTROL</b>                                |                                                                                                                                                     |                                   |                                    |                             |                      |
| $V_{ENABLE}$ High (output enabled) $V_{ENABLE}$      |                                                                                                                                                     | 1.8                               |                                    | $V_{IN}$                    | V                    |
| $V_{ENABLE}$ Low (output disabled) $V_{ENABLE}$      |                                                                                                                                                     | -0.2                              |                                    | 0.5                         | V                    |
| $I_{ENABLE}$ High (output enabled) $I_{ENABLE}$      | $V_{ENABLE} = 1.8\text{V}$ to $V_{IN}$ , $V_{IN} = 1.8\text{V}$ to $6.5^{(4)}$                                                                      |                                   | 1                                  | 100                         | nA                   |
| $I_{ENABLE}$ Low (output disabled) $I_{ENABLE}$      | $V_{ENABLE} = 0\text{V}$ to $0.5\text{V}$                                                                                                           |                                   | 2                                  | 100                         | nA                   |
| Output Disable Time                                  | $C_{OUT} = 1.0\mu\text{F}$ , $R_{LOAD} = 33\Omega$                                                                                                  |                                   | 200                                |                             | $\mu\text{s}$        |
| Output Enable Time                                   | $C_{OUT} = 1.0\mu\text{F}$ , $R_{LOAD} = 33\Omega$                                                                                                  |                                   | 1.5                                |                             | ms                   |
| <b>THERMAL SHUTDOWN</b>                              |                                                                                                                                                     |                                   |                                    |                             |                      |
| Junction Temperature                                 |                                                                                                                                                     |                                   |                                    |                             | $^{\circ}\text{C}$   |
| Shutdown                                             |                                                                                                                                                     |                                   | 160                                |                             | $^{\circ}\text{C}$   |
| Reset from Shutdown                                  |                                                                                                                                                     |                                   | 140                                |                             | $^{\circ}\text{C}$   |
| <b>GROUND PIN CURRENT</b>                            |                                                                                                                                                     |                                   |                                    |                             |                      |
| Ground Pin Current $I_{GND}$                         | $I_{OUT} = 2\text{mA}$                                                                                                                              |                                   | 400                                | 500                         | $\mu\text{A}$        |
|                                                      | $I_{OUT} = 100\text{mA}$                                                                                                                            |                                   | 500                                | 650                         | $\mu\text{A}$        |
| Enable Pin Low                                       | $V_{ENABLE} \leq 0.5\text{V}$                                                                                                                       |                                   | 0.01                               | 0.2                         | $\mu\text{A}$        |
| <b>INPUT VOLTAGE</b> $V_{IN}$                        |                                                                                                                                                     |                                   |                                    |                             |                      |
| Operating Input Voltage Range <sup>(5)</sup>         |                                                                                                                                                     | 1.8                               |                                    | 10                          | V                    |
| Specified Input Voltage Range                        | $V_{IN} > 1.8\text{V}$                                                                                                                              | $V_{OUT} + 0.4$                   |                                    | 10                          | V                    |
| <b>Over Temperature</b>                              | <b><math>V_{IN} &gt; 1.8\text{V}</math></b>                                                                                                         | <b><math>V_{OUT} + 0.6</math></b> |                                    | <b>10</b>                   | V                    |
| <b>TEMPERATURE RANGE</b>                             |                                                                                                                                                     |                                   |                                    |                             |                      |
| Specified Range $T_J$                                |                                                                                                                                                     | -40                               |                                    | +85                         | $^{\circ}\text{C}$   |
| Operating Range $T_J$                                |                                                                                                                                                     | -55                               |                                    | +125                        | $^{\circ}\text{C}$   |
| Storage Range $T_A$                                  |                                                                                                                                                     | -65                               |                                    | +150                        | $^{\circ}\text{C}$   |
| Thermal Resistance                                   |                                                                                                                                                     |                                   |                                    |                             | $^{\circ}\text{C/W}$ |
| SOT23-5 Surface Mount $\theta_{JA}$                  | Junction-to-Ambient                                                                                                                                 |                                   | 200                                |                             | $^{\circ}\text{C/W}$ |
| SO-8 Surface Mount $\theta_{JA}$                     | Junction-to-Ambient                                                                                                                                 |                                   | 150                                |                             | $^{\circ}\text{C/W}$ |

- NOTES: (1) The REG101 does not require a minimum output capacitor for stability. However, transient response can be improved with proper capacitor selection.  
(2) Dropout voltage is defined as the input voltage minus the output voltage that produces a 2% change in the output voltage from the value at  $V_{IN} = V_{OUT} + 1\text{V}$  at fixed load.  
(3) Current limit is the output current that produces a 10% change in output voltage from  $V_{IN} = V_{OUT} + 1\text{V}$  and  $I_{OUT} = 2\text{mA}$ .  
(4) For  $V_{ENABLE} > 6.5\text{V}$ , see typical characteristic " $I_{ENABLE}$  VS  $V_{ENABLE}$ ".  
(5) The REG101 no longer regulates when  $V_{IN} < V_{OUT} + V_{DROP (MAX)}$ . In drop-out, the impedance from  $V_{IN}$  to  $V_{OUT}$  is typically less than  $1\Omega$  at  $T_J = +25^{\circ}\text{C}$ .







# TYPICAL CHARACTERISTICS

For all models, at  $T_J = +25^\circ\text{C}$  and  $V_{\text{ENABLE}} = 1.8\text{V}$ , unless otherwise noted.









# TYPICAL CHARACTERISTICS (Cont.)

For all models, at  $T_J = +25^\circ\text{C}$  and  $V_{\text{ENABLE}} = 1.8\text{V}$ , unless otherwise noted.









# TTYPICAL CHARACTERISTICS (Cont.)

For all models, at  $T_J = +25^\circ\text{C}$  and  $V_{\text{ENABLE}} = 1.8\text{V}$ , unless otherwise noted.









# TYPICAL CHARACTERISTICS (Cont.)

For all models, at  $T_J = +25^\circ\text{C}$  and  $V_{\text{ENABLE}} = 1.8\text{V}$ , unless otherwise noted.



# TYPICAL CHARACTERISTICS (Cont.)

For all models, at  $T_J = +25^\circ\text{C}$  and  $V_{\text{ENABLE}} = 1.8\text{V}$ , unless otherwise noted.



## BASIC OPERATION

The REG101 series of LDO (Low Drop-Out) linear regulators offers a wide selection of fixed output voltage versions and an adjustable output version. The REG101 belongs to a family of new generation LDO regulators that utilize a DMOS pass transistor to achieve ultra-low dropout performance and freedom from output capacitor constraints. Ground pin current remains under 650 $\mu$ A over all line, load, and temperature conditions. All versions have thermal and over-current protection, including foldback current limit.

The REG101 does not require an output capacitor for regulator stability and is stable over most output currents and with almost any value and type of output capacitor up to 10 $\mu$ F or more. For applications where the regulator output current drops below several milliamps, stability can be enhanced by: adding a 1k $\Omega$  to 2k $\Omega$  load resistor; using capacitance values less than 10 $\mu$ F; or keeping the effective series resistance greater than 0.05 $\Omega$  including the capacitor's ESR and parasitic resistance in printed circuit board traces, solder joints, and sockets.

Although an input capacitor is not required, it is good analog design practice to connect a 0.1 $\mu$ F low ESR capacitor across




FIGURE 1. Fixed Voltage Nominal Circuit for REG101.

the input supply voltage. This is recommended to improve ripple rejection by reducing input voltage ripple.

Figure 1 shows the basic circuit connections for the fixed voltage models. Figure 2 gives the connections for the adjustable output version (REG101A) and example resistor values for some commonly used output voltages. Values for other voltages can be calculated from the equation shown in Figure 2.

## INTERNAL CURRENT LIMIT

The REG101 internal current limit has a typical value of 170mA. A foldback feature limits the short-circuit current to a typical short-circuit value of 60mA. This helps to protect the regulator from damage under all load conditions. A characteristic of  $V_{OUT}$  versus  $I_{OUT}$  is given in Figure 3 and in the Typical Characteristics section.




FIGURE 3. Foldback Current Limit of the REG101-3.3 at 25°C.




FIGURE 2. Adjustable Voltage Circuit for REG101A.

## ENABLE

The Enable pin is active HIGH and compatible with standard TTL-CMOS levels. Inputs below 0.5V (max) turn the regulator off and all circuitry is disabled. Under this condition, ground pin current drops to approximately 10nA. When a pull-up resistor is used, and operation down to  $V_{IN} = 1.8V$  is required, use values  $< 50k\Omega$ .

## OUTPUT NOISE

A precision band-gap reference is used for the internal reference voltage,  $V_{REF}$ . This reference is the dominant noise source within the REG101 and it generates approximately 29 $\mu V_{rms}$  in the 10Hz to 100kHz bandwidth at the reference output. The regulator control loop gains up the reference noise, so that the noise voltage of the regulator is approximately given by:

$$V_N = 29\mu V_{rms} \frac{R_1 + R_2}{R_2} = 29\mu V_{rms} \cdot \frac{V_{OUT}}{V_{REF}}$$

Since the value of  $V_{REF}$  is 1.267V, this relationship reduces to:

$$V_N = 23 \frac{\mu V_{rms}}{V} \cdot V_{OUT}$$

Connecting a capacitor,  $C_{NR}$ , from the Noise Reduction (NR) pin to ground, as shown in Figure 4, forms a low-pass filter for the voltage reference. For  $C_{NR} = 10nF$ , the total noise in the 10Hz to 100kHz bandwidth is reduced by approximately a factor of 2.8 for  $V_O = 3.3V$ . This noise reduction effect is shown in Figure 5 and as “RMS Noise Voltage vs CNR” in the Typical Characteristics section.

Noise can be further reduced by carefully choosing an output capacitor,  $C_{OUT}$ . Best overall noise performance is




FIGURE 5. Output Noise versus Noise Reduction Capacitor.

achieved with very low ( $< 0.22\mu F$ ) or very high ( $> 2.2\mu F$ ) values of  $C_{OUT}$ . See “RMS Noise Voltage vs  $C_{OUT}$ ” in the Typical Characteristics section.

The REG101 utilizes an internal charge pump to develop an internal supply voltage sufficient to drive the gate of the DMOS pass element above  $V_{IN}$ . The charge-pump switching noise (nominal switching frequency = 2MHz) is not measurable at the output of the regulator over most values of  $C_{OUT}$  and  $I_{OUT}$ .

The REG101 adjustable version does not have the noise-reduction pin available, however, the adjust pin is the summing junction of the error amplifier. A capacitor,  $C_{FB}$ , connected from the output to the adjust pin will reduce both the output noise and the peak error from a load transient. See the typical characteristics for output noise performance.




FIGURE 4. Block Diagram.

## DROP-OUT VOLTAGE

The REG101 uses an N-channel DMOS as the “pass” element. When the input voltage is within a few tens of millivolts of the output voltage, the DMOS device behaves like a resistor. Therefore, for low values of  $V_{IN}$  to  $V_{OUT}$ , the regulator’s input-to-output resistance is the  $R_{DS_{ON}}$  of the DMOS pass element (typically 600m $\Omega$ ). For static (DC) loads, the REG101 will typically maintain regulation down to  $V_{IN}$  to  $V_{OUT}$  voltage drop of 60mV at full rated output current. In Figure 6, the bottom line (DC dropout) shows the minimum  $V_{IN}$  to  $V_{OUT}$  voltage drop required to prevent drop-out under DC load conditions.

For large step changes in load current, the REG101 requires a larger voltage drop across it to avoid degraded transient response. The boundary of this “transient drop-out” region is shown as the top line in Figure 6. Values of  $V_{IN}$  to  $V_{OUT}$  voltage drop above this line insure normal transient response.

In the transient dropout region between “DC” and “Transient”, transient response recovery time increases. The time required to recover from a load transient is a function of both the magnitude and rate of the step change in load current and the available “headroom”  $V_{IN}$  to  $V_{OUT}$  voltage drop. Under worst-case conditions (full-scale load change with  $V_{IN}$  to  $V_{OUT}$  voltage drop close to DC dropout levels), the REG101 can take several hundred microseconds to re-enter the specified window of regulation.




FIGURE 6. Transient and DC Dropout.

## TRANSIENT RESPONSE

The REG101 response to transient line and load conditions improves at lower output voltages. The addition of a capacitor (nominal value 0.47 $\mu$ F) from the output pin to ground may improve the transient response. In the adjustable version, the addition of a capacitor,  $C_{FB}$  (nominal value 10nF), from the output to the adjust pin will also improve the transient response.

## THERMAL PROTECTION

The REG101 has thermal shutdown circuitry that protects the regulator from damage. The thermal protection circuitry disables the output when the junction temperature reaches approximately 160°C, allowing the device to cool. When the junction temperature cools to approximately 140°C, the output circuitry is again enabled. Depending on various conditions, the thermal protection circuit may cycle on and off. This limits the dissipation of the regulator, but may have an undesirable effect on the load.

Any tendency to activate the thermal protection circuit indicates excessive power dissipation or an inadequate heat sink. For reliable operation, junction temperature should be limited to 125°C, maximum. To estimate the margin of safety in a complete design (including heat sink), increase the ambient temperature until the thermal protection is triggered. Use worst-case loads and signal conditions. For good reliability, thermal protection should trigger more than 35°C above the maximum expected ambient condition of your application. This produces a worst-case junction temperature of 125°C at the highest expected ambient temperature and worst-case load.

The internal protection circuitry of the REG101 has been designed to protect against overload conditions. It was not intended to replace proper heat sinking. Continuously running the REG101 into thermal shutdown will degrade reliability.

## POWER DISSIPATION

The REG101 is available in two different package configurations. The ability to remove heat from the die is different for each package type and, therefore, presents different considerations in the printed circuit board (PCB) layout. The PCB area around the device that is free of other components moves the heat from the device to the ambient air. While it is difficult to impossible to quantify all of the variables in a thermal design of this type, performance data for several configurations are shown in Figure 7.

Power dissipation depends on input voltage, load condition, and duty cycle. Power dissipation is equal to the product of the average output current times the voltage across the output element,  $V_{IN}$  to  $V_{OUT}$  voltage drop.

$$P_D = (V_{IN} - V_{OUT}) \cdot I_{OUT(AVG)}$$

Power dissipation can be minimized by using the lowest possible input voltage necessary to assure the required output voltage.

## REGULATOR MOUNTING

Solder pad footprint recommendations for the various REG101 devices are presented in the Application Bulletin AB-132, "Solder Pad Recommendations for Surface-Mount Devices" (SBFA015), available from the Texas Instruments web site ([www.ti.com](http://www.ti.com)).




FIGURE 7. Maximum Power Dissipation versus Ambient Temperature for the Various Packages.

**PACKAGING INFORMATION**

| Orderable part number             | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">REG101NA-2.5/250</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1G                |
| REG101NA-2.5/250.B                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1G                |
| <a href="#">REG101NA-2.5/3K</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1G                |
| REG101NA-2.5/3K.B                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1G                |
| <a href="#">REG101NA-2.8/250</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1E                |
| REG101NA-2.8/250.B                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1E                |
| <a href="#">REG101NA-2.85/250</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1N                |
| REG101NA-2.85/250.B               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1N                |
| <a href="#">REG101NA-2.85/3K</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1N                |
| REG101NA-2.85/3K.B                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1N                |
| <a href="#">REG101NA-3.3/250</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| REG101NA-3.3/250.B                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| REG101NA-3.3/250G4                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| <a href="#">REG101NA-3.3/3K</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| REG101NA-3.3/3K.B                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| REG101NA-3.3/3KG4                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1C                |
| <a href="#">REG101NA-3/250</a>    | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | R01D                |
| REG101NA-3/250.B                  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | R01D                |
| <a href="#">REG101NA-3/3K</a>     | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | R01D                |
| REG101NA-3/3K.B                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | R01D                |
| <a href="#">REG101NA-5/250</a>    | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1B                |
| REG101NA-5/250.B                  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1B                |
| <a href="#">REG101NA-5/3K</a>     | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1B                |
| REG101NA-5/3K.B                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1B                |
| <a href="#">REG101NA-A/250</a>    | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| REG101NA-A/250.A                  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| REG101NA-A/250.B                  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| <a href="#">REG101NA-A/3K</a>     | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| REG101NA-A/3K.A                   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| REG101NA-A/3K.B                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| REG101NA-A/3KG4                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | RO1A                |
| <a href="#">REG101UA-2.5</a>     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U25       |
| REG101UA-2.5.B                   | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U25       |
| <a href="#">REG101UA-3</a>       | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U30       |
| <a href="#">REG101UA-3.3</a>     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U33       |
| REG101UA-3.3.B                   | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U33       |
| <a href="#">REG101UA-3.3/2K5</a> | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U33       |
| REG101UA-3.3/2K5.B               | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U33       |
| REG101UA-3.B                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U30       |
| <a href="#">REG101UA-5</a>       | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U50       |
| REG101UA-5.B                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U50       |
| <a href="#">REG101UA-5/2K5</a>   | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U50       |
| REG101UA-5/2K5.B                 | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101U50       |
| <a href="#">REG101UA-A</a>       | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101UA        |
| REG101UA-A.A                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101UA        |
| REG101UA-A.B                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | REG<br>101UA        |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| REG101NA-2.5/250  | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-2.5/3K   | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-2.8/250  | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-2.85/250 | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-2.85/3K  | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-3.3/250  | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-3.3/3K   | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-3/250    | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-3/3K     | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-5/250    | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-5/3K     | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-A/250    | SOT-23       | DBV             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101NA-A/3K     | SOT-23       | DBV             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| REG101UA-3.3/2K5  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| REG101UA-5/2K5    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| REG101NA-2.5/250  | SOT-23       | DBV             | 5    | 250  | 203.0       | 203.0      | 35.0        |
| REG101NA-2.5/3K   | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101NA-2.8/250  | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-2.85/250 | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-2.85/3K  | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101NA-3.3/250  | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-3.3/3K   | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101NA-3/250    | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-3/3K     | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101NA-5/250    | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-5/3K     | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101NA-A/250    | SOT-23       | DBV             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| REG101NA-A/3K     | SOT-23       | DBV             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| REG101UA-3.3/2K5  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| REG101UA-5/2K5    | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| REG101UA-2.5   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-2.5.B | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-3     | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-3.3   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-3.3.B | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-3.B   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-5     | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-5.B   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-A     | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-A.A   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| REG101UA-A.B   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |



## SOT-23 - 1.45 mm max height

## SMALL OUTLINE TRANSISTOR




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.

# EXAMPLE BOARD LAYOUT


DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.



## PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

**D0008A**

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



## SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025