




LOC		DIST		REVISONS				
AD	47	FR	LTR	DESCRIPTION		DATE	DWN	APVD
		N2	REVISED	PER	ECO-11-024315	12JAN12	KH	DD

- 1

HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR NATURAL.
PIN CONTACTS: PHOSPHOR BRONZE.
GROUND BUSSES: PHOSPHOR BRONZE.
- 2

PIN CONTACTS & GROUND BUSES: 0.00076(0.00030) MIN. GOLD IN CONTACT AREA.
0.00063-0.00191[.000025-.000075] TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127-0.00254[.000050-.000100] NICKEL ON ENTIRE CONTACT.
- 3

DATE CODE MARKED IN AREA INDICATED.
- GROUND BUSES: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00063-0.00191[.000025-.000075] TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127-0.00254[.000050-.000100] NICKEL ON ENTIRE BUS.

OBSOLETE	151.13	[5.950]	119	153.62	[6.048]	156.08	[6.145]	157.84	[6.214]	240	1-536274-1
OBSOLETE	138.43	[5.450]	109	140.92	[5.548]	143.48	[5.645]	145.14	[5.714]	220	1-536274-0
OBSOLETE	125.73	[4.950]	99	128.22	[5.048]	130.68	[5.145]	132.44	[5.214]	200	536274-9
OBSOLETE	113.03	[4.450]	89	115.52	[4.548]	117.98	[4.645]	119.74	[4.714]	180	536274-8
	100.33	[3.950]	79	102.82	[4.048]	105.28	[4.145]	107.04	[4.214]	160	536274-7
	87.63	[3.450]	69	90.12	[3.548]	92.58	[3.645]	94.34	[3.714]	140	536274-6
	74.93	[2.950]	59	77.42	[3.048]	79.88	[3.145]	81.64	[3.214]	120	536274-5
	62.23	[2.450]	49	64.72	[2.548]	67.18	[2.645]	68.94	[2.714]	100	536274-4
	49.53	[1.950]	39	52.02	[2.048]	54.48	[2.145]	56.24	[2.214]	80	536274-3
	36.83	[1.450]	29	39.32	[1.548]	41.78	[1.645]	43.54	[1.714]	60	536274-2
	24.13	[.950]	19	26.62	[1.048]	29.08	[1.145]	30.84	[1.214]	40	536274-1
	E		D	C		B		A		NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± ± 0.13 [.005]
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN
J.GERACE
2-12-92

CHK
J.GERACE
2-12-92

APVD
J.GERACE
2-12-92

PRODUCT SPEC
108-1272

APPLICATION SPEC
114-11005

WEIGHT
-

CUSTOMER DRAWING

NAME
PLUG ASSEMBLY, 10.92[.430]
STACK, 3.68[.145] ACTION PIN
TAIL, BOARD TO BOARD, MICRO-STRIP

SIZE
A1

CAGE CODE
00779

DRAWING NO
536274

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
N2

TE Connectivity

4805 (3/11)