





Product Details			
Model Name	LP	ECCO Group Europe Part Number	30102372
Internal ERP Description	BEACON, LP, XEN, 2W, 230 VAC, RED		
Product Type	Xenon Beacon		
Product Image – Amber beacon only shown		Application	Industrial
		Product Dimensions 	

Electrical Characteristics			
Input Voltage	230V AC	Input current	25mA @ 230V AC
Frequency	75 FPM	Light Source	Non-replaceable
Flash Mode	Single flash	Flash Pattern	N/A
Technology	Xenon	Power rating	2W
		Estimated Tube Life	3,000 Hours

Photometric Characteristics		Polar Plot
Colour	Amber	
Max intensity at HV0	9 cd from top	
Min intensity	2 cd from side	
Timing Diagram		
		


--

Enclosure			
IP rating	IP 67	Fixing centres	45 mm
Cable exit	Central base grommet	Fastening hardware	2 x M5 x 14mm studs with M5 nuts
Cable dimensions	2 x 0.75mm ²	Packaging	Thin wall carton
Recommended Mounting	Upright or 90°	Max Fastening Torque	5 N/m
Weight (unboxed)	130g	Weight (boxed)	150g

Approvals and Certifications			
EMC	UN ECE R10-03 6101	WEEE	Yes (marking only for own brand products)
CE	Yes	RoHS	Yes