

# High Speed, Precision, JFET Input Instrumentation Amplifier (Fixed Gain = 10 or 100)

## FEATURES

- Slew Rate: 30V/ $\mu$ s
- Gain-Bandwidth Product: 35MHz
- Settling Time (0.01%): 3 $\mu$ s
- Overdrive Recovery: 0.4 $\mu$ s
- Gain Error: 0.05% Max
- Gain Drift: 5ppm/ $^{\circ}$ C
- Gain Nonlinearity: 16ppm Max
- Offset Voltage (Input + Output): 600 $\mu$ V Max  
– Drift with Temperature: 2 $\mu$ V/ $^{\circ}$ C
- Input Bias Current: 40pA Max
- Input Offset Current: 40pA Max  
– Drift with Temperature (to 70 $^{\circ}$ C): 0.5pA/ $^{\circ}$ C

## APPLICATIONS

- Fast Settling Analog Signal Processing
- Multiplexed Input Data Acquisition Systems
- High Source Impedance Signal Amplification from High Resistance Bridges, Capacitance Sensors, Photodetector Sensors
- Bridge Amplifier with < 1Hz Lowpass Filtering

## DESCRIPTION

The LT<sup>®</sup>1102 is the first fast FET input instrumentation amplifier offered in the low cost, space saving 8-pin packages. Fixed gains of 10 and 100 are provided with excellent gain accuracy (0.01%) and non-linearity (3ppm). No external gain setting resistor is required.


Slew rate, settling time, gain-bandwidth product, overdrive recovery time are all improved compared to competitive high speed instrumentation amplifiers.

Industry best speed performance is combined with impressive precision specifications: less than 10pA input bias and offset currents, 180 $\mu$ V offset voltage. Unlike other FET input instrumentation amplifiers, on the LT1102 there is no output offset voltage contribution to total error, and input bias currents do not double with every 10 $^{\circ}$ C rise in temperature. Indeed, at 70 $^{\circ}$ C ambient temperature the input bias current is only 40pA.


**LT**, LT, LTC and LTM are registered trademarks of Linear Technology Corporation.

## TYPICAL APPLICATION

**Wideband Instrumentation Amplifier  
with  $\pm 150$ mA Output Current**



**Slew Rate**



# LT1102



## ABSOLUTE MAXIMUM RATINGS (Note 1)

Supply Voltage .....  $\pm 20\text{V}$   
 Differential Input Voltage .....  $\pm 40\text{V}$   
 Input Voltage .....  $\pm 20\text{V}$

Output Short-Circuit Duration ..... Indefinite  
 Operating Temperature Range  
 LT1102I .....  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$   
 LT1102AC/LT1102C .....  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$   
 LT1102AM/LT1102M (**OBSELETE**).....  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$   
 Storage Temperature Range .....  $-65^{\circ}\text{C}$  to  $150^{\circ}\text{C}$   
 Lead Temperature (Soldering, 10 sec) .....  $300^{\circ}\text{C}$

**Order Options** Tape and Reel: Add #TR  
 Lead Free: Add #PBF Lead Free Tape and Reel: Add #TRPBF  
 Lead Free Part Marking: <http://www.linear.com/leadfree/>

## PACKAGE/ORDER INFORMATION

|                                                                                                                                                                                                               |                                                                                   |                                                                                                                                                                                                                                                                                                            |                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
|  <p>H PACKAGE<br/>8-LEAD TO-5 METAL CAN</p> <p><b>OBSELETE PACKAGE</b><br/>Consider the N8 Package for Alternate Source</p> | <p>ORDER PART NUMBER</p> <p>LT1102AMH<br/>LT1102MH<br/>LT1102ACH<br/>LT1102CH</p> |  <p>N8 PACKAGE<br/>8-LEAD PDIP</p> <p><math>T_{JMAX} = 100^{\circ}\text{C}</math>, <math>\theta_{JA} = 130^{\circ}\text{C/W}</math></p> <p><b>OBSELETE PACKAGE</b><br/>Consider the N8 Package for Alternate Source</p> | <p>ORDER PART NUMBER</p> <p>LT1102IN8<br/>LT1102ACN8<br/>LT1102CN8</p> <p>LT1102MJ8<br/>LT1102CJ8</p> <p>LT1102 • POI01</p> |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|

Consult LTC Marketing for parts specified with wider operating temperature ranges.

# ELECTRICAL CHARACTERISTICS

$V_S = \pm 15V$ ,  $V_{CM} = 0V$ ,  $T_A = 25^\circ C$ , Gain = 10 or 100, unless otherwise noted.

| SYMBOL   | PARAMETER                       | CONDITIONS                                        | LT1102AM/AC |            |          | LT1102M/I/C |            |          | UNITS          |
|----------|---------------------------------|---------------------------------------------------|-------------|------------|----------|-------------|------------|----------|----------------|
|          |                                 |                                                   | MIN         | TYP        | MAX      | MIN         | TYP        | MAX      |                |
| $G_E$    | Gain Error                      | $V_O = \pm 10V$ , $R_L = 50k$ or $2k$             |             | 0.010      | 0.050    |             | 0.012      | 0.070    | %              |
| $G_{NL}$ | Gain Nonlinearity               | $G = 100$ , $R_L = 50k$                           |             | 3          | 14       |             | 4          | 18       | ppm            |
|          |                                 | $G = 100$ , $R_L = 2k$                            |             | 8          | 20       |             | 8          | 25       | ppm            |
|          |                                 | $G = 10$ , $R_L = 50k$ or $2k$                    |             | 7          | 16       |             | 7          | 30       | ppm            |
| $V_{OS}$ | Input Offset Voltage            |                                                   |             | 180        | 600      |             | 200        | 900      | $\mu V$        |
| $I_{OS}$ | Input Offset Current            |                                                   |             | 3          | 40       |             | 4          | 60       | pA             |
| $I_B$    | Input Bias Current              |                                                   |             | $\pm 3$    | $\pm 40$ |             | $\pm 4$    | $\pm 60$ | pA             |
|          | Input Resistance<br>Common Mode | $V_{CM} = -11V$ to $8V$                           |             | $10^{12}$  |          |             | $10^{12}$  |          | $\Omega$       |
|          |                                 | $V_{CM} = 8V$ to $11V$                            |             | $10^{11}$  |          |             | $10^{11}$  |          | $\Omega$       |
|          | Differential Mode               |                                                   |             | $10^{12}$  |          |             | $10^{12}$  |          | $\Omega$       |
| $e_n$    | Input Noise Voltage             | 0.1Hz to 10Hz                                     |             | 2.8        |          |             | 2.8        |          | $\mu V_{p-p}$  |
|          | Input Noise Voltage<br>Density  | $f_0 = 10Hz$                                      |             | 37         |          |             | 37         |          | $nV/\sqrt{Hz}$ |
|          |                                 | $f_0 = 1000Hz$ (Note 2)                           |             | 19         | 30       |             | 20         |          | $nV/\sqrt{Hz}$ |
|          | Input Noise Current<br>Density  | $f_0 = 1000Hz$ , 10Hz (Note 3)                    |             | 1.5        | 4        |             | 2          | 5        | $fA/\sqrt{Hz}$ |
|          | Input Voltage Range             |                                                   | $\pm 10.5$  | $\pm 11.5$ |          | $\pm 10.5$  | $\pm 11.5$ |          | V              |
| CMRR     | Common Mode<br>Rejection Ratio  | 1k Source Imbalance, $V_{CM} = \pm 10.5V$         | 84          | 98         |          | 82          | 97         |          | dB             |
| PSRR     | Power Supply<br>Rejection Ratio | $V_S = \pm 9V$ to $\pm 18V$                       | 88          | 102        |          | 86          | 101        |          | dB             |
| $I_S$    | Supply Current                  |                                                   |             | 3.3        | 5.0      |             | 3.4        | 5.6      | mA             |
| $V_O$    | Maximum Output<br>Voltage Swing | $R_L = 50k$                                       | $\pm 13.0$  | $\pm 13.5$ |          | $\pm 13.0$  | $\pm 13.5$ |          | V              |
|          |                                 | $R_L = 2k$                                        | $\pm 12.0$  | $\pm 13.0$ |          | $\pm 12.0$  | $\pm 13.0$ |          | V              |
| BW       | Bandwidth                       | $G = 100$ (Note 4)                                | 120         | 220        |          | 100         | 220        |          | kHz            |
|          |                                 | $G = 10$ (Note 4)                                 | 2.0         | 3.5        |          | 1.7         | 3.5        |          | MHz            |
| SR       | Slew Rate                       | $G = 100$ , $V_{IN} = \pm 0.13V$ , $V_O = \pm 5V$ | 12          | 17         |          | 10          | 17         |          | V/ $\mu s$     |
|          |                                 | $G = 10$ , $V_{IN} = \pm 1V$ , $V_O = \pm 5V$     | 21          | 30         |          | 18          | 30         |          | V/ $\mu s$     |
|          | Overdrive Recovery              | 50% Overdrive (Note 5)                            |             | 400        |          |             | 400        |          | ns             |
|          | Settling Time                   | $V_O = 20V$ Step (Note 4)                         |             |            |          |             |            |          |                |
|          |                                 | $G = 10$ to 0.05%                                 |             | 1.8        | 4.0      |             | 1.8        | 4.0      | $\mu s$        |
|          |                                 | $G = 10$ to 0.01%                                 |             | 3.0        | 6.5      |             | 3.0        | 6.5      | $\mu s$        |
|          |                                 | $G = 100$ to 0.05%                                |             | 7          | 13       |             | 7          | 13       | $\mu s$        |
|          |                                 | $G = 100$ to 0.01%                                |             | 9          | 18       |             | 9          | 18       | $\mu s$        |

**ELECTRICAL CHARACTERISTICS**

$V_S = \pm 15V$ ,  $V_{CM} = 0V$ , Gain = 10 or 100,  $-55^\circ C \leq T_A \leq 125^\circ C$  for AM/M grades,  
 $-40^\circ C \leq T_A \leq 85^\circ C$  for I grades, unless otherwise noted.

| SYMBOL                   | PARAMETER                    | CONDITIONS                                        | LT1102AM   |            |          | LT1102M/I  |            |          | UNITS            |
|--------------------------|------------------------------|---------------------------------------------------|------------|------------|----------|------------|------------|----------|------------------|
|                          |                              |                                                   | MIN        | TYP        | MAX      | MIN        | TYP        | MAX      |                  |
| $G_E$                    | Gain Error                   | $G = 100$ , $V_O = \pm 10V$ , $R_L = 50k$ or $2k$ |            | 0.10       | 0.25     |            | 0.10       | 0.30     | %                |
|                          |                              | $G = 10$ , $V_O = \pm 10V$ , $R_L = 50k$ or $2k$  |            | 0.05       | 0.12     |            | 0.06       | 0.15     | %                |
| $TCG_E$                  | Gain Error Drift<br>(Note 6) | $G = 100$ , $R_L = 50k$ or $2k$                   |            | 9          | 20       |            | 10         | 25       | ppm/ $^\circ C$  |
|                          |                              | $G = 10$ , $R_L = 50k$ or $2k$                    |            | 5          | 10       |            | 6          | 14       | ppm/ $^\circ C$  |
| $G_{NL}$                 | Gain Nonlinearity            | $G = 100$ , $R_L = 50k$                           |            | 20         | 70       |            | 24         | 90       | ppm              |
|                          |                              | $G = 100$ , $R_L = 2k$                            |            | 28         | 85       |            | 32         | 110      | ppm              |
|                          |                              | $G = 10$ , $R_L = 50k$ or $2k$                    |            | 9          | 20       |            | 9          | 24       | ppm              |
| $V_{OS}$                 | Input Offset Voltage         |                                                   |            | 300        | 1400     |            | 400        | 2000     | $\mu V$          |
| $\Delta V_{OS}/\Delta T$ | Input Offset Voltage Drift   | (Note 6)                                          |            | 2          | 8        |            | 3          | 12       | $\mu V/^\circ C$ |
| $I_{OS}$                 | Input Offset Current         |                                                   |            | 0.3        | 4        |            | 0.4        | 6        | nA               |
| $I_B$                    | Input Bias Current           |                                                   |            | $\pm 2$    | $\pm 10$ |            | $\pm 2.5$  | $\pm 15$ | nA               |
| CMRR                     | Common Mode Rejection Ratio  | $V_{CM} = \pm 10.3V$                              | 82         | 97         |          | 80         | 96         |          | dB               |
| PSRR                     | Power Supply Rejection Ratio | $V_S = \pm 10V$ to $\pm 17V$                      | 88         | 100        |          | 84         | 99         |          | dB               |
| $I_S$                    | Supply Current               | $T_A = 125^\circ C$                               |            | 2.5        |          |            | 2.5        |          | mA               |
| $V_O$                    | Maximal Output Voltage Swing | $R_L = 50k$                                       | $\pm 12.5$ | $\pm 13.2$ |          | $\pm 12.5$ | $\pm 13.2$ |          | V                |
|                          |                              | $R_L = 2k$                                        | $\pm 12.0$ | $\pm 12.6$ |          | $\pm 12.0$ | $\pm 12.6$ |          | V                |

$V_S = \pm 15V$ ,  $V_{CM} = 0V$ , Gain = 10 or 100,  $0^\circ C \leq T_A \leq 70^\circ C$ , unless otherwise noted.

| SYMBOL                   | PARAMETER                    | CONDITIONS                                        | LT1102AC   |            |           | LT1102C    |            |           | UNITS            |
|--------------------------|------------------------------|---------------------------------------------------|------------|------------|-----------|------------|------------|-----------|------------------|
|                          |                              |                                                   | MIN        | TYP        | MAX       | MIN        | TYP        | MAX       |                  |
| $G_E$                    | Gain Error                   | $G = 100$ , $V_O = \pm 10V$ , $R_L = 50k$ or $2k$ |            | 0.04       | 0.11      |            | 0.05       | 0.14      | %                |
|                          |                              | $G = 10$ , $V_O = \pm 10V$ , $R_L = 50k$ or $2k$  |            | 0.03       | 0.09      |            | 0.04       | 0.12      | %                |
| $TCG_E$                  | Gain Error Drift<br>(Note 6) | $G = 100$ , $R_L = 50k$ or $2k$                   |            | 8          | 18        |            | 9          | 22        | ppm/ $^\circ C$  |
|                          |                              | $G = 10$ , $R_L = 50k$ or $2k$                    |            | 5          | 10        |            | 6          | 14        | ppm/ $^\circ C$  |
| $G_{NL}$                 | Gain Nonlinearity            | $G = 100$ , $R_L = 50k$                           |            | 8          | 30        |            | 9          | 40        | ppm              |
|                          |                              | $G = 100$ , $R_L = 2k$                            |            | 11         | 36        |            | 12         | 48        | ppm              |
|                          |                              | $G = 10$ , $R_L = 50k$ or $2k$                    |            | 8          | 18        |            | 8          | 22        | ppm              |
| $V_{OS}$                 | Input Offset Voltage         |                                                   |            | 230        | 1000      |            | 280        | 1400      | $\mu V$          |
| $\Delta V_{OS}/\Delta T$ | Input Offset Voltage Drift   | (Note 6)                                          |            | 2          | 8         |            | 3          | 12        | $\mu V/^\circ C$ |
| $I_{OS}$                 | Input Offset Current         |                                                   |            | 10         | 150       |            | 15         | 220       | pA               |
| $\Delta I_{OS}/\Delta T$ | Input Offset Current Drift   | (Note 6)                                          |            | 0.5        | 3         |            | 0.5        | 4         | pA/ $^\circ C$   |
| $I_B$                    | Input Bias Current           |                                                   |            | $\pm 40$   | $\pm 300$ |            | $\pm 50$   | $\pm 400$ | pA               |
| $\Delta I_B/\Delta T$    | Input Bias Current Drift     | (Note 6)                                          |            | 1          | 4         |            | 1          | 6         | pA/ $^\circ C$   |
| CMRR                     | Common Mode Rejection Ratio  | $V_{CM} = \pm 10.3V$                              | 83         | 98         |           | 81         | 97         |           | dB               |
| PSRR                     | Power Supply Rejection Ratio | $V_S = \pm 10V$ to $\pm 17V$                      | 87         | 101        |           | 85         | 100        |           | dB               |
| $I_S$                    | Supply Current               | $T_A = 70^\circ C$                                |            | 2.8        |           |            | 2.9        |           | mA               |
| $V_O$                    | Maximum Output Voltage Swing | $R_L = 50k$                                       | $\pm 12.8$ | $\pm 13.4$ |           | $\pm 12.8$ | $\pm 13.4$ |           | V                |
|                          |                              | $R_L = 2k$                                        | $\pm 12.0$ | $\pm 12.8$ |           | $\pm 12.0$ | $\pm 12.8$ |           | V                |

## ELECTRICAL CHARACTERISTICS

**Note 1:** Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

**Note 2:** This parameter is tested on a sample basis only.

**Note 3:** Current noise is calculated from the formula:

$$i_n = (2qI_B)^{1/2}$$

where  $q = 1.6 \cdot 10^{-19}$  coulomb. The noise of source resistors up to  $1\text{G}\Omega$  swamps the contribution of current noise.

**Note 4:** This parameter is not tested. It is guaranteed by design and by inference from the slew rate measurement.


**Note 5:** Overdrive recovery is defined as the time delay from the removal of an input overdrive to the output's return from saturation to linear operation.

50% overdrive equals  $V_{IN} = \pm 2\text{V}$  ( $G = 10$ ) or  $V_{IN} = \pm 200\text{mV}$  ( $G = 100$ ).


**Note 6:** This parameter is not tested. It is guaranteed by design and by inference from other tests.

## TYPICAL PERFORMANCE CHARACTERISTICS


**Small Signal Response,  $G = 10$**   
(Input = 50mV Pulse)




**Small Signal Response,  $G = 100$**   
(Input = 5mV Pulse)




**Slew Rate,  $G = 100$**   
(Input =  $\pm 130\text{mV}$  Pulse)




**Settling Time,  $G = 10$**   
(Input From  $-10\text{V}$  to  $10\text{V}$ )




**Settling Time,  $G = 10$**   
(Input From  $10\text{V}$  to  $-10\text{V}$ )



**Settling Time,  $G = 100$**   
(Input From  $-10\text{V}$  to  $10\text{V}$ )




**Settling Time,  $G = 100$**   
(Input From  $10\text{V}$  to  $-10\text{V}$ )




# TYPICAL PERFORMANCE CHARACTERISTICS

Capacitive Load Handling




LT1102 • TPC08

Output Impedance vs Frequency




LT1102 • TPC09

Gain vs Frequency




LT1102 • TPC10

Undistorted Output vs Frequency




LT1102 • TPC11

Voltage Noise vs Frequency




LT1102 • TPC12

Input Bias Current Over the Common Mode Range




LT1102 • TPC13

Warm-Up Drift




LT1102 • TPC14

Common Mode Range vs Temperature



LT1102 • TPC15


Supply Current vs Temperature



LT1102 • TPC16


# TYPICAL PERFORMANCE CHARACTERISTICS

Short-Circuit Current vs Time




LT1102 • TPC17

Distribution of Offset Voltage




LT1102 • TPC18

Gain Error vs Temperature



LT1102 • TPC19

Gain Nonlinearity Over Temperature



LT1102 • TPC20

## APPLICATIONS INFORMATION


In the two op amp instrumentation amplifier configuration, the first amplifier is basically in unity gain, and the second amplifier provides all the voltage gain. In the LT1102, the second amplifier is decompensated for gain of 10 stability, therefore high slew rate and bandwidth are achieved. Common mode rejection versus frequency is also optimized in the  $G = 10$  mode, because the bandwidths of the two op amps are similar. When  $G = 100$ , this statement is no longer true; however, by connecting an 18pF capacitor between pins 1 and 2, a common mode AC gain is created to cancel the inherent roll-off. From 200Hz to 30kHz, CMRR versus frequency is improved by an order of magnitude.

### Input Protection

Instrumentation amplifiers are often used in harsh environments where overload conditions can occur. The LT1102 employs FET input transistors, consequently the differential input voltage can be  $\pm 30V$  (with  $\pm 15V$  supplies,  $\pm 36V$  with  $\pm 18V$  supplies). Some competitive instrumentation amplifiers have NPN inputs which are protected by back-to-back diodes. When the differential input Voltage exceeds  $\pm 13V$  on these competitive devices, input current increases to milliampere level; more than  $\pm 10V$  differential voltage can cause permanent damage.

When the LT1102 inputs are pulled below the negative supply or above the positive supply, the inputs will clamp a diode voltage below or above the supplies. No damage will occur if the input current is limited to 20mA.

**Common Mode Rejection Ratio vs Frequency**



LT1102 • A101

### Gains Between 10 and 100

Gains between 10 and 100 can be achieved by connecting two equal resistors ( $= R_X$ ) between pins 1 and 2 and pins 7 and 8.


$$\text{Gain} = 10 + \frac{R_X}{R + R_X/90}$$

The nominal value of  $R$  is 1.84k $\Omega$ . The usefulness of this method is limited by the fact that  $R$  is not controlled to better than  $\pm 10\%$  absolute accuracy in production. However, on any specific unit, 90R can be measured between Pins 1 and 2.


# APPLICATIONS INFORMATION

## Gain = 20, 110, or 200 Instrumentation Amplifiers

### Differential Output




### Single Ended Output



GAIN = 200, AS SHOWN  
 GAIN = 20, SHORT PIN 1 TO PIN 2, PIN 7 TO PIN 8 ON BOTH DEVICES  
 GAIN = 110, SHORT PIN 1 TO PIN 2, PIN 7 TO PIN 8 ON ONE DEVICE,  
 NOT ON THE OTHER  
 INPUT REFERRED NOISE IS REDUCED BY  $\sqrt{2}$  (G = 200 OR 20)

LT1102 • AI02


## Multiplexed Input Data Acquisition



800kHz SIGNALS CAN BE MULTIPLEXED WITH LT1102 IN G = 10

LT1102 • AI03

## Voltage Programmable Current Source is Simple and Precise




LT1102 • AI04

## Dynamic Response of the Current Source

A = 5V/DIV

B = 5mA/DIV





HORIZ. = 20µs/DIV


LT1102 • AI05

## TYPICAL APPLICATIONS


### Basic Connections



### Settling Time Test Circuit




### Offset Nulling



## PACKAGE DESCRIPTION


### H Package 8-Lead TO-5 Metal Can (.230 Inch PCD) (Reference LTC DWG # 05-08-1321)



\* LEAD DIAMETER IS UNCONTROLLED BETWEEN THE REFERENCE PLANE AND THE SEATING PLANE

\*\* FOR SOLDER DIP LEAD FINISH, LEAD DIAMETER IS  $\frac{.016 - .024}{(0.406 - 0.610)}$  H8 (TO-5) 0.230 PCD 0801


### J8 Package 8-Lead Cerdip (Narrow .300 Inch, Hermetic) (Reference LTC DWG # 05-08-1110)



## OBSOLETE PACKAGES

# PACKAGE DESCRIPTION

**N8 Package**  
**8-Lead PDIP (Narrow .300 Inch)**  
 (Reference LTC DWG # 05-08-1510)



NOTE:  
 1. DIMENSIONS ARE  $\frac{\text{INCHES}}{\text{MILLIMETERS}}$

\*THESE DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS.  
 MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED .010 INCH (0.254mm)