


PANDUIT PART #	RECOMMENDED FASTENER	A	B	C	D +.015 (+.38) -.005 (-.13)	E	F	G (REF)	H (REF)	I (REF)	USE WITH CABLE TIE CROSS SECTIONS	WEIGHT 100 pcs lbs (g)
TM2S8-186	#8 (M4) SCREW	.630 (16.0)	.422 (10.7)	.275 (7.0)	.215 (5.5)	.064 (1.6)	.155 (3.9)	.105 (2.7)	.325 (8.3)	.178 (4.5)	MINIATURE INTERMEDIATE STANDARD	.10 (45)
TM3S8-186		.867 (22.0)	.614 (15.6)	.373 (9.5)	.322 (8.2)	.087 (2.2)	.209 (5.3)	.114 (2.9)	.325 (8.3)	.178 (4.5)	STANDARD LIGHT HEAVY	.33 (150)
TM3S10-186	#10 (M5) SCREW	.867 (22.0)	.614 (15.6)	.373 (9.5)	.322 (8.2)	.087 (2.2)	.209 (5.3)	.114 (2.9)	.385 (9.8)	.200 (5.1)		.31 (141)



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. COUNTERBORE HOLE TO PROVIDE LESS OF AN OBSTRUCTION TO THE BUNDLE.
3. UNIQUE CRADLE DESIGN PROVIDES MAXIMUM STABILITY AND RIGIDITY TO THE WIRE BUNDLE.

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS

CAD FILENAME/LAYERS W10001CT/01 SS-27607

PANDUIT CORP. TINLEY PARK, ILLINOIS

TM2, TM3 TIE MOUNTS
METAL DETECTABLE POLYPROPYLENE SERIESUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm .1$ (2.5) (XXX) $\pm .020$ (.5)
(.XX) $\pm .02$ (.5) ANGLES $\pm 5^\circ$ UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

										PANDUIT CORP. TINLEY PARK, ILLINOIS				
										TM2, TM3 TIE MOUNTS METAL DETECTABLE POLYPROPYLENE SERIES				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5)(.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± 5°			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
I	9/22/08	ERW		CHANGED TM3S8 'H' DIMENSION FROM .385 TO .325	SS-27606	I				DRAWN BY ERW	MAT'L:		SCALE NONE	
R	9/10/08	ERW	TGS	DRAWING RELEASED	SS-27606	R	TGS			DATE 9/10/08	POLYPROPYLENE COLOR: -186 BLUE		DRAWING NO. SS-27607	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			CHK'D TGS			SIZE	