



HOW TO ORDER:

GLENAIR P/N:	900-012	NF	2	25	-	1	P	1	
MILITARY P/N:	M28840/12	A	2	G		1	P	1	

BASIC PART NUMBER _____
 CLASS CODE (SEE MIL-C-28840) _____
 FIGURE (SEE NOTE 3) _____
 SHELL SIZE (TABLE I) _____

KEY POSITION (SEE MIL-C-28840) _____
 CONTACT STYLE (SEE MIL-C-28840) _____
 INSERT ARRANGEMENT (SEE MIL-C-28840) _____


FIGURE 1

FIGURE 2

900-012
Receptacle, Flange Mount
MIL-C-28840/12



MIL-C-28840

TABLE I: CONNECTOR DIMENSIONS

MILITARY SHELL SIZE	SHELL SIZE	A THREAD CLASS 2A	O REF. MTG.HOLE	R T.P. C _L TO C _L	$\pm .020$ (0.5)	$\pm .008$ (0.2)	GG DIA. MAX.
A	11	.750-.1P-.2L-D.S.	.812 (20.6)	.750 (19.1)	1.023 (26.0)	.123 (3.1)	.758 (19.3)
B	13	.875-.1P-.2L-D.S.	.937 (23.8)	.843 (21.4)	1.138 (28.9)	.123 (3.1)	.880 (22.4)
C	15	1.062-.1P-.2L-D.S.	1.124 (28.5)	.968 (24.6)	1.258 (32.0)	.123 (3.1)	1.005 (25.5)
D	17	1.125-.1P-.2L-D.S.	1.187 (30.1)	1.015 (25.8)	1.383 (35.1)	.123 (3.1)	1.130 (28.7)
E	19	1.312-.1P-.2L-D.S.	1.374 (34.9)	1.140 (29.0)	1.508 (38.3)	.123 (3.1)	1.255 (31.9)
F	23	1.500-.1P-.2L-D.S.	1.562 (39.7)	1.281 (32.5)	1.718 (43.6)	.123 (3.1)	1.443 (36.7)
G	25	1.625-.1P-.2L-D.S.	1.687 (42.8)	1.392 (35.4)	1.818 (46.2)	.150 (3.8)	1.567 (39.8)
H	29	1.812-.1P-.2L-D.S.	1.874 (47.6)	1.568 (39.8)	2.138 (54.3)	.150 (3.8)	1.880 (47.8)
J	33	2.000-.1P-.2L-D.S.	2.062 (52.4)	1.734 (44.0)	2.328 (59.1)	.176 (4.5)	2.067 (52.5)

NOTES:

1. INTERPRET PER MIL-STD-100.
2. SEE MIL-C-28840 FOR ADDITIONAL DESIGN DETAILS.
3. FIGURE 1 LEAVE BLANK, FIGURE 2 INSERT 2
EXAMPLE: M28840/12AG1P1 OR 900-012A251P1 = FIGURE 1
M28840/12A2G1P1 OR 900-012A2251P1 = FIGURE 2.

△ 4 GLENAIR NF = CLASS A
GLENAIR ZU = CLASS B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

<u>900-012NF11-1G1</u>	<u>900-012NF11-1G2</u>	<u>900-012NF11-1P1</u>	<u>900-012NF11-1P3</u>	<u>900-012NF11-1S1</u>	<u>900-012NF11-1S2</u>
<u>900-012NF11-1S3</u>	<u>900-012NF11-1S5</u>	<u>900-012NF11-1S6</u>	<u>900-012NF13-1G1</u>	<u>900-012NF13-1P1</u>	<u>900-012NF13-1P2</u>
<u>900-012NF13-1P3</u>	<u>900-012NF13-1P4</u>	<u>900-012NF13-1P5</u>	<u>900-012NF13-1P6</u>	<u>900-012NF13-1S1</u>	<u>900-012NF13-1S2</u>
<u>900-012NF13-1S3</u>	<u>900-012NF13-1S4</u>	<u>900-012NF13-1S5</u>	<u>900-012NF13-1S6</u>	<u>900-012NF15-1D1</u>	<u>900-012NF15-1F1</u>
<u>900-012NF15-1F6</u>	<u>900-012NF15-1G1</u>	<u>900-012NF15-1P1</u>	<u>900-012NF15-1P2</u>	<u>900-012NF15-1P4</u>	<u>900-012NF15-1P5</u>
<u>900-012NF15-1P6</u>	<u>900-012NF15-1S1</u>	<u>900-012NF15-1S2</u>	<u>900-012NF15-1S3</u>	<u>900-012NF15-1S5</u>	<u>900-012NF15-1S6</u>
<u>900-012NF17-1D2</u>	<u>900-012NF17-1D4</u>	<u>900-012NF17-1E2</u>	<u>900-012NF17-1E5</u>	<u>900-012NF17-1P1</u>	<u>900-012NF17-1P2</u>
<u>900-012NF17-1P3</u>	<u>900-012NF17-1P4</u>	<u>900-012NF17-1P5</u>	<u>900-012NF17-1S1</u>	<u>900-012NF17-1S2</u>	<u>900-012NF17-1S3</u>
<u>900-012NF17-1S4</u>	<u>900-012NF19-1F1</u>	<u>900-012NF19-1G1</u>	<u>900-012NF19-1P1</u>	<u>900-012NF19-1P2</u>	<u>900-012NF19-1P3</u>
<u>900-012NF19-1P4</u>	<u>900-012NF19-1S1</u>	<u>900-012NF19-1S2</u>	<u>900-012NF19-1S3</u>	<u>900-012NF19-1S4</u>	<u>900-012NF19-1S5</u>
<u>900-012NF23-1F5</u>	<u>900-012NF23-1P1</u>	<u>900-012NF23-1P2</u>	<u>900-012NF23-1P3</u>	<u>900-012NF23-1P5</u>	<u>900-012NF23-1P6</u>
<u>900-012NF23-1S1</u>	<u>900-012NF23-1S2</u>	<u>900-012NF23-1S4</u>	<u>900-012NF23-1S5</u>	<u>900-012NF25-1B1</u>	<u>900-012NF25-1P1</u>
<u>900-012NF25-1P2</u>	<u>900-012NF25-1P4</u>	<u>900-012NF25-1P5</u>	<u>900-012NF25-1S1</u>	<u>900-012NF25-1S2</u>	<u>900-012NF25-1S3</u>
<u>900-012NF25-1S4</u>	<u>900-012NF25-1S5</u>	<u>900-012NF25-1S6</u>	<u>900-012NF29-1P1</u>	<u>900-012NF29-1P3</u>	<u>900-012NF29-1S1</u>
<u>900-012NF33-1P1</u>	<u>900-012NF33-1P2</u>	<u>900-012NF33-1P3</u>	<u>900-012NF33-1S1</u>	<u>900-012Z113-1G1</u>	<u>900-012ZU13-1P1</u>
<u>900-012ZU15-1S1</u>	<u>900-012ZU17-1S1</u>	<u>900-012ZU23-1F1</u>	<u>900-012NF17-1E1</u>	<u>900-012NF17-1G1</u>	<u>900-012NF17-1G2</u>
<u>900-012NF13-1G2</u>	<u>900-012NF15-1P3</u>	<u>900-012NF23-1G1</u>			