

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC ,UL94V0
-CONTACT MATERIAL: BRASS
-ACCESSORIES: BRASS
-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

- NOMINAL CURRENT: 40A
- CONTACT RESISTANCE: <= 7.3 mOhms
- CONTACT/CONTACT : >=1000 V
- CONTACT/GROUND : >=1200 V
- INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 24 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum
- Female screw : 0.5 N.m minimum

PRESS FIT PERFORMANCES

	PRESS FIT CONTACTS
INSERTION FORCE	$\leq 200 \text{ N}$ Average insertion 160N
EXTRACTION FORCE	$\geq 30 \text{ N}$


NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.
- Termination plating spec:
 - Ni 1.27µm+Sn 0.5 to 1.5µ(pure bright)
- Active area plating spec:
 - Ni + Gold
- Shell plating :2 to 4µm Cu + Ni + 3 to 10µmm Sn(pure bright)
- Accessories: Sn pure bright + nickel
- Packaging spec: See GS-14-920


TABLE 1: PCB HOLE DIAMETERS

HOLE 1:PCB HOLE DIAMETERS		SnPb holes for CONTACTS	Sn holes for CONTACTS	holes ACCESSORIES
P.C.B HOLE DEFINITION (NOTE-1 AND 2)	DRILL DIAMETER	ø3.22 REF(NOTE 3)	ø3.22 REF(NOTE 3)	ø3.10±0.10
	DRILLED HOLE	ø3.19-3.25	ø3.19-3.25	
	COPPER PLATING	25μ MINI (RECOMMENDED 50μ MAXI)	25μ MINI (RECOMMENDED 50μ MAXI)	
	TIN-LEAD PLATING	15μ MAXI (RECOMMENDED 5μ MINI)		
	TIN PLATING		0.8 tol,2μ	
	FINISH HOLE (AFTER REFLOW)	ø 3.02-3.20	ø3.08-3.20	

NOTE-1: THESE DIMENSIONS MUST BE RESPECT TO SECURE PRESS-FIT PIN PERFORMANCES.
NOTE-2: ACCORDING TO IEC-352-5 SPEC.
NOTE-3: MAJOR REQUIREMENT FOR PRESS FIT PIN PERFORMANCE



DETAIL OF PRESS FIT
scale: 3



5W5 FOR EXAMPLE

Series

DBL5W5S81C6M40LF

Shell size: **E A B C**
(see sheet 3)

Front accessory definition
(see sheet 2)

blank: without accessory

L : threaded insert M3

0 : threaded insert UNC 4-40

V : female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts

S : Socket

Termination type

81C Right angle/Europe standard

Plating

5 200 matings/unmatings

6 500 matings/unmatings

PCB accessories definition(see sheet 2)

M Metal brackets


A Without accessory

Power contacts —


40 : Fitted with power contacts 40 Amp.

rev	ecn no	dr	date
A	LS05-0113	MPE	2005-10-1
B	LS06-0208	LGO	2006-12-1
C	LS07-0273	MPE	2007/11/0
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - ☒ 150 1302		tolerance std ISO 406 ISO 1101		projection 		 mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	P LEARGE	2005-10-11			0.XX	±0.1				
Chr					0°. ±2°	0.XXX			±0.05	ECN
Appr			Product family				- Spec ref			
			SUB FEMALE DW EUROPE foot print				C01-8639-2316		Rev. C	
full power right angle press fit							CUSTOMER		sheet 1 of 5	



www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED						Scale
Dr	M PESSON	2005-10-11	ANGULAR	0.X	±0.3	size		
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	±0.1	A2		
Chr			0° ±2°	0.XXX	±0.05	ECN	LS07-0273	
Appr			Product family			Spec ref		
FCI		SUB FEMALE DW EUROPE foot print		full power right angle press fit		cat no	C01-8639-2316	Rev. C
						CUSTOMER		sheet 2 of 5



PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS8IC5A40LF	40	200	without	without
D*LxWxS8IC5A40LF	40	200	insert M3	without
D*OxWxS8IC5A40LF	40	200	insert UNC 4.40	without
D*VxWxS8IC5A40LF	40	200	female screw UNC 4.40	without
D*xWxS8IC5M40LF	40	200	without	metal bracket
D*LxWxS8IC5M40LF	40	200	insert M3	metal bracket
D*OxWxS8IC5M40LF	40	200	insert UNC 4.40	metal bracket
D*VxWxS8IC5M40LF	40	200	female screw UNC 4.40	metal bracket

shell size

E
A
A
B
C










LAYOUTS
xWx
2V2
3V3
3W3
5W5
8W8

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS8IC6A40LF	40	500	without	without
D*LxWxS8IC6A40LF	40	500	insert M3	without
D*OxWxS8IC6A40LF	40	500	insert UNC 4.40	without
D*VxWxS8IC6A40LF	40	500	female screw UNC 4.40	without
D*xWxS8IC6M40LF	40	500	without	metal bracket
D*LxWxS8IC6M40LF	40	500	insert M3	metal bracket
D*OxWxS8IC6M40LF	40	500	insert UNC 4.40	metal bracket
D*VxWxS8IC6M40LF	40	500	female screw UNC 4.40	metal bracket





Copyright FCI.

www.fciconnect.com			surface ☒ tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1
Eng	P LEGARE	2005-10-11			0.XX	±0.1		
Chr			0° ±2°		0.XXX	±0.05	ECN	LS07-0273
Appr			Product family			- Spec ref		
			SUB FEMALE DW EUROPE foot print				Rev. C	
			full power right angle press fit				C	
catalog no			-		CUSTOMER			sheet 3 of 5



SIDE VIEW FOR ALL LAYOUTS





Copyright FCI.

www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	M PESSON	2005-10-11	ANGULAR	0.X	± 0.3		size	A2
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	± 0.1		Scale	2:1
Chr			0° $\pm 2°$	0.XXX	± 0.05		ECN	LS07-0273
Appr			Product family				Spec ref	
FCI		SUB FEMALE DW EUROPE foot print			C01-8639-2316		Rev.	C
		full power right angle press fit					CUSTOMER	
		catalog no					sheet 5 of 5	