



4

3

2



1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FT	0		C	REVISED PER 0G3B-0119-01	20AUG2001	EZ DB




282853-2 AS SHOWN

- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 WIRE SIZE RANGE
SOLID WIRE: 0,03-2,5mm² (13AWG).
STRANDED WIRE: 0,03-1,5mm² (15AWG).
- 4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 6 NOT CUMULATIVE TOLERANCE.



127.00	13	1-282853-3
116.84	12	1-282853-2
106.68	11	1-282853-1
96.52	10	1-282853-0
86.36	9	282853-9
76.20	8	282853-8
66.04	7	282853-7
55.88	6	282853-6
45.72	5	282853-5
35.56	4	282853-4
25.40	3	282853-3
15.24	2	282853-2
DIM. A	N° OF POS.	PART NUMBER

RECOMMENDED PCB LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 20AUG2001 E. ZANOLINI	BUCHANAN Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK 20AUG2001 D. BIEVENOUR		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 20AUG2001 D. BIEVENOUR	NAME TERMINAL BLOCK PCB MOUNT TOP ENTRY WIRE 10.16mm PITCH	
0 PLC ± 1 PLC ±.3 2 PLC ±.25 3 PLC ± 4 PLC ± ANGLES ±2		PRODUCT SPEC 108-20166		
MATERIAL		APPLICATION SPEC 114-20079	SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-282853	
FINISH		WEIGHT -		
CUSTOMER DRAWING			SCALE 3:1	SHEET 1 OF 1 REV C