

Duplex Multimode 50/125 Fiber Plenum Rated Patch Cable (LC/LC), 30M (100-ft.)

MODEL NUMBER: **N520-30M-P**



Description

Tripp Lite's 30-meter multimode duplex Fibre Channel optic LC/LC patch cable is manufactured from 50/125 zipcord fiber. The cable has LC connectors on each end. It has a PLENUMrated jacket and is FDDI and OFNR rated. 50/125 Duplex multimode fiber is most commonly used in Fibre Channel applications. It is backward compatible with 62.5 micron fiber and provides built-in headroom for future applications. Plenum rated cable used where local fire code calls for fireproof cable. The cable provides higher bandwidth optimized for Gigabit and 10Gbps networks as well. Also available in 1, 2, 3, 5, 10, 15, 20, 25, and 50 meter lengths. Enter "N520-" in the search field to bring up all lengths. For LC-SC cables, search "N516-", and for SC-SC, search "N506-".

Features

- Constructed with 50/125 micron cable
- Length - 30M
- Plenum Rated (CMP) jacket
- Use on fiber and fibre channel installations
- LC male to LC male connectors
- Higher bandwidth optimized for Gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications
- Number of fibers: 2
- Fiber type: all glass graded index
- Core diameter: two 50+/-3 microns
- CLAD diameter: 125+/-2 microns
- Primary coating diameter: 245+/-15 microns
- Primary coating material: acrylate
- Secondary coating diameter: 900+/-50 microns
- Attenuation @850NM: 3.5DB/KM maximum, @1300NM: 1.0DB/KM maximum

Highlights

- Premium PLENUM multimode patch cable
- Attenuation loss meets or exceeds the latest industry standards
- Loop-back cables provide an easier "single-person" solution for testing fiber optic cable systems
- Higher bandwidth optimized for Gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/LC connectors
- Use Plenum jacketed cable where local fire codes dictate

Package Includes

- 30M duplex MMF cable LC/LC 50/125 fiber, Plenum rated jacket



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Bandwidth @850NM: 220 MHz-KM minimum, @1300NM: 600 MHz-KM minimum
- Numeric aperture: .275 nominal
- Proof test level: 100,000 PSI
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	50/125 - OM2
Intended Application	Computer Networking (Fiber)
Cable Type	MULTIMODE 50/125 FIBER OPTIC
Model Type	LC/LC
Network Speed	1Gbps
INPUT	
Cable Length (m)	30
UPC ASSIGNMENT	
Unit Carton UPC#	037332145314
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	LC
Connector B	LC
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.