

CCPD-033 5×7mm SMD LVPECL Clock Oscillator

CCPD-033 Model
5×7 mm SMD, 3.3V, LVPECL



Model CCPD-033 is a 77.760 MHz to 161.132800 MHz LVPECL Clock Oscillator operating at 3.3 Volts. The oscillator utilizes a High Q Third Overtone crystal design providing very low Jitter and Phase Noise. No Sub-Harmonics are present in the Output Signal.



5×7mm SMD

Applications:

**Digital Video
SONET/SDH/DWDM
Storage Area Networks
Broadband Access
Ethernet, Gigabit Ethernet**

Rev: T
Date: 19-Nov-2014
Page 1 of 3

CCPD-033 5×7mm SMD LVPECL Clock Oscillator



CCPD-033 Model

5×7 mm SMD, 3.3V, LVPECL

Frequency Range:	77.760 MHz to 161.132800 MHz
Frequency Stability Options(ppm):	±20, ±25, ±50, ±100
Temperature Range:	(standard) 0°C to +70°C
(Option M)	-20°C to +70°C
(Option X)	-40°C to +85°C
Storage:	-45°C to 90°C
Input Voltage:	3.3V ± 0.3V
Input Current:	55mA Typical, 88mA Max
Output:	Differential LVPECL
Symmetry:	45/55% Max @ zero crossing point
Rise/Fall Time:	1nsec Max (20% to 80%)

Logic: Terminated to Vdd-2V into 50 Ω

Temp. 0°C to 85°C "0"=1.490 Min, 1.680 Max

"1"=2.275 Min, 2.420 Max

Temp. -40°C to 0°C "0"=1.470 Min, 1.745 Max

"1"=2.215 Min, 2.420 Max

Disable Time: 200nSec Max

Enable Time: 1mSec Typical, 2mSec Max


Phase Jitter: 12kHz~80MHz 0.5pSec Typical, 1psec RMS Max

Phase Noise: (See Plot Below)

Sub-harmonics:

None

Aging: <3ppm 1st year, <1ppm every year thereafter



Rev: T
Date: 19-Nov-2014
Page 2 of 3

CCPD-033 5×7mm SMD LVPECL Clock Oscillator

CCPD-033 Model
5×7 mm SMD, 3.3V, LVPECL



Crystek Part Number Guide

CCPD - 033 X - 25 - 155.520

#1 #2 #3 #4 #5

#1 Crystek LVPECL Osc.
#2 Model 033
#3 Temp Range: Blank = 0/70°C, M = -20/70°C, X = -40/85°C
#4 Stability: (see Table 1)
#5 Frequency in MHz: 3 or 6 decimal places

Example:
CCPD-033X-25-155.520
3.3V, -40/85°C, ±25ppm, 155.520 MHz

Stability Indicator

Blank	± 100ppm
50	± 50ppm
25	± 25ppm
20*	± 20ppm

*not available in -40/85

Table 1


Mechanical:

Shock: MIL-STD-883, Method 2002, Condition B
Solderability: MIL-STD-883, Method 2003
Vibration: MIL-STD-883, Method 2007, Condition A
Solvent Resistance: MIL-STD-202, Method 215
Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J


Environmental:

Thermal Shock: MIL-STD-883, Method 1011, Condition A
Moisture Resistance: MIL-STD-883, Method 1004


RECOMMENDED REFLOW SOLDERING PROFILE




NOTE: Reflow Profile with 240°C peak also acceptable.




Dimensions inches (mm)
All dimensions are Max unless otherwise specified.



Tristate Function	
Function pin 1	Output pin
Open or N/C	Active
"1" level 0.7×Vdd Min	Active
"0" level 0.3×Vdd Max	High Z



SUGGESTED PAD LAYOUT



0.01µF Bypass Capacitor Recommended

PIN	Connection
1	Enable/Disable
2	N/C
3	GND
4	Output
5	Comp Output
6	Vcc

Rev: T
Date: 19-Nov-2014
Page 3 of 3