

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


55451-2670

Status:

Active

Description:

1.25mm Pitch Mi II™ System Wire-to-Board Header, Dual Row, Vertical, Lead-Free, 26 Circuits



Documents:	
3D Model	Product Specification PS-54596-019 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	55451
Application	Signal, Wire-to-Board
Product Name	Mini Mi II™
UPC	756054760871
Physical	
Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1100.670/mg
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	100V
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-54596-019
Sales Drawing	SD-55451-006

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

55451Series

Mates With

54596 IDT Receptacle Housing

This document was generated on 11/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION