










CONNECTION DIAGRAM(BOTTOM VIEW)



GENERAL TOLERANCE

DIMENTION	TOLERANCE
Max. 1mm	±0.1
1mm~Max. 3mm	±0.2
Min. 3mm	±0.3

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	H.SASAKI	TE Connectivity					
			CHK	N.FUNAYAMA						
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± ± ± ± ± ±	APVD	A.NAGAI	NAME OUDH-D SPEC,000 CUSTOMER DRAWING					
			PRODUCT SPEC	—						
			APPLICATION SPEC	—						
			WEIGHT	—						
MATERIAL	FINISH		CUSTOMER DRAWING		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
—	—				A3	00779	 3-1440007-0	—		
					SCALE	4:1	SHEET	1 OF 2	REV	B2

2		1						
LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

ⓑ

ⓑ


ⓑ


1461249-1	0UDH-SH-148D ,000	48V	0UDH-SH-148D	j
7-1419129-4	0UDH-SH-124D ,000	24V	0UDH-SH-124D	i
7-1419129-2	0UDH-SH-112D ,000	12V	0UDH-SH-112D	h
7-1419145-4	0UDH-SH-106D ,000	6V	0UDH-SH-106D	g
7-1419145-3	0UDH-SH-105D ,000	5V	0UDH-SH-105D	f
8-1419129-5	0UDH-SS-124D ,000	24V	0UDH-SS-124D	e
8-1419129-0	0UDH-SS-112D ,000	12V	0UDH-SS-112D	d
7-1419129-6	0UDH-SS-109D ,000	9V	0UDH-SS-109D	c
7-1419129-5	0UDH-SS-106D ,000	6V	0UDH-SS-106D	b
3-1440007-0	0UDH-SS-105D ,000	5V	0UDH-SS-105D	a
PART NO.	DESCRIPTION	PART B	PART A	ITEM

RELAY TYPE

NOTES
1.-SS-:PLASTIC SEALD TYPE
-SH-:WASHABLE TYPE

Ⓐ 2.LOT NO. SYSTEM AS FOLLOWING:



DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	DWN	 TE Connectivity				
			CHK					
		MATERIAL	FINISH	APVD	NAME			
				0UDH-D SPEC,000 CUSTOMER DRAWING				
				PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				APPLICATION SPEC	A3	00779	Ⓒ= 3-1440007-0	-
				WEIGHT	CUSTOMER DRAWING			
				SCALE 4:1		SHEET 2 OF 2		REV B2