


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER					SIG				POWER		E1
		E2	P6	P5	P4	P3	4	3	2	1	P2	P1	
51750-073-- NOTE ③	D C B A												



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	N/A [N/A]	SIGNAL
PA	.042 [1.07]	POWER
PD	.092 [2.34]	POWER
HA	N/A [N/A]	HOLD-DOWN

mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	angles	COPY	projection	title	code
A	DG06-0033	RYAN	03/01/06	.XX±.01/0.X±0.3	0°±2°			2P + 16S + 4P VERTICAL STB RECEPT	213
				.XXX±.005/0.XX±0.13					
				.XXX±.0020/0.XXX±0.051					
				dr RYAN YUAN 03/01/06		INCH/MM		product family PwrBlade	code
				enrg SALLY LUO 03/01/06		scale 1:1		size A	sheet 1 of 4
				chr BEER FU 03/01/06				dwg no 51750-073	
				appd JOSEPH HSIA 03/01/06					
sheet index	revision sheet	A	A	A	A				
		1	2	3	4				

cage code 22526




Pro/E

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51750-073--
NOTE(3)



mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI	
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	projection	1:1	title	www.fciconnect.com
A				angles	.XXX±.005/0.XX±0.13	INCH/MM	1:1	2P + 16S + 4P	
				dr	.XXX±.002/0.XXX±0.051	scale	1:1	VERTICAL STB RECEPT	
				enrg	RYAN YUAN 03/01/06	product family	PwrBlade	code	
				chr	SALLY LUO 03/01/06	size	A	213	
				appd	BEER FU 03/01/06	dwg no	51750-073	sheet	
					JOSEPH HSIA 03/01/06	2 of 4			
sheet index	revision sheet								

Pro/E


code code 22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51750-073--
NOTE ③



mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI	
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		www.fciconnect.com	
A				linear	.XXX±.005/0.XX±0.13	projection		title	2P + 16S + 4P
				linear	.XXX±.002/0.XXX±0.051				VERTICAL STB RECEPT
				angles	0°±2°			product family	PwrBlade
				dr	RYAN YUAN 03/01/06	INCH/MM		size	dwg no
				enrg	SALLY LUO 03/01/06	scale		A	51750-073
				chr	BEER FU 03/01/06				code
				appd	JOSEPH HSIA 03/01/06				213
sheet index	revision	sheet							sheet
									3 of 4

Pro/E

code code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

PRODUCT NUMBER
51750-073--
NOTE ③

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

② HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

③ PLATING:
SEE PRINT 10064183 FOR PLATING SPEC OF 51750-073; 51750-073LF

④ MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

⑧ MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

⑨ $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.

⑩ "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

⑪ CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE 2				tolerances unless otherwise specified				CUSTOMER				A FCI www.fciconnect.com				
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3				COPY				projection <td colspan="4" rowspan="3">title 2P + 16S + 4P VERTICAL STB RECEPT</td>	title 2P + 16S + 4P VERTICAL STB RECEPT						
A					.XXX±.005/0.XX±0.13															
					.XXX±.0020/0.XXX±0.051															
				angles	0°±2°															
				dr	RYAN YUAN 03/01/06				INCH/MM				product family PwrBlade				code 213			
				engr	SALLY LUO 03/01/06															
				chr	BEER FU 03/01/06				scale 1:1				A 51750-073				sheet 4 of 4			
				appd	JOSEPH HSIA 03/01/06															
sheet index		revision sheet																		

Pro/E

cage code 22526