

REVISIONS

DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1858	A	RELEASED	JWM	04/01/08	JN	04/01/08	JN	04/01/08



Volts: 12
Watts: 50
Filament: C-8
MOL: 1.77
MOD: 2.0
Avg Life: 4000 hrs
Bulb: MR16
Base: GU5.3
Dichroic Reflector
CT deg K: 3000
Approx, Initial Max. Beam CP: 10,000
Beam Angle: 12°
Burning Position: Any

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:					
	Jeff McVicker	04/01/08	Lamp, Narrow spot MR 16					
	CHECKED BY:	DATE:	SIZE	DWG. NO.		ELECTRONIC FILE	REV	
	Jason Nash	04/01/08	A	EXT		16F682	A	
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]		SHEET: 1 OF 1	
	Jason Nash	04/01/08						

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.