





PRELIMINARY

**SOLID STATE DEVICES, INC**14849 Firestone Boulevard · La Mirada, CA 90638  
Phone: (714) 670-SSDI (7734) · Fax: (714) 522-7424**SFF20N60B****Designer's Data Sheet****FEATURES:**

- Rugged construction with polysilicon gate
- Low RDS(on) and high transconductance
- Excellent high temperature stability
- Very fast switching speed
- Fast recovery and superior dv/dt performance
- Increased reverse energy capability
- Low input and transfer capacitance for easy paralleling
- Ceramic Seals for improved hermeticity
- Hermetically sealed surface mount power package
- TX, TXV and Space Level screening available
- Replaces: IXTH20N60 Types

**20 AMPS  
600 VOLTS  
0.35  $\Omega$   
N-CHANNEL  
POWER MOSFET****MILPACK 2****MAXIMUM RATINGS**

| CHARACTERISTIC                                                           | SYMBOL           | VALUE       | UNIT  |
|--------------------------------------------------------------------------|------------------|-------------|-------|
| Drain to Source Voltage                                                  | V <sub>DS</sub>  | 600         | Volts |
| Gate to Source Voltage                                                   | V <sub>GS</sub>  | ±20         | Volts |
| Continuous Drain Current                                                 | I <sub>D</sub>   | 20          | Amps  |
| Operating and Storage Temperature                                        | Top & Tstg       | -55 to +175 | °C    |
| Thermal Resistance, Junction to Case                                     | R <sub>θJC</sub> | 0.5         | °C/W  |
| Total Device Dissipation @ TC=25°C<br>Total Device Dissipation @ TC=55°C | P <sub>D</sub>   | 250<br>190  | Watts |

**PACKAGE OUTLINE: MILPACK 2****PIN OUT:****PIN 1: DRAIN  
PIN 2: SOURCE  
PIN 3: GATE****NOTE: All specifications are subject to change without notification. SCD's for these devices should be reviewed by SSDI prior to release.****DATA SHEET #: F00209 C****MED**

# SFF20N60B

PRELIMINARY



SOLID STATE DEVICES, INC

14849 Firestone Boulevard · La Mirada, CA 90638  
Phone: (714) 670-SSDI (7734) · Fax: (714) 522-7424**ELECTRICAL CHARACTERISTICS @ T<sub>J</sub>=25 °C (Unless Otherwise Specified)**

| RATING                                                                                                                                                                                      |                                                                                       | SYMBOL                                                                        | MIN | TYP                   | MAX                   | UNIT       |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------|-----|-----------------------|-----------------------|------------|
| Drain to Source Breakdown Voltage<br>(V <sub>GS</sub> =0 V, I <sub>D</sub> =250μA)                                                                                                          |                                                                                       | BV <sub>DSS</sub>                                                             | 600 | ---                   | ---                   | V          |
| Drain to Source on State Resistance<br>(V <sub>GS</sub> =10 V, I <sub>D</sub> =60% Rated ID)                                                                                                |                                                                                       | R <sub>DS(on)</sub>                                                           | --- | 0.35                  | 0.35                  | Ω          |
| On State Drain Current<br>(V <sub>DS</sub> > I <sub>D(on)</sub> X R <sub>DS(on)</sub> Max, V <sub>GS</sub> =10 V)                                                                           |                                                                                       | I <sub>D(on)</sub>                                                            | 20  | ---                   | ---                   | A          |
| Gate Threshold Voltage<br>(V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA)                                                                                                        |                                                                                       | V <sub>GS(th)</sub>                                                           | 2.0 | ---                   | 4.5                   | V          |
| Forward Transconductance<br>(V <sub>DS</sub> > I <sub>D(on)</sub> X R <sub>DS(on)</sub> Max,<br>I <sub>DS</sub> =60% rated ID)                                                              |                                                                                       | g <sub>fs</sub>                                                               | 12  | 18                    | ---                   | S(Ω)       |
| Zero Gate Voltage Drain Current<br>(V <sub>DS</sub> =max rated voltage, V <sub>GS</sub> =0 V)<br>(V <sub>DS</sub> =80% rated V <sub>DS</sub> , V <sub>GS</sub> =0 V, T <sub>A</sub> =125°C) |                                                                                       | I <sub>DSS</sub>                                                              | --- | ---                   | 200<br>1000           | μA         |
| Gate to Source Leakage Forward<br>Gate to Source Leakage Reverse                                                                                                                            | At rated V <sub>GS</sub>                                                              | I <sub>GSS</sub>                                                              | --- | ---                   | +100<br>-100          | nA         |
| Total Gate Charge<br>Gate to Source Charge<br>Gate to Drain Charge                                                                                                                          | V <sub>GS</sub> =10 Volts<br>80% rated V <sub>DS</sub><br>50 %Rated ID                | Q <sub>g</sub><br>Q <sub>gs</sub><br>Q <sub>gd</sub>                          | --- | 150<br>29<br>60       | 170<br>40<br>85       | nC         |
| Turn on Delay Time<br>Rise Time<br>Turn Off Delay Time<br>Fall Time                                                                                                                         | V <sub>DD</sub> =50%<br>rated V <sub>DS</sub><br>50% rated ID<br>R <sub>G</sub> =6.2Ω | t <sub>d(on)</sub><br>t <sub>r</sub><br>t <sub>d(off)</sub><br>t <sub>f</sub> | --- | 30<br>30<br>110<br>30 | 40<br>60<br>150<br>60 | nsec       |
| Diode Forward Voltage<br>(I <sub>S</sub> =rated ID, V <sub>GS</sub> =0 V, T <sub>J</sub> =25°C)                                                                                             |                                                                                       | V <sub>SD</sub>                                                               | --- | ---                   | 1.5                   | V          |
| Diode Reverse Recovery Time<br>Reverse Recovery Charge                                                                                                                                      | T <sub>J</sub> =25°C<br>I <sub>F</sub> =10A<br>di/dt=100 A/μsec                       | t <sub>rr</sub><br>Q <sub>RR</sub>                                            | --- | 600<br>---            | 800<br>---            | nsec<br>μC |
| Input Capacitance<br>Output Capacitance<br>Reverse Transfer Capacitance                                                                                                                     | V <sub>GS</sub> =0 Volts<br>V <sub>DS</sub> =25 Volts<br>f= 1 MHz                     | C <sub>iss</sub><br>C <sub>oss</sub><br>C <sub>rss</sub>                      | --- | 4500<br>420<br>140    | ---                   | pF         |

SAFE OPERATING AREA (S.O.A.)  
T<sub>C</sub> = 25 °C, D.C. CONDITION