

48567.75




FIG "F"

COMMERCIAL COPPER CABLE RANGE				METRIC COPPER CABLE RANGE			B"	H"	J" DIA.	L"	T"	W"
CATALOG NUMBER	FIG. NO.	COMPLETE CABLE RANGE	SMALL GROOVE	LARGE GROOVE	COMPLETE CABLE RANGE	SMALL GROOVE						
NAS29-2N	1B	6 SOL. (.162 DIA.) TO 250 kcmil (.575 DIA.)	6 SOL. (.162 DIA.) TO 1/0 STR. (.372 DIA.)	2/0 STR. (.420 DIA.) TO 250 kcmil (.575 DIA.)	10mm ² (.412mm DIA.) TO 120mm ² (.440mm DIA.)	10mm ² (.412mm DIA.) TO 50mm ² (.827mm DIA.)	70mm ² (.922mm DIA.) TO 120mm ² (.440mm DIA.)	60.5 2.38	45.7 1.80	3/8"-16	98.6 3.88 142.7 5.62	50.8 2.00
NAH29-34N	1D											
NAH29-22N	1E											
NAS29-34N	1A											
NAS34-2N	1C	1/0 SOL. (.385 DIA.) TO 500 kcmil (.813 DIA.)	1/0 SOL. (.385 DIA.) TO 4/0 STR. (.529 DIA.)	250 kcmil (.575 DIA.) TO 500 kcmil (.813 DIA.)	50mm ² (.827mm DIA.) TO 240mm ² (.635mm DIA.)	50mm ² (.827mm DIA.) TO 95mm ² (.820mm DIA.)	120mm ² (.440mm DIA.) TO 240mm ² (.635mm DIA.)	60.5 2.38	52.1 2.05	3/8"-16	149.4 5.88 142.7 5.62	55.9 2.20
NAH34-2N	1A											
NAH34-34N	1E											
NAH34-44N	1E											
NAS40-2N	1A	2/0 STR. (.420 DIA.) TO 800 kcmil (1.031 DIA.)	2/0 STR. (.420 DIA.) TO 500 kcmil (.813 DIA.)	500 kcmil (.813 DIA.) TO 800 kcmil (1.031 DIA.)	70mm ² (.922mm DIA.) TO 400mm ² (.635mm DIA.)	70mm ² (.922mm DIA.) TO 240mm ² (.635mm DIA.)	240mm ² (.635mm DIA.) TO 400mm ² (.635mm DIA.)	60.5 2.38	58.4 2.30	3/8"-16	149.4 5.88 142.7 5.62	65.0 2.56
NAH40-2N	1A											
NAS40-34N	1E											
NAH40-34N	1E											
NAS40-44N	1	4/0 STR. (.529 DIA.) TO 1000 kcmil (1.152 DIA.)	4/0 STR. (.529 DIA.) TO 750 kcmil (.938 DIA.)	750 kcmil (.938 DIA.) TO 1000 kcmil (1.152 DIA.)	95mm ² (.820mm DIA.) TO 500mm ² (.635mm DIA.)	95mm ² (.820mm DIA.) TO 400mm ² (.635mm DIA.)	400mm ² (.635mm DIA.) TO 500mm ² (.635mm DIA.)	66.5 2.62	58.4 2.30	3/8"-16	149.4 5.88 142.7 5.62	71.4 2.81
NAH44-2N	1A											
NAH44-34N	1E											
NAH44-44N	1											
NAS46-2N	1A	1000 kcmil (1.152 DIA.) TO 1500 kcmil (1.412 DIA.)	_____	1000 kcmil (1.152 DIA.) TO 1500 kcmil (1.412 DIA.)	500mm ² (.635mm DIA.) TO 800mm ² (.635mm DIA.)	_____	500mm ² (.635mm DIA.) TO 800mm ² (.635mm DIA.)	77.7 3.06	73.2 2.88	1/2"-13	162.3 6.31 185.7 7.31	81.0 3.19
NAH46-34N	1E											
NAH46-44N	1											
NAS48-2N	1A											
NAH48-34N	1E	2000 kcmil (1.632 DIA.) TO 2500 kcmil (1.824 DIA.)	500 kcmil (.813 DIA.) TO 1500 kcmil (1.412 DIA.)	1500 kcmil (1.412 DIA.) TO 2000 kcmil (1.632 DIA.)	240mm ² (.635mm DIA.) TO 1000mm ² (.410mm DIA.)	240mm ² (.635mm DIA.) TO 800mm ² (.635mm DIA.)	800mm ² (.635mm DIA.) TO 1000mm ² (.410mm DIA.)	82.6 3.25	79.2 3.12		165.1 6.50 190.5 7.50	85.9 3.38
NAH48-44N	1											
NAH486-34N	1E	2500 kcmil (1.824 DIA.)	_____	2500 kcmil (1.824 DIA.)	1000 mm ² (41.10 mm DIA.) 1250 mm ² (46.3 mm DIA.)	_____	1000 mm ² (41.10 mm DIA.) 1250 mm ² (46.3 mm DIA.)	95.2 3.75	96.8 3.81	5/8"-11	180.8 7.12	100.6 3.96
NAH486-2N	1F											

NOTES:

▷ COMPLETE CABLE RANGE MAY BE ACCOMMODATED BY REVERSING CAP.

2 CATALOG NUMBER NAH48-44NTMH2 INCLUDES
THE NAH48-44N TERMINAL SHOWN AND THE
TMH2 KIT CONSISTS OF:
(4) 1/2 X 1.75 LONG HEX HEAD BOLTS
(4) 1/2 HEX NUTS
(4) 1/2 SPLIT LOCK WASHERS

MATERIALS:
CAST COPPER ALLOY
(4) 1/2 FLAT WASHERS
ALL HARDWARE IS SILICONE BRONZE

GENERAL NOTES:

1. ALTHOUGH THIS DRAWING MAY ORIGINALLY HAVE BEEN DEVELOPED TO BE USED IN THE ELECTRIC DESIGN OF AEROSPACE PRODUCTS, TECHNIQUES MAY RESULT IN THIS COPY NOT BEING TO SCALE, THEREFORE, DO NOT SCALE THIS PRINT.
2. THE DIMENSIONS, TOLERANCES AND SPECIFICATIONS OF THIS DRAWING ARE PREVIOUS TO THE DEFINITION OF THE FUNCTIONAL REQUIREMENTS FOR THIS COMPONENT OR PRODUCT. ANY PART MEETING THESE REQUIREMENTS SHALL BE CONSIDERED AS COMPLIANT.

THIS DRAWING AND/OR SPECIFICATION IS THE PROPERTY OF FORMAN ENGINEERING CO. INC. IT IS TO BE USED IN STRICT CONFIDENCE AND SHALL NOT BE REPRODUCED, OR COPIED, OR DISCLOSED TO OTHERS, OR USED AS THE BASIS FOR THE MANUFACTURE OF ANY PRODUCT.

TERMINAL			
CAT. NO. <i>NAS-N</i>		(TABLE) <i>SCALE</i>	
DRAWN <i>ASM</i>		DESIGNED <i>H.C. 12-8-83</i>	
DATE <i>12-8-83</i>		SEL. APPROV. <i>12/14/83</i>	
FRAMATOME CONNECTORS USA INC.		PROJ. APPROV.	
BURNBY ELECTRICAL		DRAWING NO.	
 MANCHESTER, NH 03028 U.S.A.		REV. <i>6</i>	
SE79584			