




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		H	REVISED PER 0G3B-0237-05	9/20/05	SS	CJ
			J	REVISED PER ECR-13-011599	08NOV13	AV	RP




- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.3 - 0.9MM² (22-18 AWG).
3. INSULATION RANGE: 1.50-2.39[.059-.094] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1



SECTION C-C
SCALE 20:1

5	0.25[.010] BRASS	1-794221-0
1	0.25[.010] BRASS	794221-3
PRE-TIN	0.25[.010] BRASS	794221-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	 TE Connectivity							
		CHK R. SWING 1-15-97								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SOCKET, MINI UNIVERSAL MATE-N-LOK 2 —						
	0 PLC ± —	APVO —	NAME							
	1 PLC ± —	PRODUCT SPEC —								
	2 PLC ± —	APPLICATION SPEC —								
	3 PLC ± 0.30 [0.012]	—								
4 PLC ± —		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT —		A2 00779 C-794221 —				
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1	REV J