

## 1200RS Series

Through Hole Radial Lead Shielded Inductors



## **FEATURES**

_	D 110		
	RoHS	comn	liani
	110110	CUITID	mann

Radial format

Integral EMI shield

Compact size

Up to 4.6A loc

■ 10µH to 1mH

■ Low DC resistance

■ UL 94V-0 materials

Backward compatible with Sn/Pb soldering systems

## **DESCRIPTION**

The 1200RS Series of inductors is suitable for power line filtering in low to medium current applications such as switching power supply circuits. The integral ferrite shield makes these devices ideal for protecting circuits susceptible to EMI.

For lower current versions with the same footprint see our 1200LRS Series.

SELECTION GUIDE			
Order Code	Inductance (0.1V@10kHz)	DC Current <sup>1</sup>	DC Resistance
	±15%	Max.	Max.
	μН	A	mΩ
12RS103C	10 ±20%	4.6	23
12RS153C	15 ±20%	4.0	36
12RS223C	22 ±20%	3.3	42
12RS333C	33	2.7	57
12RS473C	47	2.2	100
12RS683C	68	1.8	150
12RS104C	100	1.4	190
12RS154C	150	1.25	230
12RS224C	220	1.10	290
12RS334C	330	0.85	510
12RS474C	470	0.72	980
12RS684C	680	0.55	1200
12RS105C	1000	0.44	1500

ABSOLUTE MAXIMUM RATINGS				
Operating free air temperature range	-40°C to +85°C			
Storage temperature range	-40°C to 125°C			

SOLDERING INFORMATION <sup>2</sup>				
Peak wave solder temperature	260°C for 10 seconds			
Pin finish	Matte tin			


All specifications typical at T<sub>A</sub>=25°C


- 1 Maximum DC current occurs when either the inductance falls to 75% of its nominal value or when its temperature rise reaches 40°C, whichever is sooner.
- 2 For further information, please visit www.murata-ps.com/rohs






Through Hole Radial Lead Shielded Inductors







Through Hole Radial Lead Shielded Inductors

