

TOSHIBA

Leading Innovation >>>

www.toshiba-components.com/mobile

> **TC358770XBG DISPLAY
INTERFACE CONVERTER
CHIPSET FOR HIGH
RESOLUTION DISPLAY**
DUAL MIPI® INPUT TO DISPLAY PORT



> TC358770XBG DISPLAY INTERFACE CONVERTER CHIPSET FOR HIGH RESOLUTION DISPLAY

TOSHIBA
Leading Innovation >>>

HIGHLIGHTS

- > TC358770XBG concatenates two video streams coming into its dual MIPI® receivers into one image and converts it into a Display Port video stream
- > Solutions are based on the latest versions of industry standard MIPI DSI 1.01 and VESA Display Port 1.1a
- > Support for high-resolution display port panels that require more than 4 Gbps data bandwidth
- > Audio data is supported via I²S for an external Display Port panel
- > Applicable to portable products such as tablets and netbooks with high-resolution display port panels


DESCRIPTION

The Toshiba Mobile Industry Processor Interface (MIPI®) Display Serial Interface (DSI) to Display Port converter chipset enables Application Processors to support high-resolution Display Port panels that require bandwidth above 4 Gbps. Designated TC358770XBG, the chipset incorporates dual MIPI DSI receivers, and accepts multiple video packets simultaneously over dual DSI receivers. The Application Processor should be able to divide one high-resolution image and send the data over two DSI transmitter ports. The bridge concatenates the video packets from the dual ports into a single video

packet row. After converting the MIPI DSI data into Display Port data, the bridge is able to drive a Display Port panel. Each DSI receiver port has four lanes, with data speed of 1 Gbps per lane, times two ports, for a total throughput bandwidth of up to 8 Gbps. Each MIPI DSI receiver port supports 1 to 4-lane configurations. As the Display Port interface uses fewer lines and power consumption is more efficient, availability and usage of high-resolution Display Port panels is becoming a feature in handheld applications such as tablets and netbooks. The Toshiba TC358770XBG display bridge enables connectivity of Display Port panels to Application Processors with MIPI DSI interfaces. The bridge supports the Synchronous Clock mode of the Display Port interface standard. High-resolution panels such as 1920 x 1200 at 24 bit per pixel can be supported with 4-lane DSI. Higher resolutions than 1920 x 1200, such as Quad-WXGA, creates difficulty as the bandwidth requirement is higher than 4 Gbps. This bridge offers solution in supporting high-resolution panels by utilising the two DSI ports that most Application Processors already have.

The TC358770XBG bridge supports audio streaming from the application processor via I²S interface to the Host. The audio data is transmitted through the Display Port link if the application requires, i.e. connecting to an external panel. The bridge can support either an internal or external Display Port panel at one time.

> TC358770XBG BLOCK DIAGRAM



FEATURES

> DSI RX Ports

- MIPI DSI compliant version 1.01
- Supports two independent DSI RX ports
 - Supports 1 to 4-data lane configurations per port
 - Supports up to 1 Gbps per data lane
 - Bidirectional support on Data Lane 0
 - Receives and concatenates video packets from each DSI link and outputs them as one row of Display Port video packet
- Video input data formats: RGB565, RGB666 and RGB888

> Display Port TX Port

- VESA Display Port 1.1a compliant
- Supports a four-lane main link for high bandwidth applications
 - Supports data rates at 1.62 Gbps or 2.7 Gbps per lane of Display Port link with voltage swings at 0.4, 0.6, 0.8 or 1.2V
 - AUX channel supported at 1 Mbps
- Supports Audio related secondary data packets
- HPD (Hot Plug Detect) support through GPIO based interrupts
- SSCG with ~30 KHz modulation to reduce EMI
- Built in PRBS7 and colorbar generators to test Display Port link
- Supports HDCP encryption
- Support for audio related secondary data packets

> Audio Interface

- Either I²S or TDM Audio interface are available (pins are multiplexed)
- I²S Audio Interface
 - Supports single stereo channel
 - Supports 16, 18, 20 or 24-bit data
 - Supports sampling frequencies of 32, 44.1, 48, 88.2, 96, 176.4 and 192 KHz
- TDM Audio Interface
 - Supports single data link
 - Supports 2, 4, 6 or 8 channels
 - Supports 16, 18, 20 or 24-bit PCM audio data word

> I²C Interface

- I²C slave interface for access to bridge set of registers
- I²C compliant slave interface support for normal (100 KHz) and fast mode (400 KHz)

> Clock Source




- Display Port clock source from an external clock input or clock can be derived from the DSI interface - generates all internal and output clocks to display devices
- Built-in PLLs generate a high speed Display Port serialising clock


> Power Supply Inputs

- Core and MIPI D-PHY: 1.2V +/- 0.1V
- Digital I/O: 1.8 +/- 0.15V
- Display Port: 1.8V

> Package

- TC358770XBG: BGA 100balls, 5mm*5mm size, 0.4mm pitch, 1.0mm height





For more information visit www.toshiba-components.com/mobile

TOSHIBA

Leading Innovation >>>

GERMANY

TOSHIBA ELECTRONICS EUROPE GMBH CENTRAL EUROPEAN SALES

Hansaallee 181, 40549 Düsseldorf
Tel.: +49 (0211) 5296 0
Fax.: +49 (0211) 5296 400

FRANCE

TOSHIBA ELECTRONICS EUROPE GMBH, FRANCE BRANCH

7 rue Ampère, 92804 Puteaux Cedex
Tel.: +33 (1) 47 282 828
Fax.: +33 (1) 47 282 389

ITALY

TOSHIBA ELECTRONICS EUROPE GMBH, ITALY BRANCH

Via Torri Bianche, 6
Palazzo Tiglio - 5° piano
20871 Vimercate - MB
Tel.: +39 (039) 68701
Fax.: +39 (039) 6870205

UK

TOSHIBA ELECTRONICS EUROPE GMBH, UK BRANCH

Delta House, The Crescent,
Southwood Business Park,
Farnborough, Hampshire GU14 0NL
Tel: +44 (0870) 0602370
Fax: +44 (01252) 530250

SPAIN

TOSHIBA ELECTRONICS EUROPE GMBH, SPAIN BRANCH

Parque Empresarial, San Fernando, Edificio
Europa, 1ª Planta, E-28831 Madrid
Tel.: +34 (91) 660 6798
Fax.: +34 (91) 660 6799

SWEDEN

TOSHIBA ELECTRONICS EUROPE GMBH, SWEDEN BRANCH

Gustavslundsvägen 18, 5th Floor,
S-167 15 Bromma
Tel.: +46 (08) 704 0900
Fax.: +46 (08) 80 8459

MIPI® is a registered trademark of the MIPI Alliance Group
MDDI® is a trademark of the Video Electronics Standards Association (VESA)

The Toshiba products listed on this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic applications etc.). These Toshiba products are neither intended nor warranted for usage in equipment that requires extraordinary high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury („Unintended Usage“). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices etc. Unintended Usage of Toshiba products listed in this document shall be made at the customer's risk. The products described in this document may include products subject to the foreign exchange and foreign trade laws.

The information contained in this document is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent right of TOSHIBA or others.

Copyright and published by Toshiba Electronics Europe GmbH, Hansaallee 181, 40546 Düsseldorf, Handelsregister Düsseldorf HRB 22487, Geschäftsführ Horoshi Otsuka, Amtsgericht Düsseldorf

Product or company names mentioned here are Trademarks of their respective owners. The information contained here is subject to change without notice.

Document Number: TEE/E:12:002