

AZ943

15 AMP MINIATURE PC BOARD RELAY

FEATURES

- High performance
- Low seated height
- Flux tight and sealed versions available
- Class B insulation (130°C) standard
- Class F insulation (155°C) available
- UL, CUR file E43203
- TÜV file R50161256

CONTACTS

Arrangement	SPST (1 Form A) SPDT (1 Form C)
Ratings	Form A and C Max. switched power: 210 W or 2770 VA Max. switched current: 15 A AC, 7 A DC Max. switched voltage: 30 VDC or 300 VAC
UL/CUR	1 Form A 15 A at 125 VAC, general use 10A at 277 VAC, general use, 100,000 cycles TV - 5 120 VAC 1/2 HP at 125 VAC 125 VA at 120 VAC Pilot Duty, 100k cycles (N.O.) 8A at 125 VAC, 1000W (N.O.) Tungsten
TÜV	1 Form C 10 A at 277 VAC, general use, 100,000 cycles 1/2 HP at 125 VAC N.O. 125 VA at 120 VAC Pilot Duty, 100k cycles (N.O.) 10 A/7A N.O./N.C. at 30 VDC resistive
	1 Form A 10 A at 277 VAC, resistive, 70k cycles
	1 Form C 5 A at 250 VAC, resistive, 100k cycles 8 A at 250 VAC, resistive, 50k cycles 12 A at 125 VAC, resistive, 100k cycles
Material	Silver tin oxide (gold plating available not TÜV approved)
Resistance	< 100 milliohms initially (24 V, 1 A method)

COIL

Power	
At Pickup Voltage	203 mW
Max Continuous Dissipation	1.8 W at 20°C (68°F) Class B 2.4 W at 20°C (68°F) Class F
Temperature Rise	32°C (58°F) at nominal coil voltage
Temperature	Max. 130°C (266°F) Class B Max. 155°C (311°F) Class F



GENERAL DATA

Life Expectancy Mechanical Electrical	1 x 10 ⁷ 1 x 10 ⁵ at 10 A 277 VAC Res.
Operate Time	10 ms max.
Release Time	5 ms max. (with no coil suppression)
Dielectric Strength (at sea level for 1 min.)	1500 Vrms contact to coil 1000 Vrms across contacts
Insulation Resistance	100 megohms min. at 500 VDC, 50% RH
Dropout	Greater than 10% of nominal coil voltage
Ambient Temperature Operating Storage	At nominal coil voltage -40°C(-40°F) to 90°C(194°F) Class B -40°C(-40°F) to 110°C(230°F) Class F -40°C(-40°F) to 130°C(266°F)
Vibration	0.062" DA at 10–55 Hz
Shock	10 g
Enclosure	P.B.T. polyester
Terminals	Tinned copper alloy, P.C.
Max. Solder Temp.	270°C (518°F)
Max. Solder Time	5 seconds
Max. Solvent Temp.	80°C (176°F)
Max. Immersion Time	30 seconds
Weight	10 g

NOTES

1. All values at 20°C (68°F).
2. Relay may pull in with less than "Must Operate" value.
3. Unsealed relays should not be dip cleaned.
4. Specifications subject to change without notice.



AMERICAN ZETTLER, INC.

www.azettler.com

75 COLUMBIA ALISO VIEJO, CA 92656 • PHONE: (949) 831-5000 FAX: (949) 831-8642 E-MAIL: SALES@AZETTLER.COM


AZ943

RELAY ORDERING DATA

STANDARD RELAYS				
COIL SPECIFICATIONS				ORDER NUMBER*
Nominal Coil VDC	Must Operate VDC	Max Continuous VDC	Coil Resistance $\pm 10\%$	
5	3.8	11.2	70	AZ943-1CH-5D
6	4.5	13.4	100	AZ943-1CH-6D
9	6.8	20.1	225	AZ943-1CH-9D
12	9.0	26.8	400	AZ943-1CH-12D
18	13.5	40.2	900	AZ943-1CH-18D
24	18.0	53.4	1,600	AZ943-1CH-24D
48	36.0	107.3	6,400	AZ943-1CH-48D

* Substitute "1AH" in place of "1CH" to indicate 1 Form A contact. Add suffix "E" for epoxy sealed versions. Add suffix "G" for gold plated contacts. To indicate Class F version, add suffix "F".

MECHANICAL DATA



Dimensions in inches with metric equivalents in parentheses. Tolerance: $\pm .010$ "



AMERICAN ZETTLER, INC.

www.azettler.com

75 COLUMBIA ALISO VIEJO, CA 92656 • PHONE: (949) 831-5000 FAX: (949) 831-8642 E-MAIL: SALES@AZETTLER.COM

8/13/09