

# DB222-B



1-port omni exposed dipole antenna, 158–166 MHz, 360° HPBW, fixed electrical tilt

- Broad response
- Weather resistant

**OBSOLETE**

This product was discontinued on: March 27, 2020

## General Specifications

Antenna Type	Omni
Band	Single band
Color	Silver
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radiator Material	Aluminum
RF Connector Interface	N Male
RF Connector Location	Bottom
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

## Dimensions

Length	3,225.8 mm   127 in
--------	---------------------

## Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	158 – 166 MHz
Polarization	Vertical

## Electrical Specifications

Frequency Band, MHz	158–166
---------------------	---------

# DB222-B

Gain, dBi	5.1
Beamwidth, Horizontal, degrees	360
Beamwidth, Vertical, degrees	36
Beam Tilt, degrees	0
VSWR   Return loss, dB	1.5   14.0
Input Power per Port, maximum, watts	500

## Mechanical Specifications

Wind Loading at Velocity, maximum	284.7 N @ 100 mph   64.0 lbf @ 100 mph
Wind Speed, maximum	201 km/h   124.896 mph

## Packaging and Weights

Net Weight, without mounting kit	7.2 kg   15.873 lb
----------------------------------	--------------------

## Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

DB365-OS	—	Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.
----------	---	---

## \* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
------------------	---

# DB365-OS

---

Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.

## General Specifications

<b>Application</b>	Outdoor
<b>Color</b>	Silver

## Dimensions

<b>Compatible Diameter, maximum</b>	88.9 mm   3.5 in
<b>Compatible Diameter, minimum</b>	33 mm   1.299 in

## Material Specifications

<b>Material Type</b>	Galvanized steel
----------------------	------------------

## Packaging and Weights

<b>Included</b>	Brackets   Hardware
<b>Packaging quantity</b>	2

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CE	Compliant with the relevant CE product directives
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

