

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		C2	REVISED PER ECO-12-007964	02MAY2012	KH	MS

- 1

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN, RAL 7032.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2





SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3

END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING.
- 4

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.
- 5

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 6


NOT CUMULATIVE TOLERANCE.



282822-3 AS SHOWN

7.6	30	6	2-282822-6
3.5	125	25	2-282822-5
	120	24	2-282822-4
	115	23	2-282822-3
	110	22	2-282822-2
	105	21	2-282822-1
	100	20	2-282822-0
	95	19	1-282822-9
	90	18	1-282822-8
	85	17	1-282822-7
	80	16	1-282822-6
	75	15	1-282822-5
	70	14	1-282822-4
	65	13	1-282822-3
	60	12	1-282822-2
	55	11	1-282822-1
	50	10	1-282822-0
	45	9	282822-9
	40	8	282822-8
	35	7	282822-7
	30	6	282822-6
	25	5	282822-5
	20	4	282822-4
	15	3	282822-3
	10	2	282822-2

DIM. B DIM. A N° POS. PART NUMBER



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2

1 PLC ±.2

2 PLC ±.25

3 PLC ±.25

4 PLC ±.25

ANGLES ±2

MATERIAL

FINISH

DWN E. ZANOLINI 20JUL2001

CHK D. BIEVENOUR 20JUL2001

APVD D. BIEVENOUR 20JUL2001

PRODUCT SPEC 108-20166

APPLICATION SPEC 114-20079

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

TERMINAL BLOCK HEADER ASSEMBLY
180 DEG OPEN ENDS, STACKING
5mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-282822

SCALE 3:1

SHEET 1 OF 1

REV C2