




THICK FILM CHIP RESISTORS

- Very high quality and stability
- Power rating at 70°C: CR0603 - 0.10W, CR0805 - 0.125W, CR1206 - 0.25W
- Three layer contacting process with nickel barrier prevents leaching and provides excellent solderability
- Tight tolerances of bottom electrode width
- Suitable for all types of soldering processes

Models CR0603/CR0805/CR1206

Bourns® Chip Resistors



Electrical Characteristics

Characteristic	Model CR0603	Model CR0805	Model CR1206
Power Rating @ 70°C	1/10W	1/8W	1/4W
Operating Temperature Range	-55°C to +125°C		
Derated to 0 Load at	+125°C		
Maximum Working Voltage	50V	150V	200V
Maximum Overload Voltage	100V	300V	400V
Resistance Range: 1%, E-96	10Ω-1MΩ		
Resistance Range: 5%, E-24 Zero Ohm Jumper <0.01Ω	1Ω-10MΩ		
Temperature Coefficient	Special value on request 1%: ±100ppm/°C 5%: ±200ppm/°C 1Ω-10Ω: -200ppm/°C to +500ppm/°C		

Chip Dimensions in Inches (millimeters)

Dimension	Model CR0603	Model CR0805	Model CR1206
L	0.063±0.004 (1.60±0.10)	0.079±0.006 (2.00±0.15)	0.126±0.006 (3.20±0.15)
W	0.031±0.004 (0.80±0.10)	0.049±0.004 (1.25±0.10)	0.063±0.006 (1.60±0.15)
H	0.018±0.004 (0.45±0.10)	0.020±0.004 (0.50±0.10)	0.024±0.004 (0.60±0.10)
l ₁	0.012±0.008 (0.30±0.20)	0.016±0.008 (0.40±0.20)	0.020±0.010 (0.50±0.25)
l ₂	0.012±0.008 (0.30±0.20)	0.016±0.008 (0.40±0.20)	0.020±0.010 (0.50±0.25)

Dimensional Drawings



- Paper tape on reel for automatic placement

Models CR0603/CR0805/CR1206

Bourns® Chip Resistors

Performance Characteristics (Tests According to MIL-STD-202, MIL-R-55342B, EIA RS-396)


Test	Procedure	Method	Specification	Deviation from Nominal	
				1%	5%
DC Resistance	—	MIL-STD-202 303 EIA RS-396 4.4	MIL-R-55342D 4.7.2	$F: \leq \pm 1\%$	$\leq \pm 5.0\%$
Thermal Shock	-40°C, 60 minutes; +125°C, 60 minutes	MIL-STD-202 107 EIA RS-396 4.5	MIL-R-55342D 4.7.3	$\leq \pm 0.5\% + 0.05\Omega$	$\leq \pm 1\% + 0.05\Omega$
Low Temperature Operation	-55°C, 1 hour off; 45 minutes on	MIL-R-55342D 4.7.4 EIA RS-396 4.6	MIL-R-55342D 4.7.4	$\leq \pm 0.5\% 0.05\Omega$	$\leq \pm 1.0\% + 0.05\Omega$
Short Time Overload	Rated Voltage x 2.5; 5 seconds CR0603: 100V max. CR0805: 300V max. CR1206: 400V max.	MIL-R-55342D 4.7.5 EIA RS-396 4.7	MIL-R-55342D 4.7.5	$\leq \pm 1\% + 0.05\Omega$	$\leq \pm 2.0\% + 0.05\Omega$
High Temperature Exposure	+125°C; 1000 hours	MIL-R-55342D 4.7.6 EIA RS-396 4.8	MIL-R-55342D 4.7.6	$\leq \pm 1.0\% + 0.05\Omega$	$\leq \pm 2.0\% + 0.1\Omega$
Resistance to Soldering Heat	260°C, 10 seconds	MIL-R-55342D 4.7.7	MIL-R-55342D 4.7.7	$\leq \pm 0.5\% + 0.05\Omega$	$\leq \pm 1.0\% + 0.05\Omega$
Moisture Resistance	90-98%RH; 10 cycles	MIL-STD-202 106D EIA RS-396 4.9	MIL-R-55342D 4.7.8	$\leq \pm 0.5\% + 0.05\Omega$	$\leq \pm 2.0\% + 0.05\Omega$
Load Life 1000 Hours	+70°C; 1.5 hours on, 0.5 hours off; 1000 hours	MIL-STD-202 108 Condition D EIA RS-396 4.12	MIL-R-55342D 4.7.10	$\leq \pm 1.0\% + 0.05\Omega$	$\leq \pm 3.0\% + 0.1\Omega$
Solderability	+235°C; 3 seconds	MIL-STD-202 208 EIA RS-396 4.11	MIL-R-55342D 4.7.11	$\geq 95\%$ of area covered	$\geq 95\%$ of area covered
Terminal Strength	Pull Test	MIL-R-55342D 4.7.12	MIL-R-55342D 4.7.12	$\geq 500\text{g}$	$\geq 500\text{g}$
Current Noise	Quan-Tech Model 315B	MIL-STD-202 308	MIL-R-55342D 6.6	$R \leq 1\text{k}\Omega$; max. $1\mu\text{V/V}$ $R \leq 10\text{k}\Omega$; max. $3\mu\text{V/V}$ $R \leq 100\text{k}\Omega$; max. $6\mu\text{V/V}$ $R \leq 1\text{M}\Omega$; max. $10\mu\text{V/V}$	$R \leq 1\text{k}\Omega$; max. $1\mu\text{V/V}$ $R \leq 10\text{k}\Omega$; max. $3\mu\text{V/V}$ $R \leq 100\text{k}\Omega$; max. $6\mu\text{V/V}$ $R \leq 2\text{M}\Omega$; max. $10\mu\text{V/V}$
Humidity, Steady State	+40°C; 90-95% RH, 1344 Hours	MIL-STD-202 103B Condition D	—	$\leq \pm 2.5\% + 0.05\Omega$	$\leq \pm 2.5\% + 0.05\Omega$
Salt Spray	96 hours	MIL-STD-202 101D Condition A	—	$\leq \pm 1.0\% + 0.2\Omega$	$\leq \pm 1.0\% + 0.1\Omega$
Vibration	10-2000 Hz, 6 hours	MIL-STD-202 201A	—	$\leq \pm 0.5\% + 0.1\Omega$	$\leq \pm 1.0\% + 0.1\Omega$
Voltage Coefficient	—	MIL-STD-202 309	—	$\leq 100\text{ppm/V}$	$\leq 100\text{ppm/V}$
Insulation Resistance	Test Potential 500V CR0603: 100V	MIL-STD-202 302 Condition B	—	$\geq 10^9\text{M}\Omega$	$\geq 10^9\text{M}\Omega$
Dielectric Withstanding Voltage	—	MIL-STD-202 301	—	$\geq 500\text{V}$ (CR1206, CR0805) $\geq 300\text{V}$ (CR0603)	
Drop Test	1m	MIL-STD-202 203B	—	$\leq \pm 0.5\% + 0.1\Omega$	$\leq \pm 1.0\% + 0.1\Omega$
Bending Test	5mm/90mm; 10 sec.	—	—	$\leq \pm 1\% + 0.05\Omega$	$\leq \pm 1.0\% + 0.05\Omega$

Specifications are subject to change without notice.

Models CR0603/CR0805/CR1206


Bourns® Chip Resistors

Packaging Dimensions (Conforms to EIA RS-481A)




Maximum 1mm thick
*Cumulative tolerance over 10 holes: ±0.2mm

Series	A	B
CR0603	1.9 ± 0.1	1.1 ± 0.1
CR0805	2.4 +0.2/-0.1	1.65 +0.2/-0.1
CR1206	3.5 ± 0.1	1.95 +0.1/-0.05



Marking on reel: Part number, quantity, resistance value and tolerance, date code.

Part Numbering System and Marking



Models CR0603/CR0805/CR1206

Bourns® Chip Resistors

CR0603
CR0805
CR1206



5% marking
Value = 10KΩ

CR0805
CR1206



1% marking
Value = 10KΩ

CR0603
EIA-96 Marking



1% marking
Value = 12.4KΩ

Marking Explanation

- 5% tolerance: 3 digits, first two digits are significant, third digit is number of zeros. Letter R is decimal point.
- 1% tolerance: 4 digits, first three digits are significant, fourth digit is number of zeros. Letter R is decimal point.
- 0603 1%: EIA-96 marking

EIA-96 Marking for CR0603, 1%

Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value
01	100	13	133	25	178	37	237	49	316	61	422	73	562	85	750
02	102	14	137	26	182	38	243	50	324	62	432	74	576	86	768
03	105	15	140	27	187	39	249	51	332	63	442	75	590	87	787
04	107	16	143	28	191	40	255	52	340	64	453	76	604	88	806
05	110	17	147	29	196	41	261	53	348	65	464	77	619	89	825
06	113	18	150	30	200	42	267	54	357	66	475	78	634	90	845
07	115	19	154	31	205	43	274	55	365	67	487	79	649	91	866
08	118	20	158	32	210	44	280	56	374	68	499	80	665	92	887
09	121	21	162	33	215	45	287	57	383	69	511	81	681	93	909
10	124	22	165	34	221	46	294	58	392	70	523	82	698	94	931
11	127	23	169	35	226	47	301	59	402	71	536	83	715	95	953
12	130	24	174	36	232	48	309	60	412	72	549	84	732	96	976

This table shows the first two digits for the three-digit EIA-96 part marking scheme. The third character is a letter multiplier:
S=10² R=10¹ A=10⁰ B=10¹ C=10² D=10³ E=10⁴ F=10⁵

Lab-Kit: CR1206-JW-LAB1 50 pcs. each: 1Ω - 10Ω: E12
1206 Style, ±5%, ±200ppm/°C, E24
1MΩ - 10MΩ: E12

Lab-Kit: CR0805-JW-LAB2 50 pcs. each: 24Ω - 1MΩ: E24
0805 Style, ±5%, ±200ppm/°C, E24
Jumper

Lab-Kit: CR1206-FX-LAB3 50 pcs. each: 10Ω - 1MΩ: E24
1206 Style, ±1%, ±100ppm/°C, E24
Jumper

Lab-Kit: CR1206-FX-LAB4 50 pcs. each: 10Ω - 1MΩ: E48
1206 Style, ±1%, ±100ppm/°C, E48
Every other value
Jumper

Lab-Kit: CR0805-FX-LAB5 50 pcs. each: 75Ω - 1MΩ: E24
0805 Style, ±1%, ±100ppm/°C, E24
Jumper

Lab-Kit: CR0603-JW-LAB6 50 pcs. each: 3.3Ω - 10Ω: E12
0603 Style, ±5%, ±200ppm/°C, E24
10Ω - 1MΩ: E24
Jumper