

# TPS799 200-mA, Low-Quiescent Current, Ultralow Noise, High-PSRR Low-Dropout Linear Regulator

## 1 Features

- 200-mA low-dropout regulator with EN
- Multiple output voltage versions available:
  - Fixed outputs of 1.2 V to 4.5 V
  - Adjustable outputs from 1.20 V to 6.5 V
- Inrush current protection with EN toggle
- Low  $I_Q$ : 40  $\mu$ A
- High PSRR:
  - 66 dB at 1 kHz
  - 51 dB at 10 kHz
- Stable with a low-ESR, 2- $\mu$ F typical output capacitance
- Excellent load and line transient response
- 2% overall accuracy (load, line, and temperature)
- Very low dropout: 100 mV
- Packages:
  - 5-bump, thin, 0.97-mm  $\times$  1.34-mm DSBGA
  - 5-pin SOT-23-THIN
  - 6-pin WSON

## 2 Applications

- [Base stations](#)
- [Smart phones](#)
- [EPOS](#)
- [Wearable electronics](#)
- [VCOs, RF](#)
- [Wireless LAN, Bluetooth®](#)

## 3 Description

The TPS799 low-dropout (LDO), low-power linear regulator offers excellent ac performance with very low ground current. High power-supply rejection ratio (PSRR), low noise, fast start-up, and excellent line and load transient response are provided while consuming a very low 40- $\mu$ A (typical) ground current.


The TPS799 is stable with ceramic capacitors and uses an advanced BiCMOS fabrication process to yield a dropout voltage of typically 100 mV at a 200-mA output. The TPS799 uses a precision voltage reference and feedback loop to achieve an overall accuracy of 2% over all load, line, process, and temperature variations. The TPS799 features inrush current protection when the EN toggle is used to start the device, immediately clamping the current.

This device is fully specified over the temperature range of  $T_J = -40^\circ\text{C}$  to  $+125^\circ\text{C}$ , and is offered in a low-profile, die-sized ball grid array (DSBGA) package, making this device a good choice for wireless handsets and WLAN cards. This device is also offered in 5-pin SOT-23-THIN and 6-pin WSON packages.


### Device Information<sup>(1)</sup>

| PART NUMBER | PACKAGE         | BODY SIZE (NOM)          |
|-------------|-----------------|--------------------------|
| TPS799      | SOT-23-THIN (5) | 2.90 mm $\times$ 1.60 mm |
|             | WSON (6)        | 2.00 $\times$ 2.00 mm    |
|             | DSBGA (5)       | 1.34 mm $\times$ 0.97 mm |

- (1) For all available packages, see the package option addendum at the end of the data sheet.



Typical Application Circuit: Fixed Voltage Versions



Typical Application Circuit: Adjustable Voltage Version



## Table of Contents

|                                                |           |                                                                  |           |
|------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                        | <b>1</b>  | 8.1 Application Information.....                                 | <b>13</b> |
| <b>2 Applications</b> .....                    | <b>1</b>  | 8.2 Typical Application.....                                     | <b>13</b> |
| <b>3 Description</b> .....                     | <b>1</b>  | 8.3 What To Do and What Not To Do.....                           | <b>15</b> |
| <b>4 Revision History</b> .....                | <b>2</b>  | <b>9 Power Supply Recommendations</b> .....                      | <b>15</b> |
| <b>5 Pin Configuration and Functions</b> ..... | <b>3</b>  | <b>10 Layout</b> .....                                           | <b>15</b> |
| <b>6 Specifications</b> .....                  | <b>4</b>  | 10.1 Layout Guidelines.....                                      | <b>15</b> |
| 6.1 Absolute Maximum Ratings.....              | <b>4</b>  | 10.2 Layout Example.....                                         | <b>16</b> |
| 6.2 ESD Ratings.....                           | <b>4</b>  | <b>11 Device and Documentation Support</b> .....                 | <b>17</b> |
| 6.3 Recommended Operating Conditions.....      | <b>4</b>  | 11.1 Device Support.....                                         | <b>17</b> |
| 6.4 Thermal Information.....                   | <b>4</b>  | 11.2 Documentation Support.....                                  | <b>17</b> |
| 6.5 Electrical Characteristics.....            | <b>5</b>  | 11.3 Receiving Notification of Documentation Updates..           | <b>17</b> |
| 6.6 Typical Characteristics.....               | <b>6</b>  | 11.4 Support Resources.....                                      | <b>17</b> |
| <b>7 Detailed Description</b> .....            | <b>11</b> | 11.5 Trademarks.....                                             | <b>18</b> |
| 7.1 Overview.....                              | <b>11</b> | 11.6 Electrostatic Discharge Caution.....                        | <b>18</b> |
| 7.2 Functional Block Diagrams.....             | <b>11</b> | 11.7 Glossary.....                                               | <b>18</b> |
| 7.3 Feature Description.....                   | <b>12</b> | <b>12 Mechanical, Packaging, and Orderable Information</b> ..... | <b>18</b> |
| 7.4 Device Functional Modes.....               | <b>12</b> |                                                                  |           |
| <b>8 Application and Implementation</b> .....  | <b>13</b> |                                                                  |           |


## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.


| <b>Changes from Revision K (January 2015) to Revision L (September 2021)</b>                                                                  | <b>Page</b> |
|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • Added PSRR value at 10 kHz to <i>Features</i> bullet.....                                                                                   | <b>1</b>    |
| • Added missing packages to <i>Features</i> bullet.....                                                                                       | <b>1</b>    |
| • Changed SOT to SOT-23-THIN and SON to WSON throughout document.....                                                                         | <b>1</b>    |
| • Changed <i>Applications</i> bullets.....                                                                                                    | <b>1</b>    |
| • Changed body size for DSBGA package in <i>Device Information</i> table.....                                                                 | <b>1</b>    |
| • Changed YZY package to YZU in <i>Pin Functions</i> table (typo).....                                                                        | <b>3</b>    |
| • Added note (1) to <i>Recommended Operating Conditions</i> ; moved from <i>Electrical Characteristics</i> .....                              | <b>4</b>    |
| • Deleted <i>Input Voltage</i> from <i>Electrical Characteristics</i> ; already shown in <i>Recommended Operating Conditions</i> .....        | <b>5</b>    |
| • Deleted <i>Junction Temperature</i> from <i>Electrical Characteristics</i> ; already shown in <i>Recommended Operating Conditions</i> ..... | <b>5</b>    |
| • Changed <i>Do's and Don'ts</i> title to <i>What To Do and What Not To Do</i> .....                                                          | <b>15</b>   |

| <b>Changes from Revision J (August 2010) to Revision K (January 2015)</b>                                                                                                                                                                                                                                                                            | <b>Page</b> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • Added <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | <b>1</b>    |
| • Changed <i>Features</i> list .....                                                                                                                                                                                                                                                                                                                 | <b>1</b>    |
| • Changed <i>Description</i> section.....                                                                                                                                                                                                                                                                                                            | <b>1</b>    |
| • Changed figure on front page; replaced device pinouts with application circuits.....                                                                                                                                                                                                                                                               | <b>1</b>    |
| • Changed Pin Configuration and Functions section; updated table format, renamed pin packages.....                                                                                                                                                                                                                                                   | <b>3</b>    |
| • Changed "free-air" to "junction" temperature in condition statement for <i>Absolute Maximum Ratings</i> .....                                                                                                                                                                                                                                      | <b>4</b>    |
| • Changed <i>free-air</i> to <i>junction</i> in <i>Recommended Operating Conditions</i> table conditions.....                                                                                                                                                                                                                                        | <b>4</b>    |
| • Added thermal information for additional device packages .....                                                                                                                                                                                                                                                                                     | <b>4</b>    |


## 5 Pin Configuration and Functions




**Figure 5-1. DDC Package (Fixed), 5-Pin SOT-23-THIN (Top View)**




**Figure 5-2. DDC Package (Adjustable), 5-Pin SOT-23-THIN (Top View)**




**Figure 5-3. YZU Package (Fixed), 5-Pin DSBGA (Top View)**



**Figure 5-4. YZU Package (Adjustable), 5-Pin DSBGA (Top View)**



**Figure 5-5. DRV Package (Fixed), 6-Pin WSON With Exposed Thermal Pad (Top View)**



**Figure 5-6. DRV Package (Adjustable), 6-Pin WSON With Exposed Thermal Pad (Top View)**

**Table 5-1. Pin Functions**

| NAME | PIN |     |        | I/O | DESCRIPTION                                                                                                                                                                                                        |
|------|-----|-----|--------|-----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|      | DDC | YZU | DRV    |     |                                                                                                                                                                                                                    |
| IN   | 1   | C3  | 6      | I   | Input supply.                                                                                                                                                                                                      |
| GND  | 2   | B2  | 3, Pad | —   | Ground. The pad must be tied to GND.                                                                                                                                                                               |
| EN   | 3   | A1  | 4      | I   | Driving this pin high turns on the regulator. Driving this pin low puts the regulator into shutdown mode. EN can be connected to IN if not used.                                                                   |
| NR   | 4   | A3  | 2      | —   | Fixed voltage versions only. Noise reduction; connecting this pin to an external capacitor bypasses noise generated by the internal band gap. This capacitor allows output noise to be reduced to very low levels. |
| FB   | 4   | A3  | 2      | I   | Adjustable voltage version only. Feedback; this pin is the input to the control loop error amplifier, and sets the output voltage of the device.                                                                   |
| OUT  | 5   | C1  | 1      | O   | Output of the regulator. To assure stability, a small ceramic capacitor (total typical capacitance $\geq 2 \mu\text{F}$ ) is required from this pin to ground.                                                     |
| N/C  | —   | —   | 5      | —   | Not internally connected. This pin must either be left open, or tied to GND.                                                                                                                                       |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating junction temperature range (unless otherwise noted) <sup>(1)</sup>

|                        |                                   | MIN                | MAX            | UNIT |
|------------------------|-----------------------------------|--------------------|----------------|------|
| Voltage <sup>(2)</sup> | IN                                | −0.3               | 7.0            | V    |
|                        | EN                                | −0.3               | $V_{IN} + 0.3$ | V    |
|                        | OUT                               | −0.3               | $V_{IN} + 0.3$ | V    |
| Current                | OUT                               | Internally limited |                | mA   |
| Temperature            | Operating virtual junction, $T_J$ | −55                | 150            | °C   |
|                        | Storage, $T_{stg}$                | −55                | 150            | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- (2) All voltages are with respect to network ground terminal.

### 6.2 ESD Ratings

|             |                         |                                                                                          | VALUE | UNIT |
|-------------|-------------------------|------------------------------------------------------------------------------------------|-------|------|
| $V_{(ESD)}$ | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>              | ±2000 | V    |
|             |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> | ±500  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

over operating junction temperature range (unless otherwise noted)

|           |                                | MIN | NOM | MAX | UNIT |
|-----------|--------------------------------|-----|-----|-----|------|
| $V_{IN}$  | Input voltage <sup>(1)</sup>   | 2.7 |     | 6.5 | V    |
| $I_{OUT}$ | Output current                 | 0.5 |     | 200 | mA   |
| $T_J$     | Operating junction temperature | −40 |     | 125 | °C   |

- (1) Minimum  $V_{IN} = V_{OUT} + V_{DO}$  or 2.7 V, whichever is greater.

### 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | TPS799               |               |                | UNIT |
|-------------------------------|----------------------------------------------|----------------------|---------------|----------------|------|
|                               |                                              | DDC<br>(SOT-23-THIN) | DRV<br>(WSON) | YZU<br>(DSBGA) |      |
|                               |                                              | 5 PINS               | 6 PINS        | 5 PINS         |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 225.3                | 74.2          | 143.3          | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 39.3                 | 58.8          | 1.1            | °C/W |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 47.3                 | 145.9         | 84.7           | °C/W |
| $\Psi_{JT}$                   | Junction-to-top characterization parameter   | 0.5                  | 0.2           | 3.8            | °C/W |
| $\Psi_{JB}$                   | Junction-to-board characterization parameter | 46.7                 | 54.4          | 84.4           | °C/W |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | N/A                  | 7.2           | N/A            | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics application report](#).

## 6.5 Electrical Characteristics

at  $T_J = -40^\circ\text{C}$  to  $+125^\circ\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^\circ\text{C}$

| PARAMETER                |                                                                           | TEST CONDITIONS                                                                                                                |                                                                      | MIN      | TYP                   | MAX            | UNIT                |
|--------------------------|---------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------|----------|-----------------------|----------------|---------------------|
| $V_{FB}$                 | Internal reference (TPS79901)                                             |                                                                                                                                |                                                                      | 1.169    | 1.193                 | 1.217          | V                   |
| $V_{OUT}$                | Output voltage range (TPS79901)                                           |                                                                                                                                |                                                                      | $V_{FB}$ |                       | $6.5 - V_{DO}$ | V                   |
|                          | Output accuracy, nominal                                                  | $T_J = 25^\circ\text{C}$                                                                                                       |                                                                      | -1%      |                       | 1%             |                     |
|                          | Output accuracy <sup>(1)</sup> over $V_{IN}$ , $I_{OUT}$ , temperature    | $V_{OUT} + 0.3\text{ V} \leq V_{IN} \leq 6.5\text{ V}$<br>$500\text{ }\mu\text{A} \leq I_{OUT} \leq 200\text{ mA}$             |                                                                      | -2%      | $\pm 1\%$             | 2%             |                     |
| $\Delta V_{O(\Delta V)}$ | Line regulation <sup>(1)</sup>                                            | $V_{OUT(nom)} + 0.3\text{ V} \leq V_{IN} \leq 6.5\text{ V}$                                                                    |                                                                      |          | 0.02                  |                | %/V                 |
| $\Delta V_{O(\Delta I)}$ | Load regulation                                                           | $500\text{ }\mu\text{A} \leq I_{OUT} \leq 200\text{ mA}$                                                                       |                                                                      |          | 0.002                 |                | %/mA                |
| $V_{DO}$                 | Dropout voltage <sup>(1)</sup> ( $V_{IN} = V_{OUT(nom)} - 0.1\text{ V}$ ) | $I_{OUT} = 200\text{ mA}$                                                                                                      | $V_{OUT(nom)} \leq 3.3\text{ V}$<br>$V_{OUT(nom)} \geq 3.3\text{ V}$ |          | 100<br>90             | 175<br>160     | mV                  |
| $I_{CL}$                 | Output current limit                                                      | $V_{OUT} = 0.9 \times V_{OUT(nom)}$                                                                                            |                                                                      | 220      | 400                   | 600            | mA                  |
| $I_{GND}$                | Ground pin current                                                        | $500\text{ }\mu\text{A} \leq I_{OUT} \leq 200\text{ mA}$                                                                       |                                                                      |          | 40                    | 60             | $\mu\text{A}$       |
| $I_{SHDN}$               | Shutdown current ( $I_{GND}$ )                                            | $V_{EN} \leq 0.4\text{ V}$ , $2.7\text{ V} \leq V_{IN} \leq 6.5\text{ V}$                                                      |                                                                      |          | 0.15                  | 1              | $\mu\text{A}$       |
| $I_{FB}$                 | Feedback pin current (TPS79901)                                           |                                                                                                                                |                                                                      | -0.5     |                       | 0.5            | $\mu\text{A}$       |
| PSRR                     | Power-supply rejection ratio                                              | $V_{IN} = 3.85\text{ V}$ ,<br>$V_{OUT} = 2.85\text{ V}$ ,<br>$C_{NR} = 0.01\text{ }\mu\text{F}$ ,<br>$I_{OUT} = 100\text{ mA}$ | $f = 100\text{ Hz}$                                                  |          | 70                    |                | dB                  |
|                          |                                                                           |                                                                                                                                | $f = 1\text{ kHz}$                                                   |          | 66                    |                |                     |
|                          |                                                                           |                                                                                                                                | $f = 10\text{ kHz}$                                                  |          | 51                    |                |                     |
|                          |                                                                           |                                                                                                                                | $f = 100\text{ kHz}$                                                 |          | 38                    |                |                     |
| $V_n$                    | Output noise voltage                                                      | $BW = 10\text{ Hz to }100\text{ kHz}$ ,<br>$V_{OUT} = 2.85\text{ V}$                                                           | $C_{NR} = 0.01\text{ }\mu\text{F}$                                   |          | $10.5 \times V_{OUT}$ |                | $\mu\text{V}_{RMS}$ |
|                          |                                                                           |                                                                                                                                | $C_{NR} = \text{none}$                                               |          | $94 \times V_{OUT}$   |                |                     |
|                          | Start-up time                                                             | $V_{OUT} = 2.85\text{ V}$ ,<br>$R_L = 14\text{ }\Omega$ ,<br>$C_{OUT} = 2.2\text{ }\mu\text{F}$                                | $C_{NR} = 0.001\text{ }\mu\text{F}$                                  |          | 45                    |                | $\mu\text{s}$       |
|                          |                                                                           |                                                                                                                                | $C_{NR} = 0.047\text{ }\mu\text{F}$                                  |          | 45                    |                |                     |
|                          |                                                                           |                                                                                                                                | $C_{NR} = 0.01\text{ }\mu\text{F}$                                   |          | 50                    |                |                     |
|                          |                                                                           |                                                                                                                                | $C_{NR} = \text{none}$                                               |          | 50                    |                |                     |
| $V_{EN(HI)}$             | Enable high (enabled)                                                     |                                                                                                                                |                                                                      | 1.2      |                       | $V_{IN}$       | V                   |
| $V_{EN(LO)}$             | Enable low (shutdown)                                                     |                                                                                                                                |                                                                      | 0        |                       | 0.4            | V                   |
| $I_{EN(HI)}$             | Enable pin current, enabled                                               | $V_{EN} = V_{IN} = 6.5\text{ V}$                                                                                               |                                                                      |          | 0.03                  | 1              | $\mu\text{A}$       |
| UVLO                     | Undervoltage lockout                                                      | $V_{IN}$ rising                                                                                                                |                                                                      | 1.90     | 2.20                  | 2.65           | V                   |
|                          | UVLO hysteresis                                                           | $V_{IN}$ falling                                                                                                               |                                                                      |          | 70                    |                | mV                  |
| $T_{sd}$                 | Thermal shutdown temperature                                              | Shutdown, temperature increasing                                                                                               |                                                                      |          | 165                   |                | $^\circ\text{C}$    |
|                          |                                                                           | Reset, temperature decreasing                                                                                                  |                                                                      |          | 145                   |                |                     |

(1)  $V_{DO}$  is not measured for devices with  $V_{OUT(nom)} < 2.8\text{ V}$  because minimum  $V_{IN} = 2.7\text{ V}$ .

## 6.6 Typical Characteristics

at  $T_J = -40^\circ\text{C}$  to  $+125^\circ\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^\circ\text{C}$




Figure 6-1. Load Regulation




Figure 6-2. Line Regulation




Figure 6-3. Output Voltage vs Junction Temperature




Figure 6-4. TPS799285 Dropout Voltage vs Output Current




Figure 6-5. TPS799285 Dropout Voltage vs Junction Temperature






Figure 6-6. TPS79901 Dropout vs Input Voltage

## 6.6 Typical Characteristics (continued)


at  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^{\circ}\text{C}$




**Figure 6-7. Ground Pin Current vs Input Voltage**




**Figure 6-8. TPS799285 Ground Pin Current vs Junction Temperature**




**Figure 6-9. Ground Pin Current (Disabled) vs Junction Temperature**



**Figure 6-10. TPS799285 Power-Supply Ripple Rejection vs Frequency**




**Figure 6-11. TPS799285 Power-Supply Ripple Rejection vs Frequency**




**Figure 6-12. TPS799285 Power-Supply Ripple Rejection vs Frequency**

## 6.6 Typical Characteristics (continued)


at  $T_J = -40^\circ\text{C}$  to  $+125^\circ\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^\circ\text{C}$




**Figure 6-13. TPS799285 Power-Supply Ripple Rejection vs Frequency**




**Figure 6-14. TPS799285 Power-Supply Ripple Rejection vs Frequency**




**Figure 6-15. TPS799285 Power-Supply Ripple Rejection vs Frequency**



**Figure 6-16. Power-Supply Ripple Rejection vs  $V_{IN} - V_{OUT}$**




**Figure 6-17. Power-Supply Ripple Rejection vs  $V_{IN} - V_{OUT}$**




**Figure 6-18. Power-Supply Ripple Rejection vs  $V_{IN} - V_{OUT}$**

## 6.6 Typical Characteristics (continued)


at  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^{\circ}\text{C}$




**Figure 6-19. TPS799285 Total Noise vs  $C_{NR}$**




**Figure 6-20. TPS799285 Total Noise vs  $C_{OUT}$**




**Figure 6-21. TPS799285 Line Transient Response**



**Figure 6-22. TPS799285 Load Transient Response**




**Figure 6-23. TPS799285 Turn-On Response**



**Figure 6-24. TPS799285 Enable Response**

## 6.6 Typical Characteristics (continued)

at  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $V_{IN} = V_{OUT(nom)} + 0.3\text{ V}$  or  $2.7\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 2.2\text{ }\mu\text{F}$ , and  $C_{NR} = 0.01\text{ }\mu\text{F}$  (unless otherwise noted); for TPS79901,  $V_{OUT} = 3.0\text{ V}$ ; typical values are at  $T_J = 25^{\circ}\text{C}$



**Figure 6-25. TPS799285 Power-Up and Power-Down**


## 7 Detailed Description

### 7.1 Overview


The TPS799 low-dropout (LDO) regulator combines the high performance required of many RF and precision analog applications with ultra-low current consumption. High PSRR is provided by a high-gain, high-bandwidth error loop with good supply rejection at very low headroom ( $V_{IN} - V_{OUT}$ ). A noise-reduction pin is provided to bypass noise generated by the band-gap reference and to improve PSRR, while a quick-start circuit quickly charges this capacitor at start-up. The combination of high performance and low ground current also make this device an excellent choice for portable applications. This device has thermal and overcurrent protection, and is fully specified from  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ .

The TPS799 also features inrush current protection with an EN toggle start-up, and overshoot detection at the output. When the EN toggle is used to start the device, current limit protection is immediately activated, restricting the inrush current to the device. If voltage at the output overshoots 5% from the nominal value, a pulldown resistor reduces the voltage to normal operating conditions, as shown in the [Functional Block Diagrams](#).

### 7.2 Functional Block Diagrams



**Figure 7-1. Fixed-Voltage Versions**



**Figure 7-2. Adjustable-Voltage Versions**

## 7.3 Feature Description

### 7.3.1 Internal Current Limit

The TPS799 internal current limit helps protect the regulator during fault conditions. In current limit mode, the output sources a fixed amount of current that is largely independent of the output voltage. For reliable operation, do not operate the device in a current-limit state for extended periods of time.

The PMOS pass element in the TPS799 has a built-in body diode that conducts current when the voltage at OUT exceeds the voltage at IN. This current is not limited; therefore, if extended reverse voltage operation is anticipated, external limiting may be required.

### 7.3.2 Shutdown

The enable pin (EN) is active high and is compatible with standard and low-voltage TTL-CMOS levels. When shutdown capability is not required, EN can be connected to IN.

### 7.3.3 Start Up

The TPS799 uses a start-up circuit to quickly charge the noise reduction capacitor,  $C_{NR}$ , if present (see the [Functional Block Diagrams](#)). This circuit allows for the combination of very low output noise and fast start-up times. The NR pin is high impedance so a low leakage  $C_{NR}$  capacitor must be used; most ceramic capacitors are appropriate for this configuration.

For fastest start-up, apply  $V_{IN}$  first, and then drive the enable pin (EN) high. If EN is tied to IN, start up is somewhat slower. The start-up switch is closed for approximately 135  $\mu$ s. To ensure that  $C_{NR}$  is fully charged during start-up, use a 0.01- $\mu$ F or smaller capacitor.

### 7.3.4 Undervoltage Lockout (UVLO)

The TPS799 uses an undervoltage lockout circuit to keep the output shut off until internal circuitry is operating properly. The UVLO circuit has a deglitch feature so that undershoot transients are typically ignored on the input if these transients are less than 50  $\mu$ s in duration.

## 7.4 Device Functional Modes

Driving EN over 1.2 V turns on the regulator. Driving EN below 0.4 V puts the regulator into shutdown mode, thus reducing the operating current to 150 nA, nominal.

## 8 Application and Implementation

### Note


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 8.1 Application Information


The TPS799 LDO regulator provides high PSRR while maintaining ultra-low current consumption. The device also features inrush current protection and overshoot detection at the output.

### 8.2 Typical Application

Figure 8-1 and Figure 8-2 show the basic circuit connections.



**Figure 8-1. Typical Application Circuit for Fixed Voltage Versions**



**Figure 8-2. Typical Application Circuit for Adjustable Voltage Version**

#### 8.2.1 Design Requirements

Select the desired device based on the output voltage.

Provide an input supply with adequate headroom to account for dropout and output current to account for the GND terminal current, and power the load.

## 8.2.2 Detailed Design Procedure

### 8.2.2.1 Input and Output Capacitor Requirements

Although an input capacitor is not required for stability, good analog design practice is to connect a 0.1-μF to 1-μF low ESR capacitor across the input supply near the regulator. This capacitor counteracts reactive input sources and improves transient response, noise rejection, and ripple rejection. A higher-value capacitor may be necessary if large, fast rise-time load transients are anticipated, or if the device is located several inches from the power source. If source impedance is not sufficiently low, a 0.1-μF input capacitor may be necessary to ensure stability.

The TPS799 is designed to be stable with standard ceramic capacitors with values of 2.2 μF or greater. X5R- and X7R-type capacitors are best because they have minimal variation in value and ESR over temperature. Maximum ESR must be less than 1.0 Ω.

#### 8.2.2.2 Output Noise

In most LDOs, the band gap is the dominant noise source. If a noise-reduction capacitor ( $C_{NR}$ ) is used with the TPS799, the band gap does not contribute significantly to noise. Instead, noise is dominated by the output resistor divider and the error amplifier input. To minimize noise in a given application, use a 0.01-μF noise reduction capacitor. To further optimize noise, equivalent series resistance of the output capacitor can be set to approximately 0.2 Ω. This configuration maximizes phase margin in the control loop, reducing total output noise by up to 10%.

Noise can be referred to the feedback point; with  $C_{NR} = 0.01 \mu\text{F}$  total noise is approximately given by [Equation 1](#):

$$V_N = \frac{10.5 \mu\text{V}_{\text{RMS}}}{V} \times V_{\text{OUT}} \quad (1)$$

#### 8.2.2.3 Dropout Voltage

The TPS799 uses a PMOS pass transistor to achieve a low dropout voltage. When  $(V_{\text{IN}} - V_{\text{OUT}})$  is less than the dropout voltage ( $V_{\text{DO}}$ ), the PMOS pass device is in its linear region of operation and  $r_{\text{DS(on)}}$  of the PMOS pass element is the input-to-output resistance. Because the PMOS device behaves like a resistor in dropout,  $V_{\text{DO}}$  approximately scales with the output current.

As with any linear regulator, PSRR degrades as  $(V_{\text{IN}} - V_{\text{OUT}})$  approaches dropout. This effect is illustrated in [Figure 6-10](#) through [Figure 6-18](#) in the [Typical Characteristics](#) section.

#### 8.2.2.4 Transient Response

As with any regulator, increasing the size of the output capacitor reduces over- and undershoot magnitude, but increases the duration of the transient response. The transient response of the TPS799 is enhanced by an active pulldown device that engages when the output overshoots by approximately 5% or more when the device is enabled. When enabled, the pulldown device behaves like a 350-Ω resistor to ground.

#### 8.2.2.5 Minimum Load


The TPS799 is stable with no output load. To meet the specified accuracy, a minimum load of 500 μA is required. With loads less than 500 μA at junction temperatures near 125°C, the output can drift up enough to cause the output pulldown device to turn on. The output pulldown device limits voltage drift to 5% typically; however, ground current can increase by approximately 50 μA. In typical applications, the junction cannot reach high temperatures at light loads because there is no noticeable dissipated power. The specified ground current is then valid at no load in most applications.

#### 8.2.2.6 Feedback Capacitor Requirements (TPS79901 Only)

The feedback capacitor,  $C_{\text{FB}}$ , shown in [Figure 8-2](#) is required for stability. For a parallel combination of  $R_1$  and  $R_2$  equal to 250 kΩ, any value from 3 pF to 1 nF can be used. Fixed voltage versions have an internal 30-pF feedback capacitor that is quick-charged at start up. The adjustable version does not have this quick-charge circuit, so use values below 5 pF to ensure fast start up; values above 47 pF can be used to implement an output

voltage soft-start. Larger value capacitors also improve noise slightly. The TPS79901 is stable in unity-gain configuration (OUT tied to FB) without  $C_{FB}$ .

### 8.2.3 Application Curve



**Figure 8-3. Power-Supply Rejection Ratio vs Frequency**

## 8.3 What To Do and What Not To Do

Do place at least one 2.2-μF ceramic capacitor as close as possible to the OUT pin of the regulator.

Do not place the output capacitor more than 10 mm away from the regulator.

Do connect a 0.1-μF to 1-μF low equivalent series resistance (ESR) capacitor across the IN pin and GND input of the regulator.

Do not exceed the absolute maximum ratings.

## 9 Power Supply Recommendations

These devices are designed to operate from an input voltage supply range between 2.7 V and 6.5 V. The input voltage range provides adequate headroom in order for the device to have a regulated output. This input supply is well-regulated and stable. If the input supply is noisy, additional input capacitors with low ESR can help improve the output noise performance.

## 10 Layout

### 10.1 Layout Guidelines

#### 10.1.1 Board Layout Recommendations to Improve PSRR and Noise Performance

To improve ac performance (such as PSRR, output noise, and transient response), design the board with separate ground planes for  $V_{IN}$  and  $V_{OUT}$ , with each ground plane connected only at the GND pin of the device. In addition, connect the bypass capacitor directly to the GND pin of the device.

#### 10.1.2 Thermal Information

##### 10.1.2.1 Thermal Protection

Thermal protection disables the output when the junction temperature rises to approximately 165°C, allowing the device to cool. When the junction temperature cools to approximately 145°C the output circuitry is again enabled. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit may cycle on and off. This cycling limits the dissipation of the regulator, protecting it from damage resulting from overheating.

Any tendency to activate the thermal protection circuit indicates excessive power dissipation or an inadequate heat sink. For reliable operation, limit junction temperature to 125°C maximum. To estimate the margin of safety in a complete design (including heat sink), increase the ambient temperature until the thermal protection is triggered; use worst-case loads and signal conditions. For good reliability, thermal protection triggers at least

35°C above the maximum expected ambient condition of a particular application. This configuration produces a worst-case junction temperature of 125°C at the highest expected ambient temperature and worst-case load.

The internal protection circuitry of the TPS799 is designed to protect against overload conditions. This circuitry is not intended to replace proper heat sinking. Continuously running the device into thermal shutdown degrades device reliability.

#### 10.1.2.2 Power Dissipation

The ability to remove heat from the die is different for each package type, presenting different considerations in the PCB layout. The PCB area around the device that is free of other components moves the heat from the device to the ambient air. Performance data for JEDEC low- and high-K boards are given in the [Thermal Information](#) table near the front of this data sheet. Using heavier copper increases the effectiveness in removing heat from the device. The addition of plated through-holes to heat-dissipating layers also improves heat-sink effectiveness.


Power dissipation depends on input voltage and load conditions. Power dissipation is equal to the product of the output current times the voltage drop across the output pass element, as shown in [Equation 2](#):

$$P_D = (V_{IN} - V_{OUT}) \cdot I_{OUT} \quad (2)$$

#### 10.1.2.3 Package Mounting

Solder pad footprint recommendations for the TPS799 are available from the TI's website at [www.ti.com](http://www.ti.com).

### 10.2 Layout Example



**Figure 10-1. Layout Example**

## 11 Device and Documentation Support

### 11.1 Device Support

#### 11.1.1 Development Support

##### 11.1.1.1 Evaluation Modules

An evaluation module (EVM) is available to assist in the initial circuit performance evaluation using the TPS799. This EVM, the TPS799 evaluation module, can be requested at the Texas Instruments web site through the product folders or purchased [directly from the TI eStore](#).

##### 11.1.1.2 Spice Models

Computer simulation of circuit performance using SPICE is often useful when analyzing the performance of analog circuits and systems. A SPICE model for the TPS799 is available through the product folders under simulation models.

#### 11.1.2 Device Nomenclature

**Table 11-1. Device Nomenclature<sup>(1)</sup>**

| PRODUCT           | V <sub>OUT</sub>                                                                                                                                  |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| TPS799xx(x) yyy z | xx(x) is nominal output voltage (for example, 28 = 2.8 V, 285 = 2.85 V, 01 = Adjustable).<br>yyy is package designator.<br>z is package quantity. |

(1) For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder at [www.ti.com](http://www.ti.com).

### 11.2 Documentation Support

#### 11.2.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [Using New Thermal Metrics application report](#)
- Texas Instruments, [Semiconductor and IC Package Thermal Metrics application report](#)
- Texas Instruments, [TPS799xxEVM-105 user's guide](#)

#### 11.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](http://ti.com). Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 11.4 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

## 11.5 Trademarks

TI E2E™ is a trademark of Texas Instruments.

Bluetooth® is a registered trademark of Bluetooth SIG, Inc.

All trademarks are the property of their respective owners.

## 11.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 11.7 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS79901DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCR1G4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCR1G4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCRG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79901DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DDCTG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79901DRVR</a>  | Active        | Production           | WSO (DRV)   6         | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DRVR.B                | Active        | Production           | WSO (DRV)   6         | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DRVRG4                | Active        | Production           | WSO (DRV)   6         | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| <a href="#">TPS79901DRV</a>   | Active        | Production           | WSO (DRV)   6         | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| TPS79901DRV.B                 | Active        | Production           | WSO (DRV)   6         | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWT                 |
| <a href="#">TPS79901YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E9                  |
| TPS79901YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E9                  |
| <a href="#">TPS79901YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E9                  |
| TPS79901YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | E9                  |
| <a href="#">TPS799125YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | YZ                  |
| TPS799125YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | YZ                  |
| <a href="#">TPS799125YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | YZ                  |
| TPS799125YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | YZ                  |
| <a href="#">TPS79912DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS79912DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| <a href="#">TPS79912DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| TPS79912DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| <a href="#">TPS79912DRV.R</a> | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| TPS79912DRV.R.B               | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| <a href="#">TPS79912DRV.T</a> | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| TPS79912DRV.T.B               | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| TPS79912DRV.TG4               | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CCF                 |
| <a href="#">TPS79912YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F8                  |
| TPS79912YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F8                  |
| <a href="#">TPS79912YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F8                  |
| TPS79912YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F8                  |
| <a href="#">TPS79913DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BUJ                 |
| TPS79913DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BUJ                 |
| <a href="#">TPS79913DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BUJ                 |
| TPS79913DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BUJ                 |
| <a href="#">TPS79913YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F9                  |
| TPS79913YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F9                  |
| <a href="#">TPS79915DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |
| TPS79915DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |
| TPS79915DDCRG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |
| TPS79915DDCRG4.B              | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS79915DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |
| TPS79915DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWU                 |
| TPS79915DDCTG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79915YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EA                  |
| TPS79915YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EA                  |
| <a href="#">TPS79915YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EA                  |
| TPS79915YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EA                  |
| <a href="#">TPS799185DDCR</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| TPS799185DDCR.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| TPS799185DDCRG4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| TPS799185DDCRG4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| <a href="#">TPS799185DDCT</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| TPS799185DDCT.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGP                 |
| <a href="#">TPS799185YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ZA                  |
| TPS799185YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ZA                  |
| <a href="#">TPS799185YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ZA                  |
| TPS799185YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ZA                  |
| <a href="#">TPS79918DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DDCR1G4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DDCR1G4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS79918DDCRG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79918DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DDCTG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79918DRV</a>   | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DRV.B                 | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| <a href="#">TPS79918DRV</a>   | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| TPS79918DRV.B                 | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWV                 |
| <a href="#">TPS79918YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EB                  |
| TPS79918YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EB                  |
| <a href="#">TPS79918YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EB                  |
| TPS79918YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EB                  |
| <a href="#">TPS799195DRV</a>  | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BTP                 |
| TPS799195DRV.B                | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BTP                 |
| <a href="#">TPS799195DRV</a>  | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BTP                 |
| TPS799195DRV.B                | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BTP                 |
| <a href="#">TPS799195YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | AO                  |
| TPS799195YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | AO                  |
| <a href="#">TPS799195YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | AO                  |
| TPS799195YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | AO                  |
| <a href="#">TPS79919YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F6                  |
| TPS79919YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F6                  |
| <a href="#">TPS79920YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GA                  |
| TPS79920YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GA                  |
| <a href="#">TPS79921YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | G7                  |
| TPS79921YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | G7                  |
| <a href="#">TPS79925DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS79925DDCR.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |
| TPS79925DDCRG4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |
| TPS79925DDCRG4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |
| <a href="#">TPS79925DDCT</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |
| TPS79925DDCT.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWW                 |
| <a href="#">TPS79925YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EC                  |
| TPS79925YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EC                  |
| <a href="#">TPS79925YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EC                  |
| TPS79925YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EC                  |
| <a href="#">TPS79926YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F3                  |
| TPS79926YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F3                  |
| <a href="#">TPS79926YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F3                  |
| TPS79926YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F3                  |
| <a href="#">TPS79927DDCR</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BWE                 |
| TPS79927DDCR.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BWE                 |
| <a href="#">TPS79927DDCT</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BWE                 |
| TPS79927DDCT.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BWE                 |
| <a href="#">TPS79927DRV</a>  | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BPM                 |
| TPS79927DRV.B                | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BPM                 |
| <a href="#">TPS79927DRV</a>  | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BPM                 |
| TPS79927DRV.B                | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BPM                 |
| <a href="#">TPS79927YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F5                  |
| TPS79927YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | F5                  |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS799285DDCR</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXY                 |
| TPS799285DDCR.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXY                 |
| <a href="#">TPS799285DDCT</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXY                 |
| TPS799285DDCT.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXY                 |
| <a href="#">TPS799285DRVR</a> | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BST                 |
| TPS799285DRVR.B               | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BST                 |
| <a href="#">TPS799285DRVT</a> | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BST                 |
| TPS799285DRVT.B               | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | BST                 |
| <a href="#">TPS799285YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EE                  |
| TPS799285YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EE                  |
| <a href="#">TPS79928DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| TPS79928DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| <a href="#">TPS79928DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| TPS79928DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| <a href="#">TPS79928DRVR</a>  | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| TPS79928DRVR.B                | Active        | Production           | WSON (DRV)   6        | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| <a href="#">TPS79928DRVT</a>  | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| TPS79928DRVT.B                | Active        | Production           | WSON (DRV)   6        | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AWX                 |
| <a href="#">TPS79928YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ED                  |
| TPS79928YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ED                  |
| <a href="#">TPS79928YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ED                  |
| TPS79928YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | ED                  |
| <a href="#">TPS79930DDCR</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins        | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS79930DDCR.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |
| TPS79930DDCR1G4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |
| TPS79930DDCR1G4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |
| TPS79930DDCRG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79930DDCT</a>  | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |
| TPS79930DDCT.B                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXZ                 |
| TPS79930DDCTG4                | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79930YZUR</a>  | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EF                  |
| TPS79930YZUR.B                | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EF                  |
| <a href="#">TPS79930YZUT</a>  | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EF                  |
| TPS79930YZUT.B                | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EF                  |
| <a href="#">TPS799315DDCR</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| TPS799315DDCR.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| TPS799315DDCRG4               | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| TPS799315DDCRG4.B             | Active        | Production           | SOT-23-THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| <a href="#">TPS799315DDCT</a> | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| TPS799315DDCT.B               | Active        | Production           | SOT-23-THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CGQ                 |
| <a href="#">TPS799315YZUR</a> | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GP                  |
| TPS799315YZUR.B               | Active        | Production           | DSBGA (YZU)   5       | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GP                  |
| <a href="#">TPS799315YZUT</a> | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GP                  |
| TPS799315YZUT.B               | Active        | Production           | DSBGA (YZU)   5       | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | GP                  |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins            | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|---------------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS79932YZUR</a>  | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | (F4, FY)            |
| TPS79932YZUR.B                | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | (F4, FY)            |
| <a href="#">TPS79933DDCR</a>  | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCR.B                | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCR1G4               | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCR1G4.B             | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCRG4                | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79933DDCT</a>  | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCT.B                | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DDCTG4                | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 250   SMALL T&R       | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79933DRVR</a>  | Active        | Production           | WSON (DRV)   6            | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DRVR.B                | Active        | Production           | WSON (DRV)   6            | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DRVRG4                | Active        | Production           | WSON (DRV)   6            | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| <a href="#">TPS79933DRV T</a> | Active        | Production           | WSON (DRV)   6            | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DRV T.B               | Active        | Production           | WSON (DRV)   6            | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| TPS79933DRV T G4              | Active        | Production           | WSON (DRV)   6            | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AXX                 |
| <a href="#">TPS79933YZUR</a>  | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EG                  |
| TPS79933YZUR.B                | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EG                  |
| <a href="#">TPS79933YZUT</a>  | Active        | Production           | DSBGA (YZU)   5           | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EG                  |
| TPS79933YZUT.B                | Active        | Production           | DSBGA (YZU)   5           | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | EG                  |
| <a href="#">TPS79942DDCR</a>  | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |
| TPS79942DDCR.B                | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |
| TPS79942DDCR1G4               | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |

| Orderable part number        | Status<br>(1) | Material type<br>(2) | Package   Pins            | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|------------------------------|---------------|----------------------|---------------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TPS79942DDCR1G4.B            | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |
| TPS79942DDCRG4               | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 125   |                     |
| <a href="#">TPS79942DDCT</a> | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |
| TPS79942DDCT.B               | Active        | Production           | SOT-23-<br>THIN (DDC)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CJQ                 |
| <a href="#">TPS79945YZUR</a> | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | FK                  |
| TPS79945YZUR.B               | Active        | Production           | DSBGA (YZU)   5           | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | FK                  |
| <a href="#">TPS79945YZUT</a> | Active        | Production           | DSBGA (YZU)   5           | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | FK                  |
| TPS79945YZUT.B               | Active        | Production           | DSBGA (YZU)   5           | 250   SMALL T&R       | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 125   | FK                  |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF TPS799 :**

- Automotive : [TPS799-Q1](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

## TAPE AND REEL INFORMATION



### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS79901DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79901DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79901DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79901DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79901DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79901DRV1T   | WSO1N        | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS79901YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79901YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799125YZUR   | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799125YZUT   | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79912DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS79912DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79912DRVT    | WSO          | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS79912YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79912YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79913DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79913DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79913YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79915DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79915DDCRG4  | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79915DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79915YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79915YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79918DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918DDCRG4  | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79918YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79918DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79918YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79918YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799195DRVR   | WSO          | DRV             | 6    | 3000 | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS799195DRVT   | WSO          | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS799195YZUR   | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799195YZUT   | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79919YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79920YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79921YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79925DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79925DDCRG4  | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS79925DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79925YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79925YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79926YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79926YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79927DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79927DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79927DRVT    | WSON         | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS79927YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799285DDCR   | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS799285DDCT   | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS799285DRVR   | WSON         | DRV             | 6    | 3000 | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS799285DRVT   | WSON         | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS79928DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79928DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79928YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79928YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79930DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79930DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79930DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79930DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79930YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79930YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799315DDCR   | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS799315DDCRG4 | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS799315DDCT   | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS799315YZUR   | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS799315YZUT   | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79932YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79933DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS79933DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79933DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79933DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79933DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 180.0              | 8.4                | 3.1     | 3.05    | 1.1     | 4.0     | 8.0    | Q3            |
| TPS79933DRV7    | WSO7         | DRV             | 6    | 250  | 179.0              | 8.4                | 2.2     | 2.2     | 1.2     | 4.0     | 8.0    | Q2            |
| TPS79933YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79933YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79942DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79942DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79942DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 179.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS79945YZUR    | DSBGA        | YZU             | 5    | 3000 | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |
| TPS79945YZUT    | DSBGA        | YZU             | 5    | 250  | 180.0              | 8.4                | 1.07    | 1.42    | 0.74    | 4.0     | 8.0    | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal


| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS79901DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |
| TPS79901DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79901DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |
| TPS79901DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79901DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 183.0       | 183.0      | 20.0        |
| TPS79901DRVT    | WSON         | DRV             | 6    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79901YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79901YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS799125YZUR   | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS799125YZUT   | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79912DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79912DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79912DRVT    | WSON         | DRV             | 6    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79912YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79912YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79913DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79913DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79913YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS79915DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79915DDCRG4  | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79915DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79915YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79915YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS799185DDCR   | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799185DDCRG4 | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799185DDCT   | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS799185YZUR   | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS799185YZUT   | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79918DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79918DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79918DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79918YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79918YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS799195DRVR   | WSON         | DRV             | 6    | 3000 | 203.0       | 203.0      | 35.0        |
| TPS799195DRVT   | WSON         | DRV             | 6    | 250  | 203.0       | 203.0      | 35.0        |
| TPS799195YZUR   | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS799195YZUT   | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79919YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79920YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79921YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79925DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79925DDCRG4  | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79925DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79925YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79925YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79926YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79926YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79927DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79927DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79927DRVT    | WSON         | DRV             | 6    | 250  | 203.0       | 203.0      | 35.0        |
| TPS79927YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS799285DDCR   | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799285DDCT   | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS799285DRVR   | WSON         | DRV             | 6    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799285DRVT   | WSON         | DRV             | 6    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79928DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79928DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79928YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79928YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79930DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79930DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS79930DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |
| TPS79930DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79930YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79930YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS799315DDCR   | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799315DDCRG4 | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS799315DDCT   | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS799315YZUR   | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS799315YZUT   | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79932YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79933DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |
| TPS79933DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79933DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 183.0       | 183.0      | 20.0        |
| TPS79933DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79933DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 183.0       | 183.0      | 20.0        |
| TPS79933DRVVT   | WSON         | DRV             | 6    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79933YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79933YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |
| TPS79942DDCR    | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79942DDCR1G4 | SOT-23-THIN  | DDC             | 5    | 3000 | 200.0       | 183.0      | 25.0        |
| TPS79942DDCT    | SOT-23-THIN  | DDC             | 5    | 250  | 200.0       | 183.0      | 25.0        |
| TPS79945YZUR    | DSBGA        | YZU             | 5    | 3000 | 182.0       | 182.0      | 20.0        |
| TPS79945YZUT    | DSBGA        | YZU             | 5    | 250  | 182.0       | 182.0      | 20.0        |



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.



4222173/B 04/2018

**NOTES:**

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

# EXAMPLE BOARD LAYOUT


DRV0006A

WSN - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
SCALE:25X



SOLDER MASK DETAILS

4222173/B 04/2018

NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).
5. Vias are optional depending on application, refer to device data sheet. If some or all are implemented, recommended via locations are shown.

## EXAMPLE STENCIL DESIGN

DRV0006A

WSO - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD





SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD #7  
88% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:30X

4222173/B 04/2018

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



4225563/A 12/2019

**NOTES:**


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.

# EXAMPLE BOARD LAYOUT


DRV0006D

WSN - 0.8 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



**LAND PATTERN EXAMPLE**  
EXPOSED METAL SHOWN  
SCALE:25X



**SOLDER MASK DETAILS**

4225563/A 12/2019


NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).
5. Vias are optional depending on application, refer to device data sheet. If some or all are implemented, recommended via locations are shown.

**DRV0006D**

**WSN - 0.8 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD




## SOLDER PASTE EXAMPLE BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD #7  
88% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:30X

4225563/A 12/2019

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



4220752/C 08/2024

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-193.
4. Support pin may differ or may not be present.

# EXAMPLE BOARD LAYOUT


DDC0005A

SOT-23 - 1.1 max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPLODED METAL SHOWN  
SCALE:15X




SOLDERMASK DETAILS

4220752/C 08/2024

NOTES: (continued)

4. Publication IPC-7351 may have alternate designs.
5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




SOLDER PASTE EXAMPLE  
 BASED ON 0.125 THICK STENCIL  
 SCALE:15X

4220752/C 08/2024

NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
7. Board assembly site may have different recommendations for stencil design.




# PACKAGE OUTLINE

YZU0005

DSBGA - 0.625 mm max height

DIE SIZE BALL GRID ARRAY



4222196/A 11/2015

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


YZU0005

DSBGA - 0.625 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
SCALE:50X



SOLDER MASK DETAILS  
NOT TO SCALE

4222196/A 11/2015


NOTES: (continued)

- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. Refer to Texas Instruments Literature No. SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

**YZU0005**

**DSBGA - 0.625 mm max height**

## DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:50X

4222196/A 11/2015

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated