




Electronic Terminal Block with Miniature Switching Relay

1/2

1 changeover contact

Data sheet


Description	Item-No.	Pack.-unit pcs																																																		
Switching relay terminal block	859-357	1																																																		
- Switching relay terminal block with miniature switching relay 1 changeover contact for medium switching powers. - Safe electrical isolation meets DIN VDE 0140, DIN EN 61140. - Mounting on DIN 35 rail.																																																				
DC-Load limiting value graph 																																																				
Note: Inductive loads have to be attenuated by an appropriate protective circuit in order to protect relay coils and contacts !																																																				
Technical Data <table><tr><td>Contact material</td><td>AgSnO₂</td></tr><tr><td>Input nominal voltage U_N</td><td>AC 115 V / DC 110 V*</td></tr><tr><td></td><td>* cUL_{US} ratings only for input nominal voltage U_N AC 115 V</td></tr><tr><td>Input voltage range</td><td>U_N -15 %...+10 %</td></tr><tr><td>Current input at U_N (coil 20 °C)</td><td>3.5 mA</td></tr><tr><td>Max. switching voltage</td><td>AC 250 V</td></tr><tr><td>Max. continuous current (terminal blocks in a row)</td><td>5 A</td></tr><tr><td>Max. switching power (resistive)</td><td>AC 1250 VA</td></tr><tr><td>(resistive)</td><td>DC see load limiting value graph</td></tr><tr><td>Making capacity</td><td>10 A at max. 4 s and 10 % relative cyclic duration factor</td></tr><tr><td>Recommended min. load</td><td>≥ 100 mA / AC/DC 12 V</td></tr><tr><td>Max. number of switching operations with/without load</td><td>6 min⁻¹ / 20 s⁻¹</td></tr><tr><td>Operating power</td><td>< 420 mW</td></tr><tr><td>Pull-in/dropout/bounce time t_{yp}</td><td>5 ms / 6 ms / 5 ms</td></tr><tr><td>Operation at normal rating</td><td>100 % continuous duty</td></tr><tr><td>Dielectric strength contact/coil</td><td>4 kV</td></tr><tr><td>Surge voltage strength contact/coil (1.2/50 μs)</td><td>6 kV</td></tr><tr><td>Open contact</td><td>1 kV</td></tr><tr><td>Nominal voltage acc. to VDE 0110 Part1/ 4.97</td><td></td></tr><tr><td>IEC 60664-1</td><td>250 V / 4 kV / 3</td></tr><tr><td>Mechanical life</td><td>5 x 10⁶ switching operations</td></tr><tr><td>at max. load (resistive)</td><td>3 x 10⁴ switching operations</td></tr><tr><td>Ambient operating temperature at U_N</td><td>-25 °C...+50 °C</td></tr><tr><td>at 1.2 x U_N</td><td>-25 °C...+40 °C</td></tr><tr><td>Storage temperature</td><td>-40 °C...+70 °C</td></tr></table>			Contact material	AgSnO ₂	Input nominal voltage U _N	AC 115 V / DC 110 V*		* cUL _{US} ratings only for input nominal voltage U _N AC 115 V	Input voltage range	U _N -15 %...+10 %	Current input at U _N (coil 20 °C)	3.5 mA	Max. switching voltage	AC 250 V	Max. continuous current (terminal blocks in a row)	5 A	Max. switching power (resistive)	AC 1250 VA	(resistive)	DC see load limiting value graph	Making capacity	10 A at max. 4 s and 10 % relative cyclic duration factor	Recommended min. load	≥ 100 mA / AC/DC 12 V	Max. number of switching operations with/without load	6 min ⁻¹ / 20 s ⁻¹	Operating power	< 420 mW	Pull-in/dropout/bounce time t _{yp}	5 ms / 6 ms / 5 ms	Operation at normal rating	100 % continuous duty	Dielectric strength contact/coil	4 kV	Surge voltage strength contact/coil (1.2/50 μs)	6 kV	Open contact	1 kV	Nominal voltage acc. to VDE 0110 Part1/ 4.97		IEC 60664-1	250 V / 4 kV / 3	Mechanical life	5 x 10 ⁶ switching operations	at max. load (resistive)	3 x 10 ⁴ switching operations	Ambient operating temperature at U _N	-25 °C...+50 °C	at 1.2 x U _N	-25 °C...+40 °C	Storage temperature	-40 °C...+70 °C
Contact material	AgSnO ₂																																																			
Input nominal voltage U _N	AC 115 V / DC 110 V*																																																			
	* cUL _{US} ratings only for input nominal voltage U _N AC 115 V																																																			
Input voltage range	U _N -15 %...+10 %																																																			
Current input at U _N (coil 20 °C)	3.5 mA																																																			
Max. switching voltage	AC 250 V																																																			
Max. continuous current (terminal blocks in a row)	5 A																																																			
Max. switching power (resistive)	AC 1250 VA																																																			
(resistive)	DC see load limiting value graph																																																			
Making capacity	10 A at max. 4 s and 10 % relative cyclic duration factor																																																			
Recommended min. load	≥ 100 mA / AC/DC 12 V																																																			
Max. number of switching operations with/without load	6 min ⁻¹ / 20 s ⁻¹																																																			
Operating power	< 420 mW																																																			
Pull-in/dropout/bounce time t _{yp}	5 ms / 6 ms / 5 ms																																																			
Operation at normal rating	100 % continuous duty																																																			
Dielectric strength contact/coil	4 kV																																																			
Surge voltage strength contact/coil (1.2/50 μs)	6 kV																																																			
Open contact	1 kV																																																			
Nominal voltage acc. to VDE 0110 Part1/ 4.97																																																				
IEC 60664-1	250 V / 4 kV / 3																																																			
Mechanical life	5 x 10 ⁶ switching operations																																																			
at max. load (resistive)	3 x 10 ⁴ switching operations																																																			
Ambient operating temperature at U _N	-25 °C...+50 °C																																																			
at 1.2 x U _N	-25 °C...+40 °C																																																			
Storage temperature	-40 °C...+70 °C																																																			

Electronic Terminal Block with Miniature Switching Relay

2/2

1 changeover contact

Data sheet

	Terminal block width	6 mm / 0.236 in		
	Wire connection	CAGE CLAMP®		
		0.08-2.5 mm ² / AWG 28-14		
	Stripped length	5-6 mm / 0.22 in		
	Standards / prescriptions	VDE 0435 Part 201, DIN EN 61810-1		
		VDE 0140, DIN EN 61140		
	Approvals	cUL _{us}		
		UL508 / CSA22.2		
		E175199		
		CB scheme		
		IEC 60947-1 / IEC 60947-5-1		
		DEMKO DK-7574		
		AC15	3 A	AC 250 V
		DC13	0.5 A	DC 24 V
	Accessories			
	End and intermediate plate	859-525		
	Comb type jumper bar 2-way	859-402		
	3-way	859-403		
	4-way	859-404		
	5-way	859-405		
	10-way	859-410		
	Test pin 1 mm Ø	859-500		