



FCIconnect.com

Copyright FCI




PRODUCT NUMBER
10126114-XYHLF

LEAD FREE OPTION
SEE NOTE 6,7,8

NO. OF POS.
SEE TABLE

PIN PLATING

BASE P/N



mat'l. code		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ⌀	product family HEADER	
l	tr	ec	n	dr	date	
A	NEW	ZK	06/14/13	angles	linear	
				0°±2'	linear	
				dr	ZK HU	06/14/13
				enr	ZK HU	06/14/13
				chr	RICK BIAN	06/14/13
				app	RICK BIAN	06/14/13
sheet	revision	A	A			
index	sheet	1	2			

title		FRICION LATCH HEADER DOUBLE ROW VERTICAL	
dwg no	sheet 1 of 2	size	
10126114		A3	
type Product Customer Drawing			

1		2		3		4		5		6	
PRODUCT NUMBER		NO.OF POS.		MATING LENGTH DIM H		OVERALL LENGTH DIM K		DIM L		NOTES:	
10126114-X06		2 X 3		0.230/5.84		0.300/7.62		0.200/5.08		1. MOLDING MAT'L: GLASS REINFORCED PCT, COLOR: BLACK FLAME RETARDANT PER UL 94 V-0 MAXIMUM OPERATING TEMPERATURE: 130° C OR MINERAL FILLED LCP, COLOR BLACK FLAME RETARDANT PER UL 94 V-0	
-X08		2 X 4		0.230/5.84		0.400/10.16		0.300/7.62		2. PIN MATERIAL: 3/4 HD PHOS. BRZ.	
-X10		2 X 5		0.230/5.84		0.500/12.70		0.400/10.16		3. NO SLOTS ON 2 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.	
-X12		2 X 6		0.230/5.84		0.600/15.24		0.500/12.70		4. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.	
-X14		2 X 7		0.230/5.84		0.700/17.78		0.600/15.24		5. COMPANY LOGO MAY APPEAR IN THIS AREA.	
-X16		2 X 8		0.230/5.84		0.800/20.32		0.700/17.78		6. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.	
-X18		2 X 9		0.230/5.84		0.900/22.86		0.800/20.32		7. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.	
-X20		2 X 10		0.230/5.84		1.000/25.40		0.900/22.86		PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.	
-X22		2 X 11		0.230/5.84		1.100/27.94		1.000/25.40		8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.	
-X24		2 X 12		0.230/5.84		1.200/30.48		1.100/27.94			
-X26		2 X 13		0.230/5.84		1.300/33.02		1.200/30.48			
-X28		2 X 14		0.230/5.84		1.400/35.56		1.300/33.02			
10126114-X30		2 X 15		0.230/5.84		1.500/38.10		1.400/35.56			
PIN PLATING CODES											
-1YY		30u"/.76u Au MIN. ON 50u"/1.27u Ni									
-2YY		15u/.38u Au MIN. ON 50u"/1.27u Ni									
mat'l. code surface tolerance projection product family											
ISO 1302		ISO 406		ISO 1101		INCH/MM		HEADER			
A		angles		linear		scale 3:1		title			
								FRICTION LATCH HEADER			
								DOUBLE ROW VERTICAL			
		dr		ZK HU		06/14/13		dwg no		sheet2of2 size	
		engr		ZK HU		06/14/13		10126114		A3	
		chr		RICK BIAN		06/14/13		type		Product Customer Drawing	
		appd		RICK BIAN		06/14/13					
sheet index		revision sheet									

FCI

FCIconnect.com

Copyright FCI

Form: A3

1

2

3

4

5

6

PDS: Rev :A

STATUS: Released

Printed: Jun 27, 2013