

4





3

2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20 ALL RIGHTS RESERVED. © COPYRIGHT 20 BY -

| REVISIONS | | | | |
|-----------|-----|-------------|-----------|---------|
| 変更 | | | | |
| P | LTR | DESCRIPTION | DATE | APVD |
| | D | REVISED | 15APR2014 | H.O N.Y |




- 1 適合電線：大電(株)製(HRZFV-SB AWG25×2心)
- 2 D/Cは同梱の顧客用図面(図面名称欄内)に記載
- 3 取扱説明書：411-78259

- 1 ACCEPTABLE WIRE:DAIDEN Co.Ltd.(HRZFV-SB AWG25×2C)
- 2 D/C IS DESCRIBED IN THE BUNDLED CUSTOMER DRAWING (IN DRAWING NAME COLUMN).
- 3 INSTRUCTION SHEET:411-78259



| ITEM NO. | MATERIAL / FINISH | PART NAME | ITEM NO. |
|----------|--|---|----------|
| ASSEMBLY | 材料 / 仕上げ | 部品名称 | |
| 1 | POLYAMIDE OF GLASS FILLED PLASTIC(UL94V-0) ガラス入りポリアミド系樹脂 UL 94V-0 | RETENTION HSG リテンション ハウジング | 7 |
| 2 | OLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0) ガラス入り熱可塑性ポリエステル系樹脂 UL 94V-0 | COVER HSG カバー ハウジング | 6 |
| 2 | STAINLESS STEEL ステンレス鋼 | LOCK SPRING ロック スプリング | 5 |
| 1 | STEEL/UNDER:COPPER PLATING, TOP:Ni PLATING 鋼/下地:銅めっき, 表面:ニッケルめっき | BACK SHELL OF PLUG バック シェル | 4 |
| 1 | STEEL/UNDER:COPPER PLATING, TOP:Ni PLATING 鋼/下地:銅めっき, 表面:ニッケルめっき | FRONT SHELL OF PLUG フロント シェル | 3 |
| 1 | POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0) ガラス入り熱可塑性ポリエステル系樹脂 UL 94V-0 | CAP HSG キャップ ハウジング | 2 |
| 1 | CONTACT(COPPER ALLOY/ UNDER ALL SURFACE:Ni PLATING 1.27μm MIN TOP CONTACT AREA:Au PLATING 0.76μm MIN SOLDERING AREA:Tin PLATING 2μm MIN) HSG(POLYAMIDE OF GLASS FILLED PLASTIC(UL94V-0)) INDUCTOR(TDK SP0203-R10K-PF) コンタクト(銅合金/ 全面:ニッケルめっき下地 1.27μm以上 表面 接点部:金めっき 0.76μm以上 半田付け部:錫めっき 2μm以上) ハウジング(ガラス入りポリアミド系樹脂 UL 94V-0) インダクタ(ABC0製 AN02 TB R10K) | SUB PLUG ASSY with INDUCTOR サブ プラグ アッセンブリ (インダクタ付) | 1 |

| | | | | | | | | | | | | | | | | | |
|--|---|--------------------------------------|---|---|---|--|---|-------|---|-------|---|--------|---|---------------------------|--|--------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 27OCT2006 K.RIKU | |  TE Connectivity | | | | | | | | | | | | | |
| DIMENSIONS: 単位: 概 mm | | CHK 27OCT2006 I.HASEGAWA | | | | NAME 名称 MECHATROLINK II CONNECTOR KIT | | | | | | | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3 | | APVD 27OCT2006 I.HASEGAWA | | DRAWING NO 番号 C=1827525 | | | | | | | | | | | | | |
| <table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> </table> | | 0 PLC | ± | 1 PLC | ± | 2 PLC | ± | 3 PLC | ± | 4 PLC | ± | ANGLES | ± | PRODUCT SPEC 製品規格 - | | RESTRICTED TO - | |
| 0 PLC | ± | | | | | | | | | | | | | | | | |
| 1 PLC | ± | | | | | | | | | | | | | | | | |
| 2 PLC | ± | | | | | | | | | | | | | | | | |
| 3 PLC | ± | | | | | | | | | | | | | | | | |
| 4 PLC | ± | | | | | | | | | | | | | | | | |
| ANGLES | ± | | | | | | | | | | | | | | | | |
| MATERIAL 材料 - | | FINISH 仕上 - | | SCALE 尺度 2:1 | | | | | | | | | | | | | |
| | | WEIGHT TRAY IS CONTAINED) 29.9(g) | | SHEET OF 1 | | | | | | | | | | | | | |
| | | CUSTOMER DRAWING | | REV D | | | | | | | | | | | | | |