


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		AK	REVISED PER ECO-10-008433	21MAY10	HMR	KW

1. COPPER ALLOY
- 2


5.08 μm [.000200] MINIMUM THICK SILVER PLATE PER QQ-S-365
- 3

2.54 μm [.000100] MINIMUM THICK TIN-LEAD PLATE PER ASTM-B-545, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
- 4


2.54 μm [.000100] MINIMUM THICK MATTE TIN PLATE, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.



VIEW C




VIEW Z
SAME AS VIEW C EXCEPT AS SHOWN



VIEW D

SUPERCEDED BY 9-329461-0	D	4.50 [.177]	—	4	9-329461-2
	Z	4.50 [.177]	4.11 [.162]	4	9-329461-1
	Z	4.50 [.177]	4.11 [.162]	4	9-329461-0
OBSOLETE	D	4.50 [.177]	—	3	3-329461-3
	C	4.88 [.192]	4.22 [.166]	3	2-329461-9
	Z	4.50 [.177]	4.11 [.162]	4	2-329461-7
OBSOLETE	C	4.88 [.192]	4.22 [.166]	2	2-329461-6
OBSOLETE	D	4.50 [.177]	—	2	2-329461-2
	Z	4.50 [.177]	4.11 [.162]	2	329461
	VIEW	B	A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. L. GROFT 9-24-90		 Tyco Electronics Corporation Harrisburg, PA, 17105-3608			
DIMENSIONS: MM [INCHES]			CHK M. SNEED 1-30-91					
			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD R. HENRY 1-30-91		NAME FERRULE	
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			WEIGHT —					
MATERIAL			FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTES			SEE NOTES		A2	00779	C=329461	—
CUSTOMER DRAWING					SCALE	10:1	SHEET	1 of 1
					REV AK			