



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	G1		REVISED PER ECO-10-000443	12JAN10	KK AEG

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

5 OBSOLETE	3.984	3.900	39	40	4-103185-0
	3.884	3.800	38	39	3-103185-9
	3.784	3.700	37	38	3-103185-8
	3.684	3.600	36	37	3-103185-7
5 OBSOLETE	3.584	3.500	35	36	3-103185-6
	3.484	3.400	34	35	3-103185-5
	3.384	3.300	33	34	3-103185-4
	3.284	3.200	32	33	3-103185-3
	3.184	3.100	31	32	3-103185-2
	3.084	3.000	30	31	3-103185-1
	2.984	2.900	29	30	3-103185-0
	2.884	2.800	28	29	2-103185-9
5 OBSOLETE	2.784	2.700	27	28	2-103185-8
	2.684	2.600	26	27	2-103185-7
	2.584	2.500	25	26	2-103185-6
	2.484	2.400	24	25	2-103185-5
5 OBSOLETE	2.384	2.300	23	24	2-103185-4
	2.284	2.200	22	23	2-103185-3
	2.184	2.100	21	22	2-103185-2
	2.084	2.000	20	21	2-103185-1
5 OBSOLETE	1.984	1.900	19	20	2-103185-0
	1.884	1.800	18	19	1-103185-9
	1.784	1.700	17	18	1-103185-8
	1.684	1.600	16	17	1-103185-7
5 SUPERCEDED BY 6-146280-5	1.584	1.500	15	16	1-103185-6
	1.484	1.400	14	15	1-103185-5
	1.384	1.300	13	14	1-103185-4
	1.284	1.200	12	13	1-103185-3
5 OBSOLETE	1.184	1.100	11	12	1-103185-2
	1.084	1.000	10	11	1-103185-1
5 SUPERCEDED BY 6-146280-0	.984	.900	9	10	1-103185-0
	.884	.800	8	9	103185-9
	.784	.700	7	8	103185-8
	.684	.600	6	7	103185-7
	.584	.500	5	6	103185-6
	.484	.400	4	5	103185-5
	.384	.300	3	4	103185-4
	.284	.200	2	3	103185-3
	.184	.100	1	2	103185-2
	.084	—	—	1	103185-1
	C	B	A	NO OF POSN	PART NUMBER