






ITEM-NO. (ITEM-NO.)	713-1111
Cross section1 (Cross section / mm ²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	22
Height (Height / mm)	18.8
Width (Width / mm)	40
Depth (Depth / mm)	16
No. of connection Points (No. of connection Points)	22
No. of potentials (No. of potentials)	22
COLOR (COLOR)	schwarz
Comment (Comment)	L = ((No. of poles / 2) - 1) x Pin Spacing + 5 mm