




Radial Metallized Polyester Film Capacitor

1436-XXXX Series

DIMENSIONS (mm)



Specifications:

- Type: Metallized Polyester Film
- Operating Temperature: -40°C to +85°C
- Rated Voltage: 250, 400, 630 VDC

Performance Characteristics		
Test Item	Specifications	Test Conditions
Insulation Resistance:	$\geq 30,000\text{M}\Omega$ ($C \leq .33\mu\text{F}$); $\geq 10,000\text{M}\Omega \times \mu\text{F}$ ($C > .33\mu\text{F}$)	25°C, 60±5 sec. @ 50VDC RV<100VDC; 100VDC RV<500VDC; 500VDC RV≥ 500VDC
Withstand Voltage:	No abnormality between terminals or between terminals and enclosure.	160% for 1 minute or 200% for 1-5 seconds. Charge/discharge current shall not exceed 10mA.
Dissipation Factor:	A) .75% max. @ 1kHz; B) 1.3% max. @ 10kHz	≤ 5Vrms @ 25°C
Terminal Strength:	No cutting or slack of terminals.	0.6mm wire - pull: 1kg load for 10 sec.; bending: 0.5kg load @ 90° x 4
Capacitance:	Within specified tolerance	10% @ 1kHz, ≤ 5Vrms @ 25°C
Vibration Proof:	No abnormality of the appearance.	Frequency range: 10-55-10Hz; 1.5mm amplitude; 2hrs/direction for 3 directions.
Solderability:	At least 95% of the surface of the lead wire dipped into is covered with new solder	Solder temp: 235°C ± 2° Immersion time: 2 ± 0.2 sec. Solder: H60A or H63A
Soldering Heat Resistance:	Appearance, Withstand voltage: no abnormality; Cap. variation: within ± 2% of the value before test; Dissipation factor: 1.0% max. @ 1kHz	Solder temperature: 265°C ± 5° Immersion time: 10 ± 0.5 sec.
Cold Resistance:	Capacitance variation: within +0/-5% of the value before test.	-40°C ± 2° for 2 +1/-0 hrs
Dry Heat Resistance:	Insulation resistance: $\geq 1,500\text{M}\Omega$ ($C \leq 0.33\mu\text{F}$); $\geq 300\text{M}\Omega \times \mu\text{F}$ ($C > 0.33\mu\text{F}$) Capacitance variation: within +0/-5% of the value before test.	-85°C ± 2° for 2 +1/-0 hrs
Temperature Cycle:	No remarkable abnormality on appearance. No abnormality on withstand voltage.	6 cycles: 1) -40°C ± 2° for 30 ± 1 minutes 2) +25°C ± 2° for 10~15 minutes 3) +85°C ± 2° for 30 ± 1 minutes 4) +25°C ± 2° for 10~15 minutes

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Radial Metallized Polyester Film Capacitor

1436-XXXX Series

Xicon Part Number	Value (uF)	VOLT. (VDC)	TOL. ±%	Dimensions (mm)				
				W	H	T	P	dØ
1436-2103	0.01	250	5	10.5	9.0	6.0	7.5	0.6
1436-2123	0.012	250	5	10.5	9.0	6.0	7.5	0.6
1436-2153	0.015	250	5	10.5	9.0	6.0	7.5	0.6
1436-2183	0.018	250	5	10.5	9.0	6.0	7.5	0.6
1436-2223	0.022	250	5	10.5	9.5	6.0	7.5	0.6
1436-2273	0.027	250	5	10.5	9.5	6.0	7.5	0.6
1436-2333	0.033	250	5	10.5	9.5	6.0	7.5	0.6
1436-2393	0.039	250	5	10.5	9.5	6.0	7.5	0.6
1436-2473	0.047	250	5	10.5	9.5	6.0	7.5	0.6
1436-2563	0.056	250	5	10.5	9.5	6.0	7.5	0.6
1436-2683	0.068	250	5	10.5	9.5	6.0	7.5	0.6
1436-2823	0.082	250	5	10.5	9.5	6.0	7.5	0.6
1436-2104	0.10	250	5	10.5	9.5	6.5	7.5	0.6
1436-2124	0.12	250	5	10.5	10.0	6.5	7.5	0.6
1436-2154	0.15	250	5	13.0	10.5	6.5	10	0.6
1436-2184	0.18	250	5	13.0	11.0	7.5	10	0.6
1436-2224	0.22	250	5	13.0	12.0	8.0	10	0.6
1436-2274	0.27	250	5	18.5	12.0	7.0	15	0.8
1436-2334	0.33	250	5	18.5	12.0	7.0	15	0.8
1436-2394	0.39	250	5	18.5	13.0	7.5	15	0.8
1436-2474	0.47	250	5	18.5	14.0	8.0	15	0.8
1436-2564	0.56	250	5	18.5	14.0	8.5	15	0.8
1436-2684	0.68	250	5	18.5	16.5	9.5	15	0.8
1436-2824	0.82	250	5	18.5	16.5	9.5	15	0.8
1436-2105	1.0	250	5	23.0	16.0	10.0	20	0.8
1436-2125	1.2	250	5	23.0	18.0	10.0	20	0.8
1436-2155	1.5	250	5	23.0	19.0	10.5	20	0.8
1436-2185	1.8	250	5	23.0	19.0	11.0	20	0.8
1436-2225	2.2	250	5	23.0	21.0	13.0	20	0.8
1436-2275	2.7	250	5	32.0	22.5	13.0	27.5	0.8
1436-2335	3.3	250	5	32.0	23.0	13.5	27.5	0.8
1436-2395	3.9	250	5	32.0	25.0	14.5	27.5	0.8
1436-2475	4.7	250	5	32.0	26.0	15.5	27.5	0.8
1436-4103	0.01	400	5	10.5	9.0	6.0	7.5	0.6
1436-4153	0.015	400	5	10.5	9.0	6.0	7.5	0.6
1436-4223	0.022	400	5	10.5	10.0	6.5	7.5	0.6
1436-4333	0.033	400	5	10.5	10.0	6.5	7.5	0.6
1436-4473	0.047	400	5	13.0	11.0	7.0	10.0	0.6
1436-4683	0.068	400	5	13.0	12.0	7.5	10.0	0.6
1436-4104	0.10	400	5	18.5	12.5	7.5	15.0	0.8
1436-4154	0.15	400	5	18.5	13.5	8.0	15.0	0.8
1436-4224	0.22	400	5	18.5	15.5	9.0	15.0	0.8
1436-4334	0.33	400	5	18.5	17.5	9.5	15.0	0.8
1436-4474	0.47	400	5	23.0	18.5	11.5	20.0	0.8
1436-4105	1.0	400	5	32.0	21.5	13.5	27.5	0.8
1436-4225	2.2	400	5	32.0	29.0	18.5	27.5	0.8
1436-6103	0.01	630	5	13.0	10.0	6.5	10.0	0.6
1436-6153	0.015	630	5	13.0	10.5	6.5	10.0	0.6
1436-6223	0.022	630	5	13.0	10.5	6.5	10.0	0.6
1436-6333	0.033	630	5	18.5	11.5	7.0	15.0	0.8
1436-6473	0.047	630	5	18.5	12.5	7.5	15.0	0.8
1436-6683	0.068	630	5	18.5	14.0	8.0	15.0	0.8
1436-6104	0.10	630	5	18.5	15.5	9.5	15.0	0.8
1436-6154	0.15	630	5	23.0	16.5	9.5	20.0	0.8
1436-6224	0.22	630	5	23.0	19.0	11.5	20.0	0.8
1436-6334	0.33	630	5	32.0	19.0	12.0	27.5	0.8
1436-6474	0.47	630	5	32.0	22.0	13.5	27.5	0.8
1436-6105	1.0	630	5	32.0	29.0	18.5	27.5	0.8

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[1436-2183](#) [1436-2824](#)