

CATALOG

➔ Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

➔ [Part Number Search](#)
 ➔ [Document Search](#)
 ➔ [Product Type Search](#)
 ➔ [Product Family Search](#)
 ➔ [Alphabetical Search](#)
 ➔ [RoHS/ELV Compliance & Alternates](#)
 ➔ [CAD Model Search](#)
 ➔ [Brand Search](#)
 ➔ [Tool Search](#)
 ➔ [Multiple Part Comparison](#)
 ➔ [Lead Free Solutions](#)
 ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Sockets

➔ DIP Sockets

 **528-AG10D**  [Active](#)
**Directive 2002/95/EC
Compliant**
[RoHS Compliant](#)**(Corporate P/N: 5-1437536-2)**[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
➤ General Info ➤ Sales Info ➤ Assembly Subcontractors	➤ Pricing ➤ Product Availability	➤ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Wave solder capable to 240°C, Wave solder capable to 265°C
Product Type:	DIP Socket
Number of Positions:	28
Row-to-Row Spacing (mm [in]):	15.24 [0.600]
Contact Mount:	Thru Hole
Mount Style:	Vertical

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Insulation Resistance (MΩ):	5,000
Contact Resistance (mΩ):	10
Sleeve Material:	Brass/Copper
Contact Termination Area Plating:	Gold
Product Series:	500 Series

Centerline (mm [in]):	2.54 [0.100]
Profile:	Standard
Frame Style:	Closed
Leg Style:	Straight
Contact Material:	Beryllium Copper
Contact Mating Area Plating:	Gold (25)
Contact Style:	Screw Machine
Mating Contact Type:	Four-Fingered
Height Above PC Board (mm [in]):	4.57 [0.180]
Temperature Range (° C):	125
Packaging Method:	Tube
Termination Post Length (mm [in]):	3.18 [0.125]

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]