


RF & MICROWAVE TRANSISTORS UHF PULSED APPLICATIONS

- 350 WATTS @ 10μSEC PULSE WIDTH, 10% DUTY CYCLE
- 300 WATTS @ 250μSEC PULSE WIDTH, 10% DUTY CYCLE
- 9.5 dB MIN. GAIN
- REFRACTORY GOLD METALLIZATION
- EMITTER BALLASTING AND LOW THERMAL RESISTANCE FOR RELIABILITY AND RUGGEDNESS
- INFINITE VSWR CAPABILITY AT SPECIFIED OPERATING CONDITIONS



.400 x .400 2LFL (M106)
hermetically sealed


ORDER CODE
SD1563

BRANDING
SD1563

DESCRIPTION

The SD1563 is a gold metallized silicon NPN pulse power transistor. The SD1563 is designed for applications requiring high peak power and low duty cycles within the frequency range of 400 - 500 MHz.

PIN CONNECTION



- | | |
|--------------|------------|
| 1. Collector | 3. Emitter |
| 2. Base | 4. Base |

ABSOLUTE MAXIMUM RATINGS (T_{case} = 25°C)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	65	V
V _{CES}	Collector-Emitter Voltage	65	V
V _{EBO}	Emitter-Base Voltage	3.5	V
I _C	Device Current	21.6	A
P _{DISS}	Power Dissipation	875	W
T _J	Junction Temperature	+200	°C
T _{STG}	Storage Temperature	- 65 to +150	°C

THERMAL DATA

R _{TH(j-c)}	Junction-Case Thermal Resistance	0.2	°C/W
----------------------	----------------------------------	-----	------

SD1563

ELECTRICAL SPECIFICATIONS ($T_{\text{case}} = 25^{\circ}\text{C}$)

STATIC

Symbol	Test Conditions		Value			Unit
			Min.	Typ.	Max.	
BV_{CBO}	$I_{\text{C}} = 50 \text{ mA}$	$I_{\text{E}} = 0 \text{ mA}$	65	—	—	V
BV_{CES}	$I_{\text{C}} = 50 \text{ mA}$	$V_{\text{BE}} = 0 \text{ V}$	65	—	—	V
BV_{CEO}	$I_{\text{C}} = 50 \text{ mA}$	$I_{\text{B}} = 0 \text{ mA}$	28	—	—	V
BV_{EBO}	$I_{\text{E}} = 10 \text{ mA}$	$I_{\text{C}} = 0 \text{ mA}$	3.5	—	—	V
I_{CES}	$V_{\text{CE}} = 30 \text{ V}$	$I_{\text{E}} = 0 \text{ mA}$	—	—	7.5	mA
h_{FE}	$V_{\text{CE}} = 5 \text{ V}$	$I_{\text{C}} = 5 \text{ A}$	10	—	100	—

DYNAMIC

Symbol	Test Conditions			Value			Unit
				Min.	Typ.	Max.	
P_{OUT}	$f = 425 \text{ MHz}$	$P_{\text{IN}} = 33.5 \text{ W}$	$V_{\text{CE}} = 40 \text{ V}$	300	—	—	W
P_{G}	$f = 425 \text{ MHz}$	$P_{\text{OUT}} = 300 \text{ W}$	$V_{\text{CE}} = 40 \text{ V}$	9.5	—	—	dB
η_{C}	$f = 425 \text{ MHz}$	$P_{\text{IN}} = 25 \text{ W}$	$V_{\text{CE}} = 40 \text{ V}$	55	—	—	%


Note: Pulse Width = 250 μ Sec, Duty Cycle = 10%

TYPICAL PERFORMANCE


P_{OUT} (W)	P.W. (μ Sec)	D.C. (%)	T_{J} ($^{\circ}\text{C}$ max.)	V_{CC}
360	10	10	150	40
350	20	10	150	40
325	100	10	150	40
310	500	10	150	40
300	1000	10	150	40

TYPICAL PERFORMANCE (P.W. = 120 μ Sec)


POWER OUTPUT vs POWER INPUT




POWER GAIN vs FREQUENCY





POWER OUTPUT vs COLLECTOR VOLTAGE




EFFICIENCY vs POWER INPUT






TYPICAL PERFORMANCE (P.W. = 120 μ Sec)IMPEDANCE DATA (P.W. = 120 μ Sec)


TYPICAL PERFORMANCE (P.W. = 250 μ Sec)

POWER GAIN vs FREQUENCY




EFFICIENCY vs FREQUENCY

POWER OUTPUT vs FLANGE
 T_J @ CONSTANT 125°CTHERMAL RESISTANCE vs PULSE
WIDTH

IMPEDANCE DATA (P.W. = 250 μ Sec)

PACKAGE MECHANICAL DATA

Ref.: Dwg. No.12-0106 rev. B



SGS-THOMSON MICROELECTRONICS			CONT'D		
	MINIMUM Inches/mm	MAXIMUM Inches/mm		MINIMUM Inches/mm	MAXIMUM Inches/mm
A	.045/1,14	.055/1,40	K	.105/2,67	.125/3,18
B	.710/18,03		L		.230/5,84
C	.380/9,65	.390/9,91			
D	.130/3,30				
E	.392/9,96	.402/10,29			
F	.392/9,96	.402/10,29			
G	.645/16,38	.655/16,64			
H	.895/22,73	.905/22,99			
I	.002/0,05	.006/0,15			
J	.055/1,40	.065/1,65			

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

©1994 SGS-THOMSON Microelectronics - All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A.