



FCIconnect.com

Copyright FCI.

1

2

## CONFIGURATION OF CUSTOMER DOCUMENTS

| P/N           | DOCUMENTS | DWG. NO.   | TITLE                                               |
|---------------|-----------|------------|-----------------------------------------------------|
| HLW_R/S-2C7LF | SPEC      | SC-HLW05   | CONNECTOR USED FOR FPC/FFC WITH 1mm CONTACT SPACING |
|               | CONNECTOR | JSA96403   | CAT NO.TABLE FOR 1mm SPACING CONNECTOR              |
|               |           | JSA96405   | 1mm SPACING CONNECTOR FOR FPC/FFC                   |
|               |           | JSA96406   | 1mm SPACING CONNECTOR FOR FPC/FFC                   |
|               | CABLE     | JSA93382   | RECOMMENDED CABLE(FPC)                              |
|               |           | JSA93383   | RECOMMENDED CABLE(FFC)                              |
|               | MANUAL    | BJM-HLW101 | HANDLING PROCEDURES AND REMARKS                     |

| P/N           | DOCUMENTS | DWG. NO.   | TITLE                                           |
|---------------|-----------|------------|-------------------------------------------------|
| HLW_R/S-6C7LF | SPEC      | SC-HLW06   | CONNECTOR USED FOR C/C WITH 1mm CONTACT SPACING |
|               | CONNECTOR | JSA96404   | CAT NO.TABLE FOR 1mm SPACING CONNECTOR          |
|               |           | JSA96407   | 1mm SPACING CONNECTOR FOR C/C                   |
|               |           | JSA96408   | 1mm SPACING CONNECTOR FOR C/C                   |
|               | CABLE     | JSA93626   | RECOMMENDED CABLE(C/C)                          |
|               | MANUAL    | BJM-HLW102 | HANDLING PROCEDURES AND REMARKS                 |

|             |                |     |         |                                                                                                               |                  |            |  |                        |                                                                               |         |        |
|-------------|----------------|-----|---------|---------------------------------------------------------------------------------------------------------------|------------------|------------|--|------------------------|-------------------------------------------------------------------------------|---------|--------|
| mat'l. code |                |     |         | surface 58 / tolerance ISO 1302 <input checked="" type="checkbox"/> ISO 406 <input type="checkbox"/> ISO 1101 |                  | projection |  | product family 58PF/QF |                                                                               | CODE JP |        |
| ltr         | ecn no         | dr  | date    | tolerances unless otherwise specified                                                                         |                  |            |  |                        | title<br>1mm SPACING CONNECTOR<br>DOCUMENT LIST<br>(Cat. No. HLW_R/S-2/6C7LF) |         |        |
| A           | J05-0270       | H.T | 5/11/05 | angles                                                                                                        | linear           |            |  |                        |                                                                               |         |        |
| B           | J05-0293       | H.T | 5/18/05 |                                                                                                               |                  |            |  |                        | dwg no JSA96418 sheet 1 of 1 size A4                                          |         |        |
| C           | J05-0517       | H.T | 8/11/05 |                                                                                                               |                  |            |  |                        |                                                                               |         |        |
| D           | J06-0449       | H.T | 11/2/06 | dr                                                                                                            | <i>H. Shoult</i> | 11/2/06    |  |                        |                                                                               |         |        |
|             |                |     |         | enr                                                                                                           | <i>H. Shoult</i> | 11/2/06    |  |                        |                                                                               |         |        |
|             |                |     |         | chr                                                                                                           | <i>R. Shoult</i> | 11/2/06    |  |                        | type Product Customer Drawing                                                 |         |        |
|             |                |     |         | appd                                                                                                          | <i>S. Dedam</i>  | 11/2/06    |  |                        |                                                                               |         |        |
| sheet index | revision sheet | D 1 |         |                                                                                                               |                  |            |  |                        |                                                                               |         | Rev. D |

form: A4

1

2

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO.         |               | DIMENSIONS (NOTE1) |         |      |
|---------------------|------------------|---------------|--------------------|---------|------|
|                     | RIGHT ANGLE TYPE | STRAIGHT TYPE | A ± 0.3            | B ± 0.1 | C    |
| 4                   | HLW 4R-2C7LF     | HLW 4S-2C7LF  | 6.6                | 5.12    | 3.0  |
| 5                   | HLW 5R-2C7LF     | HLW 5S-2C7LF  | 7.6                | 6.12    | 4.0  |
| 6                   | HLW 6R-2C7LF     | HLW 6S-2C7LF  | 8.6                | 7.12    | 5.0  |
| 7                   | HLW 7R-2C7LF     | HLW 7S-2C7LF  | 9.6                | 8.12    | 6.0  |
| 8                   | HLW 8R-2C7LF     | HLW 8S-2C7LF  | 10.6               | 9.12    | 7.0  |
| 9                   | HLW 9R-2C7LF     | HLW 9S-2C7LF  | 11.6               | 10.12   | 8.0  |
| 10                  | HLW10R-2C7LF     | HLW10S-2C7LF  | 12.6               | 11.12   | 9.0  |
| 11                  | HLW11R-2C7LF     | HLW11S-2C7LF  | 13.6               | 12.12   | 10.0 |
| 12                  | HLW12R-2C7LF     | HLW12S-2C7LF  | 14.6               | 13.12   | 11.0 |
| 13                  | HLW13R-2C7LF     | HLW13S-2C7LF  | 15.6               | 14.12   | 12.0 |
| 14                  | HLW14R-2C7LF     | HLW14S-2C7LF  | 16.6               | 15.12   | 13.0 |
| 15                  | HLW15R-2C7LF     | HLW15S-2C7LF  | 17.6               | 16.12   | 14.0 |
| 16                  | HLW16R-2C7LF     | HLW16S-2C7LF  | 18.6               | 17.12   | 15.0 |
| 17                  | HLW17R-2C7LF     | HLW17S-2C7LF  | 19.6               | 18.12   | 16.0 |
| 18                  | HLW18R-2C7LF     | HLW18S-2C7LF  | 20.6               | 19.12   | 17.0 |
| 19                  | HLW19R-2C7LF     | HLW19S-2C7LF  | 21.6               | 20.12   | 18.0 |
| 20                  | HLW20R-2C7LF     | HLW20S-2C7LF  | 22.6               | 21.12   | 19.0 |
| 21                  | HLW21R-2C7LF     | HLW21S-2C7LF  | 23.6               | 22.12   | 20.0 |
| 22                  | HLW22R-2C7LF     | HLW22S-2C7LF  | 24.6               | 23.12   | 21.0 |
| 23                  | HLW23R-2C7LF     | HLW23S-2C7LF  | 25.6               | 24.12   | 22.0 |
| 24                  | HLW24R-2C7LF     | HLW24S-2C7LF  | 26.6               | 25.12   | 23.0 |
| 25                  | HLW25R-2C7LF     | HLW25S-2C7LF  | 27.6               | 26.12   | 24.0 |
| 26                  | HLW26R-2C7LF     | HLW26S-2C7LF  | 28.6               | 27.12   | 25.0 |
| 27                  | HLW27R-2C7LF     | HLW27S-2C7LF  | 29.6               | 28.12   | 26.0 |
| 28                  | HLW28R-2C7LF     | HLW28S-2C7LF  | 30.6               | 29.12   | 27.0 |
| 29                  | HLW29R-2C7LF     | HLW29S-2C7LF  | 31.6               | 30.12   | 28.0 |
| 30                  | HLW30R-2C7LF     | HLW30S-2C7LF  | 32.6               | 31.12   | 29.0 |
| 31                  | HLW31R-2C7LF     | HLW31S-2C7LF  | 33.6               | 32.12   | 30.0 |
| 32                  | HLW32R-2C7LF     | HLW32S-2C7LF  | 34.6               | 33.12   | 31.0 |

CAT. NO. HLW (n) R - 2C7 LF

SERIES \_\_\_\_\_

NO. OF CONTACTS \_\_\_\_\_

R : RIGHT ANGLE TYPE

S : STRAIGHT TYPE

VARIATION \_\_\_\_\_

LEAD FREE \_\_\_\_\_

## NOTES

1. SEE PART DRAWINGS FOR DIMENSIONS A~C.

|             |          |          |         |                                           |         |            |  |                                                                                 |           |                          |              |      |
|-------------|----------|----------|---------|-------------------------------------------|---------|------------|--|---------------------------------------------------------------------------------|-----------|--------------------------|--------------|------|
| mat'l. code |          |          |         | surface 58 / tolerance ISO 406 / ISO 1101 |         | projection |  | product family 58PF/QF                                                          |           | CODE JP                  |              |      |
| ltr         | ecn no   | dr       | date    | tolerances unless otherwise specified     |         |            |  | title CAT NO. TABLE FOR<br>1mm SPACING CONNECTOR<br>(Cat. No. : HLW__R/S-2C7LF) |           |                          |              |      |
| A           | J05-0270 | H.T      | 5/10/05 | angles                                    | linear  | mm         |  |                                                                                 |           |                          |              |      |
| B           | J06-0449 | H.T      | 11/2/06 |                                           |         | scale X    |  |                                                                                 |           |                          |              |      |
|             |          |          |         | dr                                        | 11/2/06 |            |  |                                                                                 | dwg no    |                          | sheet 1 of 1 | size |
|             |          |          |         | engr                                      | 11/2/06 |            |  |                                                                                 | JSA 96403 |                          | A4           |      |
|             |          |          |         | chr                                       | 11/2/06 |            |  |                                                                                 |           |                          |              |      |
|             |          |          |         | appd                                      | 11/7/06 |            |  |                                                                                 |           |                          |              |      |
| sheet index |          | revision | B       |                                           |         |            |  | type                                                                            |           | Product Customer Drawing |              |      |
| sheet       |          | 1        |         |                                           |         |            |  |                                                                                 |           | Rev. B                   |              |      |

SC-HLW05 JSA96405 96406 93382 93383  
form: A4



INSULATOR : PBT RESIN GLASS REINFORCED (UL94V-0)  
COLOR : BLACK  
CONTACT : PHOSPHOR BRONZE  
PLATING : TIN


1. THIS PRODUCT IS RIGHT ANGLE TYPE CONNECTOR. DETAIL A  
2. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER  
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.  
3. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10  
SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.

THICKNESS : 1.2~1.6  
HOLE PATTERN (COMPONENT SIDE)

Figure 1 is a technical drawing of a component side pattern. It shows a grid of contact points. The dimensions are as follows:

- Overall width:  $1X(n-1) \pm 0.1$
- Horizontal spacing between contact points:  $1 \pm 0.1$  and  $2 \pm 0.1$
- Vertical spacing between contact points:  $2 \pm 0.1$
- Radius of contact points:  $n - \phi 0.7 \pm 0.05$
- NO.1 CONTACT POSITION is indicated by an arrow pointing to the first contact point on the left.
- A break symbol (two parallel diagonal lines) is used to indicate that the pattern is repeated.

SC-HLW05 JSA96403  
form: A4



#### MATERIAL

INSULATOR : PBT RESIN GLASS REINFORCED (UL94V-0)  
 COLOR : BLACK  
 CONTACT : PHOSPHOR BRONZE  
 PLATING : TIN

NOTE 1. THIS PRODUCT IS STRAIGHT TYPE CONNECTOR.


2. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

3. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.

#### RECOMMENDED PC BOARD



THICKNESS : 1.2~1.6

HOLE PATTERN (COMPONENT SIDE)



DETAIL A


n : NO. OF CONTACTS

|             |          |                |          |                                       |                  |                                  |                |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
|-------------|----------|----------------|----------|---------------------------------------|------------------|----------------------------------|----------------|---------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------|--|--|------------|--------|--|
| mat'l. code |          |                |          | surface 58 ✓<br>ISO 1302              |                  | tolerance<br>ISO 406<br>ISO 1101 |                | projection<br> |                                                                                     | product family<br>58QF                                                              |                                                                           |  |  | CODE<br>JP |        |  |
| ltr         | ecn no   | dr             | date     | tolerances unless otherwise specified |                  |                                  |                |                                                                                                   |                                                                                     |  | title<br>1mm SPACING<br>CONNECTOR FOR FPC/FFC<br>(Cat. No. :HLW__S-2C7LF) |  |  |            |        |  |
| A           | J05-0270 | H.T            | 5/10/05  | angles                                | linear           | ±0.2                             |                |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
| B           | J05-0735 | H.T            | 10/28/05 |                                       |                  |                                  |                |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
| C           | J06-0449 | H.T            | 11/2/06  |                                       |                  |                                  |                | scale $\propto$                                                                                   |                                                                                     | dwg no<br>sheet 1 of 1<br>JSA 96406<br>type Product Customer Drawing                |                                                                           |  |  |            |        |  |
|             |          |                |          | dr                                    | <i>J. Deland</i> |                                  | <i>11/2/06</i> |                                                                                                   |  |                                                                                     |                                                                           |  |  |            |        |  |
|             |          |                |          | enrg                                  | <i>R. Shoup</i>  |                                  | <i>11/2/06</i> |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
|             |          |                |          | chr                                   | <i>R. Shoup</i>  |                                  | <i>11/2/06</i> |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
|             |          |                |          | appd                                  | <i>J. Deland</i> |                                  | <i>11/7/06</i> |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            |        |  |
| sheet index |          | revision sheet |          | C                                     | 1                |                                  |                |                                                                                                   |                                                                                     |                                                                                     |                                                                           |  |  |            | Rev. C |  |

SC-HLW05 JSA96403  
 form: A4

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTORS



| PT. NO. | DESCRIPTION     | MATERIAL                                | THICKNESS (μm) |
|---------|-----------------|-----------------------------------------|----------------|
| 1       | BASE FILM       | POLYIMIDE OR POLYESTER OR EQUIVALENT    | 25             |
| 2       | CONDUCTOR       | COPPER FOIL (PLATING : SOLDER 1μm MIN.) | 35             |
| 3       | OVERLAY         | POLYIMIDE OR POLYESTER OR EQUIVALENT    | —              |
| 4       | SUPPORTING TAPE | POLYESTER OR POLYIMIDE OR EQUIVALENT    | 188            |


NOTES

- 1. NO BURR AT EACH PORTION.
- 2. NO PEELING IN COMMON USE.
- 3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.

|                         |  |                |  |                                                    |  |            |  |                               |  |                   |  |
|-------------------------|--|----------------|--|----------------------------------------------------|--|------------|--|-------------------------------|--|-------------------|--|
| mat'l. code             |  |                |  | surface 58 / tolerance ISO 1302 ✓ ISO 406 ISO 1101 |  | projection |  | product family 58PF/QF        |  | CODE JP           |  |
| litr ecn no dr date     |  |                |  | tolerances unless otherwise specified              |  | mm         |  | title                         |  |                   |  |
| AA J05-0270 H.T 5/11/05 |  |                |  | angles linear                                      |  | mm         |  | RECOMMENDED CABLE (FPC)       |  |                   |  |
| AB J06-0449 H.T 11/2/06 |  |                |  |                                                    |  | scale X    |  | (Cat. No. HLW__R/S-__)        |  |                   |  |
|                         |  |                |  | dr                                                 |  | FCI        |  | dwg no                        |  | sheet 1 of 1 size |  |
|                         |  |                |  | enrg                                               |  |            |  | JSA 93382                     |  | A4                |  |
|                         |  |                |  | chr                                                |  |            |  | type Product Customer Drawing |  |                   |  |
|                         |  |                |  | appd                                               |  |            |  |                               |  |                   |  |
| sheet index             |  | revision sheet |  | AB 1                                               |  |            |  |                               |  | Rev. AB           |  |

## RECOMMENDED CABLE (FFC)

n : NO. OF CONDUCTORS



| PT. NO. | DESCRIPTION     | MATERIAL                                | NOTE                                      |
|---------|-----------------|-----------------------------------------|-------------------------------------------|
| 1       | INSULATOR       | FLAME RESISTING POLYESTER OR EQUIVALENT |                                           |
| 2       | CONDUCTOR       | COPPER FOIL                             | PLATING : TIN OR SOLDER<br>1 $\mu$ m MIN. |
| 3       | SUPPORTING TAPE | FLAME RESISTING POLYESTER OR EQUIVALENT |                                           |

## NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.

|             |          |     |         |                                                               |  |            |  |                         |  |                          |  |
|-------------|----------|-----|---------|---------------------------------------------------------------|--|------------|--|-------------------------|--|--------------------------|--|
| mat'l. code |          |     |         | surface 58 / tolerance ISO 1302 $\checkmark$ ISO 406 ISO 1101 |  | projection |  | product family 58PF/QF  |  | CODE JP                  |  |
| litr        | ecn no   | dr  | date    | tolerances unless otherwise specified                         |  |            |  | title                   |  |                          |  |
| AA          | J05-0270 | H.T | 5/11/05 | angles linear                                                 |  | mm         |  | RECOMMENDED CABLE (FFC) |  |                          |  |
| AB          | J06-0449 | H.T | 11/2/06 |                                                               |  |            |  | (Cat. No. HLW__R/S-__)  |  |                          |  |
|             |          |     |         | dr                                                            |  | 11/2/06    |  | dwg no                  |  | sheet 1 of 1 size        |  |
|             |          |     |         | enrg                                                          |  | 11/2/06    |  | JSA 93383               |  | A4                       |  |
|             |          |     |         | chr                                                           |  | 11/2/06    |  | type                    |  | Product Customer Drawing |  |
|             |          |     |         | appd                                                          |  | 11/2/06    |  |                         |  |                          |  |
| sheet index | revision | AB  | 1       |                                                               |  |            |  |                         |  | Rev. AB                  |  |

form: A4

1

2

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO.         |               | DIMENSIONS (NOTE1) |         |      |
|---------------------|------------------|---------------|--------------------|---------|------|
|                     | RIGHT ANGLE TYPE | STRAIGHT TYPE | A ± 0.3            | B ± 0.1 | C    |
| 4                   | HLW 4R-6C7LF     | HLW 4S-6C7LF  | 6.6                | 5.12    | 3.0  |
| 5                   | HLW 5R-6C7LF     | HLW 5S-6C7LF  | 7.6                | 6.12    | 4.0  |
| 6                   | HLW 6R-6C7LF     | HLW 6S-6C7LF  | 8.6                | 7.12    | 5.0  |
| 7                   | HLW 7R-6C7LF     | HLW 7S-6C7LF  | 9.6                | 8.12    | 6.0  |
| 8                   | HLW 8R-6C7LF     | HLW 8S-6C7LF  | 10.6               | 9.12    | 7.0  |
| 9                   | HLW 9R-6C7LF     | HLW 9S-6C7LF  | 11.6               | 10.12   | 8.0  |
| 10                  | HLW10R-6C7LF     | HLW10S-6C7LF  | 12.6               | 11.12   | 9.0  |
| 11                  | HLW11R-6C7LF     | HLW11S-6C7LF  | 13.6               | 12.12   | 10.0 |
| 12                  | HLW12R-6C7LF     | HLW12S-6C7LF  | 14.6               | 13.12   | 11.0 |
| 13                  | HLW13R-6C7LF     | HLW13S-6C7LF  | 15.6               | 14.12   | 12.0 |
| 14                  | HLW14R-6C7LF     | HLW14S-6C7LF  | 16.6               | 15.12   | 13.0 |
| 15                  | HLW15R-6C7LF     | HLW15S-6C7LF  | 17.6               | 16.12   | 14.0 |
| 16                  | HLW16R-6C7LF     | HLW16S-6C7LF  | 18.6               | 17.12   | 15.0 |
| 17                  | HLW17R-6C7LF     | HLW17S-6C7LF  | 19.6               | 18.12   | 16.0 |
| 18                  | HLW18R-6C7LF     | HLW18S-6C7LF  | 20.6               | 19.12   | 17.0 |
| 19                  | HLW19R-6C7LF     | HLW19S-6C7LF  | 21.6               | 20.12   | 18.0 |
| 20                  | HLW20R-6C7LF     | HLW20S-6C7LF  | 22.6               | 21.12   | 19.0 |
| 21                  | HLW21R-6C7LF     | HLW21S-6C7LF  | 23.6               | 22.12   | 20.0 |
| 22                  | HLW22R-6C7LF     | HLW22S-6C7LF  | 24.6               | 23.12   | 21.0 |
| 23                  | HLW23R-6C7LF     | HLW23S-6C7LF  | 25.6               | 24.12   | 22.0 |
| 24                  | HLW24R-6C7LF     | HLW24S-6C7LF  | 26.6               | 25.12   | 23.0 |
| 25                  | HLW25R-6C7LF     | HLW25S-6C7LF  | 27.6               | 26.12   | 24.0 |
| 26                  | HLW26R-6C7LF     | HLW26S-6C7LF  | 28.6               | 27.12   | 25.0 |
| 27                  | HLW27R-6C7LF     | HLW27S-6C7LF  | 29.6               | 28.12   | 26.0 |
| 28                  | HLW28R-6C7LF     | HLW28S-6C7LF  | 30.6               | 29.12   | 27.0 |
| 29                  | HLW29R-6C7LF     | HLW29S-6C7LF  | 31.6               | 30.12   | 28.0 |
| 30                  | HLW30R-6C7LF     | HLW30S-6C7LF  | 32.6               | 31.12   | 29.0 |
| 31                  | HLW31R-6C7LF     | HLW31S-6C7LF  | 33.6               | 32.12   | 30.0 |
| 32                  | HLW32R-6C7LF     | HLW32S-6C7LF  | 34.6               | 33.12   | 31.0 |

CAT. NO. HLW (n) R - 6C7 LF

SERIES

NO. OF CONTACTS

R : RIGHT ANGLE TYPE

S : STRAIGHT TYPE

VARIATION


LEAD FREE

NOTES

1. SEE PART DRAWINGS FOR DIMENSIONS A~C.

|             |          |     |         |                                           |         |            |  |                                                                                    |  |         |  |
|-------------|----------|-----|---------|-------------------------------------------|---------|------------|--|------------------------------------------------------------------------------------|--|---------|--|
| mat'l. code |          |     |         | surface 58 / tolerance ISO 406 / ISO 1101 |         | projection |  | product family 58PF/QF                                                             |  | CODE JP |  |
| ltr         | ecn no   | dr  | date    | tolerances unless otherwise specified     |         |            |  | title<br>CAT NO. TABLE FOR<br>1mm SPACING CONNECTOR<br>(Cat. No. : HLW__R/S-6C7LF) |  |         |  |
| A           | J05-0270 | H.T | 5/10/05 | angles                                    | linear  | mm         |  |                                                                                    |  |         |  |
| B           | J06-0449 | H.T | 11/2/06 |                                           |         | scale X    |  | dwg no JSA 96404 sheet 1 of 1 size A4                                              |  |         |  |
|             |          |     |         | dr                                        | 11/2/06 |            |  |                                                                                    |  |         |  |
|             |          |     |         | engr                                      | 11/2/06 |            |  | type Product Customer Drawing                                                      |  |         |  |
|             |          |     |         | chr                                       | 11/2/06 |            |  |                                                                                    |  |         |  |
|             |          |     |         | appd                                      | 11/2/06 |            |  | Rev. B                                                                             |  |         |  |
|             |          |     |         |                                           |         |            |  |                                                                                    |  |         |  |
| sheet index | revision | B   | 1       |                                           |         |            |  |                                                                                    |  |         |  |

SC-HLW06 form: A4 JSA96407 96408 93626



MATERIAL

INSULATOR : PBT RESIN GLASS REINFORCED (UL94V-0)  
 COLOR : BLACK  
 CONTACT : PHOSPHOR BRONZE  
 PLATING : TIN


NOTE

- 1.THIS PRODUCT IS RIGHT ANGLE TYPE CONNECTOR.
- 2.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 3.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.


RECOMMENDED PC BOARD

THICKNESS : 1.2~1.6  
 HOLE PATTERN (COMPONENT SIDE)

n : NO. OF CONTACTS



|             |          |     |          |                                       |                   |            |                                                        |              |
|-------------|----------|-----|----------|---------------------------------------|-------------------|------------|--------------------------------------------------------|--------------|
| mat'l. code |          |     |          | surface 58                            | tolerance ISO 406 | projection | product family                                         | CODE         |
|             |          |     |          | ISO 1302                              | ISO 1101          |            | 58PF                                                   | JP           |
| ltr         | ecn no   | dr  | date     | tolerances unless otherwise specified |                   | mm         | title                                                  |              |
| A           | J05-0270 | H.T | 5/10/05  | angles                                | linear            |            |                                                        |              |
| B           | J05-0735 | H.T | 10/28/05 |                                       |                   |            | 1mm SPACING CONNECTOR FOR CIC (Cat. No. :HLW__R-6C7LF) |              |
| C           | J06-0449 | H.T | 11/2/06  |                                       |                   | scale      |                                                        |              |
|             |          |     |          | dr                                    | 11/2/06           | FCI        | dwg no                                                 | sheet 1 of 1 |
|             |          |     |          | enr                                   | 11/2/06           |            | JSA 96407                                              |              |
|             |          |     |          | chr                                   | 11/2/06           |            |                                                        |              |
|             |          |     |          | appd                                  | 11/2/06           |            | type Product Customer Drawing                          |              |
| sheet index | revision | C   |          |                                       |                   |            |                                                        |              |
|             | sheet    | 1   |          |                                       |                   |            |                                                        | Rev. C       |



**MATERIAL**


INSULATOR : PBT RESIN GLASS REINFORCED (UL94V-0)  
 COLOR : BLACK  
 CONTACT : PHOSPHOR BRONZE  
 PLATING : TIN

**NOTE**

1. THIS PRODUCT IS STRAIGHT TYPE CONNECTOR.
2. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
3. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.

**RECOMMENDED PC BORAD**

THICKNESS : 1.2~1.6  
 HOLE PATTERN (COMPONENT SIDE)




|             |          |     |          |                                       |           |            |                                                              |              |
|-------------|----------|-----|----------|---------------------------------------|-----------|------------|--------------------------------------------------------------|--------------|
| mat'l. code |          |     |          | surface 58                            | tolerance | projection | product family                                               | CODE         |
|             |          |     |          | ISO 1302                              | ISO 406   |            | 58QF                                                         | JP           |
| ltr         | ecn no   | dr  | date     | tolerances unless otherwise specified |           | mm         | title                                                        |              |
| A           | J05-0270 | H.T | 5/10/05  | angles                                | linear    |            |                                                              |              |
| B           | J05-0735 | H.T | 10/28/05 |                                       |           |            | 1mm SPACING<br>CONNECTOR FOR CIC<br>(Cat. No. :HLW__S-6C7LF) |              |
| C           | J06-0449 | H.T | 11/2/01  |                                       |           | scale      |                                                              |              |
|             |          |     |          | dr                                    | 11/2/06   | FCI        | dwg no                                                       | sheet 1 of 1 |
|             |          |     |          | enr                                   | 11/2/06   |            | JSA 96408                                                    | size         |
|             |          |     |          | chr                                   | 11/2/06   |            |                                                              | A4           |
|             |          |     |          | appd                                  | 11/2/06   |            | type Product Customer Drawing                                |              |
| sheet       | revision | C   |          |                                       |           |            |                                                              | Rev.         |
| index       | sheet    | 1   |          |                                       |           |            |                                                              | c            |

SC-HLW 06 JSA96404  
 form: A4

# RECOMMENDED CABLE (CIC)

n : NO. OF CONDUCTORS



| PT. NO. | DESCRIPTION     | MATERIAL                             | THICKNESS (μm) |     |
|---------|-----------------|--------------------------------------|----------------|-----|
| 1       | BASE FILM       | POLYESTER OR EQUIVALENT              | 75             | 25  |
| 2       | CONDUCTOR       | CARBON PASTE OVER SILVER PASTE       | 10 MIN.        |     |
| 3       | OVERLAY         | POLYIMIDE OR POLYESTER OR EQUIVALENT | —              |     |
| 4       | SUPPORTING TAPE | POLYESTER OR POLYIMIDE OR EQUIVALENT | 188            | 250 |

## NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.

|             |          |     |         |                                       |  |                                  |  |                  |  |                                                            |  |            |  |
|-------------|----------|-----|---------|---------------------------------------|--|----------------------------------|--|------------------|--|------------------------------------------------------------|--|------------|--|
| mat'l. code |          |     |         | surface<br>ISO 1302 ✓                 |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br>mm |  | product family<br>58PF/QF                                  |  | CODE<br>JP |  |
| ltr         | ecn no   | dr  | date    | tolerances unless otherwise specified |  |                                  |  | mm               |  | title<br>RECOMMENDED CABLE (CIC)<br>(Cat. No. HLW__R/S-__) |  |            |  |
| AA          | J05-0270 | H.T | 5/11/05 | angles                                |  | linear                           |  | scale X          |  | dwg no<br>JSA 93626                                        |  |            |  |
| AB          | J06-0449 | H.T | 11/2/06 |                                       |  |                                  |  |                  |  | sheet 1 of 1 size<br>A4                                    |  |            |  |
|             |          |     |         | dr                                    |  | 11/2/06                          |  | FCI              |  | type Product Customer Drawing                              |  |            |  |
|             |          |     |         | enr                                   |  | 11/2/06                          |  |                  |  |                                                            |  |            |  |
|             |          |     |         | chr                                   |  | 11/2/06                          |  |                  |  |                                                            |  |            |  |
|             |          |     |         | appd                                  |  | 11/7/06                          |  |                  |  |                                                            |  |            |  |
| sheet index | revision | AB  | 1       |                                       |  |                                  |  |                  |  | Rev.<br>AB                                                 |  |            |  |

form: A4

1

2