

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

ES

00


A2

ECR-14-005789



19MAR14

T.Q


W.H




2 POSITION




SECT A-A




TRADE MARK





VIEW B




GATING RECESS



MATING SECTION

KINKING FORMING  
BOTH SIDE EACH 2 PLACES  
TOTAL: 4 PLACES

VIEW B



## NOTES:


## 1.MATERIAL:

HOUSING:NYLON(G.F.) UL94V-0,COLOR:GRAY,BLUE  
POST:PRE-TIN 0.5mm SQ. BRASS WIRETOLERANCES UNLESS  
OTHERWISE SPECIFIED:10> \* : ±0.2  
30> \* >10 : ±0.25  
100> \* >30 : ±0.3  
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

SEE NOTE 1

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -

FINISH

SEE NOTE 1

DWN 06DEC02

S.YAO

CHK 31JAN03

T.SASAKI

APVD 31JAN03

T. SASAKI

PRODUCT SPEC

108-60018

APPLICATION SPEC

114-5223

WEIGHT

SEE TABLE

CUSTOMER DRAWING



TE Connectivity

AMP Mini CT Connector 1.5mm Pitch  
Single Row HDR Ass'y (H) DIP Staggered Type with Kink

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=292206

SCALE

NON

SHEET

1 of 2

REV

A2

|     |      |           |     |             |      |     |      |
|-----|------|-----------|-----|-------------|------|-----|------|
| LOC | DIST | REVISIONS |     |             |      |     |      |
|     |      | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|     |      |           | —   | SEE SHEET 1 | —    | —   | —    |

|            |            |      |      |      |      |            |            |
|------------|------------|------|------|------|------|------------|------------|
| 0.28       | 2.5        | 8.5  | 6.6  | 4.5  | 4    |            | 9-292206-4 |
| 0.23       | 2.5        | 7.0  | 5.1  | 3.0  | 3    |            | 9-292206-3 |
| 1.11       | 3.0        | 32.5 | 30.6 | 28.5 | 20   | 7-292206-0 | 2-292206-0 |
| 1.06       | 3.0        | 31.0 | 29.1 | 27.0 | 19   | 6-292206-9 | 1-292206-9 |
| 1.01       | 3.0        | 29.5 | 27.6 | 25.5 | 18   | 6-292206-8 | 1-292206-8 |
| 0.96       | 3.0        | 28.0 | 26.1 | 24.0 | 17   | 6-292206-7 | 1-292206-7 |
| 0.91       | 3.0        | 26.5 | 24.6 | 22.5 | 16   | 6-292206-6 | 1-292206-6 |
| 0.86       | 3.0        | 25.0 | 23.1 | 21.0 | 15   | 6-292206-5 | 1-292206-5 |
| 0.81       | 3.0        | 23.5 | 21.6 | 19.5 | 14   | 6-292206-4 | 1-292206-4 |
| 0.75       | 3.0        | 22.0 | 20.1 | 18.0 | 13   | 6-292206-3 | 1-292206-3 |
| 0.70       | 3.0        | 20.5 | 18.6 | 16.5 | 12   | 6-292206-2 | 1-292206-2 |
| 0.65       | 3.0        | 19.0 | 17.1 | 15.0 | 11   | 6-292206-1 | 1-292206-1 |
| 0.60       | 3.0        | 17.5 | 15.6 | 13.5 | 10   | 6-292206-0 | 1-292206-0 |
| 0.54       | 3.0        | 16.0 | 14.1 | 12.0 | 9    | 5-292206-9 | 292206-9   |
| 0.49       | 3.0        | 14.5 | 12.6 | 10.5 | 8    | 5-292206-8 | 292206-8   |
| 0.44       | 3.0        | 13.0 | 11.1 | 9.0  | 7    | 5-292206-7 | 292206-7   |
| 0.40       | 3.0        | 11.5 | 9.6  | 7.5  | 6    | 5-292206-6 | 292206-6   |
| 0.34       | 3.0        | 10.0 | 8.1  | 6.0  | 5    | 5-292206-5 | 292206-5   |
| 0.29       | 3.0        | 8.5  | 6.6  | 4.5  | 4    | 5-292206-4 | 292206-4   |
| 0.24       | 3.0        | 7.0  | 5.1  | 3.0  | 3    | 5-292206-3 | 292206-3   |
| 0.19       | 3.0        | 5.5  | 3.6  | 1.5  | 2    | 5-292206-2 | 292206-2   |
| WEIGHT (g) | D          | C    | B    | A    | Pos. | BLUE       | GRAY       |
|            | DIMENSIONS |      |      |      |      | PART NO    |            |

|                                        |                  |   |                 |           |            |               |              |        |
|----------------------------------------|------------------|---|-----------------|-----------|------------|---------------|--------------|--------|
| DIMENSIONS:<br>mm                      | DWN              | — | MATERIAL        | —         |            | FINISH        | —            |        |
|                                        | CHK              | — | TE Connectivity |           |            |               |              |        |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD             | — |                 |           |            |               |              |        |
| 0 PLC ± —                              | PRODUCT SPEC     | — |                 |           |            |               |              |        |
| 1 PLC ± SEE SHEET                      | APPLICATION SPEC | — |                 |           |            |               |              |        |
| 2 PLC ± 1 OF 2                         | WEIGHT           | — | SIZE            | CAGE CODE | DRAWING NO | RESTRICTED TO |              |        |
| 3 PLC ± —                              |                  |   | A4              | 00779     | ©=292206   | —             |              |        |
| 4 PLC ± —                              |                  |   |                 |           |            |               |              |        |
| ANGLES ± —                             | CUSTOMER DRAWING |   |                 |           | SCALE      | —             | SHEET 2 OF 2 | REV A2 |