



PANEL CUTOUT

PANEL THICKNESS	X
0.75-1.25	19.20
1.25-2.0	19.40
2.00-3.00	19.60



SWITCH FUNCTION	
PDS. 1	PDS. 2
DN	UP
1-1a	OPEN

CONTACT CONFIGURATION



CIRCUIT: SPST

- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X=±0.4; X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. RATING: 4(1)A @250VAC, 6A @250VAC
10A @125VAC
 5. MATERIALS: TERMINALS: COPPER ALLOY W/SILVER PLATING
CONTACTS: COIN SILVER
 6. MECHANICAL LIFE: >50,000 CYCLES
 7. ELECTRICAL LIFE: >10,000 CYCLES
 8. CONTACT RESISTANCE: < 20 MEGA-OHMS (INITIAL)
 9. INSULATION RESISTANCE: > 1000 MEGA-OHMS @ 500VDC
 10. DIELECTRIC STRENGTH: >1500VAC 1 MINUTE (INITIAL)
>3000V BETWEEN POLES
 11. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®			
TITLE			
R6AGRYWHFFF			
A	13364	RELEASED FOR PRODUCTION	8/12/03
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
2:1			
DATE			
8/12/03			
DR			
AR			
DWG			
M060314			
REV			
A			