

T100 Series Voltage and Continuity Testers

FLUKE®

New



The fast and easy solution to voltage, continuity and resistance measurements

Ideal for site conditions, the 3 models of the T100 Series 2-pole testers have a rugged construction and ergonomically formed housing for perfect handling. All models offer a patented three-phase rotation detection system providing quick phase rotation indication.

Moreover they have a special electrical torch function for working in low light level environments and have an ingress protection rating of IP65. The T100 Series are compliant with EN 61010-1 and EN61243-3 requirements.

Features

	T100	T120	T140
Display	12 LED's	3½ digit LCD	3½ digit LCD
LED Bargraph	●	●	●
Backlight			●
Resistance measurement			●
Voltage test	●	●	●
Optical and acoustical continuity test	●	●	●
Rotary field indication	●	●	●
Single pole test for phase detection	●	●	●
Indication of polarity	●	●	●
Electrical torch function	●	●	●

Specifications

	T100	T120	T140
Voltage AC/DC	12 – 690V	12 – 690V	12 – 690V
Continuity	0 – 400 kΩ	0 – 400 kΩ	0 – 400 kΩ
Frequency	0 – 400 Hz	0 – 400 Hz	0 – 400 Hz
Phase Rotation	100 to 690V	100 to 690V	100 to 690V
Resistance measurement	-	-	Up to 1999Ω
Response time	< 0.1s	< 0.1s	< 0.1s

Size (HxWxD): 240 mm x 56 mm x 24 mm
Case: IP65 (water-jet and dust tight protection)

Weight: 180 g
Two year warranty

Included Accessories

Two 1.5V batteries and instruction sheet

Ordering Information

Fluke T100 Voltage/Continuity Tester
Fluke T120 Voltage/Continuity Tester
Fluke T140 Voltage/Continuity Tester

UK versions are compliant with GS38

**Not available
in all countries**