


Duplex Singlemode 8.3/125 Fiber Patch Cable (SC/SC), 10M (33-ft.)

MODEL NUMBER: **N356-10M**



Description

Tripp Lite's 10-meter (33ft), singlemode duplex fiber optic SC/SC patch cable is manufactured from 8.3/125 zipcord fiber. The cable has SC connectors on each end, a PVC jacket, and is FDDI and OFNR rated. Duplex singlemode fiber is most commonly used in LAN applications.

Features

- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-meter (33ft) Connectors: 2 SC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	8.3/125
Intended Application	Computer Networking (Fiber)

Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

Applications

Networking equipment that requires singlemode fiber optic patch cables

Package Includes

10-meter (33ft) Duplex Singlemode Fiber Patch Cable, SC/SC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Type	SINGLEMODE 8.3/125 FIBER OPTIC
Model Type	SC/SC
INPUT	
Cable Length (m)	10
UPC ASSIGNMENT	
Unit Carton UPC#	037332120342
PHYSICAL	
Color	Yellow
CONNECTIONS	
Connector A	SC
Connector B	SC
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.