




### .079" [2.00 mm] Contact Centers, IDC Sockets, Insulation Displacement With or Without Strain Relief- SFH Series Mates with SBH21 series (See opposite page)

#### SPECIFICATIONS

- Centered Polarizing Key Optional
- Operating Temperature: -45°C to +105°C
- UL Flammability Rating: 94V-0
- Current Rating: 1 Amp
- Dielectric Withstanding: 500 VAC
- Insulation Resistance: 1000 Megohms



#### PART NUMBER OPTIONS

**SERIES** ——— **SFH21 - P P P N - D 10 - ID - BK - M181**

SFH21 = IDC Socket Without Strain Relief,  
.079" [2.00 mm] Contact Centers by  
.079" [2.00 mm] Row Spacing

SFH213 = IDC Socket With Strain Relief,  
.079" [2.00 mm] Contact Centers by  
.079" [2.00 mm] Row Spacing

**INSULATOR MATERIAL** ———

P = PBT

**CONTACT MATERIAL** ———

P = Phosphor Bronze

**CONTACT FINISH - RoHS Compliant** ———

P = Gold Flash Overall  
V = Gold Flash on Contact Surface, Nickel on Termination

**MODIFICATION (Omit for Standard)**  
M181 = Without Centered Polarizing Key

**COLOR**  
BK = Black

**TERMINATION TYPE**  
ID = Insulation Displacement

**NUMBER OF CONTACT POSITIONS**  
03 thru 13, 15, 17, 20, 22, 25, 30, 34 (SFH21)  
05 thru 13, 15, 17, 20, 22, 25 (SFH213)

**NUMBER OF ROWS**  
D = Dual Row

**CONTACT CENTERS**  
N = .079" [2.00 mm]

#### DIMENSIONS For complete drawings, go to [www.sullinscorp.com](http://www.sullinscorp.com) or e-mail [techsupport@sullinscorp.com](mailto:techsupport@sullinscorp.com) Dimensions in [ ] are in millimeters, all others are in inches.

