

1

2

3


4

5

6

7

A



B

C



D

E

F

G

H




## Material

- ① Terminal body (metal housing): Brass (CuZn), Tin plated
- ② Terminal screw: Steel Zinc plating "-" slot type
- ③ Wire guard: Stainless steel
- ④ Insulator (housing): Thermoplastic (UL94V-0), GREEN

## Electrical

Voltage rating: 125VAC  
 Current rating: 10A  
 Wire range:  
 Solid wire (AWG): 16-26  
 Stranded wire (AWG): 16-26  
 Torque (Lb-In): 1.7  
 Screw: M2  
 Wire strip length: 5-6mm  
 Withstanding Voltage: 1.25KV  
 Operating temperature: -40°C to +115°C  
 Soldering temperature: 250°C ± 10°C / 5 Sec  
 Safety Approval:



RECOMMENDER PCB LAYOUT

## DIMENSION

L	Nx3.5
P	(N-1)x3.5

N=Number of poles

Poles	Tolerance	
	DIM L	DIM P
2p	±0.05	±0.05
3p-6p	±0.15	±0.15
7p-12p	±0.20	±0.20
13p-18p	±0.30	±0.30
19p-24p	±0.40	±0.40

**RoHS compliant**  
 Unit: mm

Scale	Free				Date	Name	Customer-No.
TOLERANCE					Drawn	19.04.2010	Alex
X.	±0.50				Approved	08.10.2012	Amy
X.X	±0.30						
X.XX	±0.10						
DIM	TOL	①	Date	Name			
X.°	±1°	Update the WSW No.	08.10.2012	Amy			
		②	19.04.2010	Alex	Drawing-No. <b>ASS 4157 CO</b> rev01		
Angle	TOL	Id.	Modification	Date			

Customer-No.

ASSMANN WSW-No.

① A-TB350-T5xx

Drawing-No.

ASS 4157 CO rev01

Replace

Sheet

1

2

3

4

5

6

7

A

B

C

D

E

F

G

H