

G-Series





The G-Series toggle switches are single or double pole, AC rated up to 20 amps and contain a slow-make, slow-break contact mechanism. These switches are available in a wide range of ratings, terminations, circuits and bushing/toggle configurations.

Specifications

- Certifications*: UL, CSA, VDE
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate or Polycarbonate
- Bushing Material: Brass/Nickel Plate or Polycarbonate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



2G		A	5	1	-	73				
SERIES		RATING ²		TERMINATION/FUNCTION						
2G MAINTAINED		0	20A 250VAC			.250	.187			
6G MOMENTARY		5	10A 250VAC		SOLDER	TAB	TAB	SCREW	WIRE	PC
			15A 125VAC		LUG	(QC)	(QC)	TERM.	LEAD	TERM.
CIRCUIT ¹			3/4HP 125-250VAC	FUNCTION						
		6	3A 250VAC	ON-NONE-OFF	0	1	3	4	5	6
			6A 125VAC	(ON)-NONE-OFF	A	B	D	E	F	G
			1/4HP 125-250VAC	ON-NONE-(OFF)	L	M	R	S	T	U
SINGLE POLE IN			12A 250VAC	ON-NONE-ON	0	1	3	4	5	6
DOUBLE POLE BASE		7	17A 125VAC	ON-NONE-(ON)	A	B	D	E	F	G
A ON-NONE-OFF			1HP 250VAC	ON-OFF-ON	0	1	3	4	5	6
B ON-NONE-ON			10A 250VAC	ON-OFF-(ON)	A	B	D	E	F	G
C ON-OFF-ON		9	15A 125VAC	(ON)-OFF-(ON)	L	M	R	S	T	U
			12(6)A 250VAC T85							
DOUBLE POLE			3/4HP 125-250VAC							
K ON-NONE-OFF			20A 125-277VAC							
L ON-NONE-ON		72	1 1/2HP 125VAC							
M ON-OFF-ON			2HP 250VAC							

TOGGLE STYLE³

BAT	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
	.406	.343	52	57
	.562	.465	63	68
	.687	.465	73	78
	1.00	.465	A3	A8
	1.25	.465	B3	B8
	.687	.465	NBL3	NBL8
	.687	.465	NWH3	NWH8
	1.50	.465	C3	C8



NOTES:

Shading indicates standard configurations.

For bushing accessories, see pages 69 and 70.

1 Additional circuits are available on page 53.

2 Additional ratings available. Consult factory.

Rating Code 5 is applicable to certain circuits only. Consult factory for specifics.


Rating 9 is only available with nylon bushing and actuator. See page 53 for callout.

Rating 9 is only available with terminations 0 and 1, circuits A, B, K and L only.

Rating 72 is only available in maintained circuits and nylon construction. See page 53 for callout.


3 NBL toggle uses black oxide plated metal bushing for standard construction. NWH toggles use nickel plated metal bushing for standard construction.

Nylon Toggle



S.P. OR D.P. NYLON

FOR NYLON TOGGLES
AFTER TERMINATION SELECTION, ADD SUFFIXES:
(ex.) 2GK51-D-4B-B



D - **4** - **B** - **B**

NYLON TOGGLE **TOGGLE STYLE** **ACTUATOR COLOR** **BUSHING COLOR**

D **4** **B** **B**

1
2
3
4 (WITH NEOPRENE SEAL)

B BLACK
W WHITE

B BLACK
W WHITE

Additional Circuits¹

CIRCUIT	POSITION 1	POSITION 2	POSITION 3
PROGRESSIVE TWO CIRCUIT			
2GH	CIRCUIT 1 ON	2 CIRCUITS ON	CIRCUIT 2 ON
2GP	CIRCUIT 2 ON	CIRCUIT 1 ON	OFF
2GG	2 CIRCUITS ON	CIRCUIT 1 ON	OFF
6GG MOMENTARY	2 CIRCUITS (ON)	CIRCUIT 1 ON	OFF
SINGLE POLE TRIPLE THROW			
2GE	ON	ON	ON
REVERSING DOUBLE POLE DOUBLE THROW*			
2GX	ON	NONE	ON
2GO	ON	OFF	ON
6GO MOMENTARY	(ON)	OFF	(ON)

*WITH REVERSING DOUBLE POLE DOUBLE THROW CIRCUITS, USE TERMINATION/
FUNCTION FROM FOLLOWING OPTIONS:

SOLDER LUG	.250 TAB (Q.C)	SCREW TERM.	WIRE LEAD
3	3/TABS	4	1
3	3/TABS	4	1
3	3/TABS	4	1

NOTES:
Shading indicates standard configurations.
¹ Additional momentary circuits are available. Consult factory for details.