

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A" MAX	DIM "B"	PTH ϕ
76060-***0	10	50	26.60	17.10	0,46 $\pm 0,05$
76060-***2	12	60	30.40	20.90	
76060-***4	14	70	34.20	24.70	
76060-***6	16	80	38.00	28.50	0,39 $\pm 0,05$
76060-***0	10	50	26.60	17.10	
76060-***2	12	60	30.40	20.90	
76060-***4	14	70	34.20	24.70	
76060-***6	16	80	38.00	28.50	

76060-****

MODULE & TAIL PLATING TYPE
5 = RIGHT GUIDED LEAD-FREE

POLARIZATION KEY ORIENTATION
0 = NO KEY

- 1 = A
2 = B
3 = C
4 = D
- 5 = E
6 = F
7 = G
8 = H

- # OF COLUMNS
- 10 = 10 COL 0.46 PTH
12 = 12 COL 0.46 PTH
14 = 14 COL 0.46 PTH
16 = 16 COL 0.46 PTH
20 = 10 COL 0.39 PTH
22 = 12 COL 0.39 PTH
24 = 14 COL 0.39 PTH
26 = 16 COL 0.39 PTH

STANDARDIZATION EC NO: UCP2014-0108 DRWN: JCF-SKY 2013/06/18 CHKD: APPR: TELO 2013/07/15	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
					MM ONLY		3:1	METRIC				
				mm	INCH	DRAWN BY	DATE	TITLE IMPACT 100 OHM DC 5 PAIR SIGNAL MODULE GUIDE RIGHT SALES DWG				
			4 PLACES	± ---	± ---	JLAURX	2008/06/12					
			3 PLACES	± ---	± ---	CHECKED BY	DATE	molex				
			2 PLACES	± 0.13	± ---	TELO	2008/06/12					
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE	DOCUMENT NO. SD-76060-004				
0 PLACE	±	±	JLAURX	2010/11/04								
			ANGULAR ±1/2°		MATERIAL NO.		SHEET NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		2 OF 2					
					SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					