

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0717363001

Status:

Obsolete

Description:

1.27mm (.050") Pitch DIMM DRAM Socket, 8-Byte, Multiple Keys, Forklock, 200 Circuits, LVTTL 3.3V




image - Reference only

Series

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Memory Module Sockets
Series	71736
Comments	LVTTL 3.3V
Component Type	Memory Module
JEDEC Outline	MO-172
Product Name	DIMM

Physical

Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black, Natural
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Function Key	Center
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
PC Tail Length	3.23mm (.127")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm (.062")
Packaging Type	Tray
Pitch - Mating Interface	1.27mm (.050")
Pitch - Termination Interface	1.27mm (.050")
Plating min - Mating	0.051µm (2µ")
Plating min - Termination	3.810µm (150µ")
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	100V AC (RMS)/DC
Voltage Key	Center

Solder Process Data

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

Material Info

Reference - Drawing Numbers

Product Specification	PS-71243-9999
-----------------------	---------------

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

71736Series

This document was generated on 03/04/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION