




1



1. MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASFILLED, COLOUR BLUE. FLAME RETARDANT PER UL 94-V0.
2. MATERIAL BOX: BRASS ASTM B36 C26000-H02
3. MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C17200 - TF 00
4. PLATING: SEE SHEET 213-2 OF 2 

76325
SHEET 213 - 1 OF 2

© COPYRIGHT BY SENG ELECTRONICS INC.

[illegible]

PRODUCT	NO	NO OF POS	DIM. ('J')	DIM. ('K')
76325	- X02	2 x 02	2.54 100	5.08 200
	- X03	2 x 03	5.08 200	7.62 300
	- X04	2 x 04	7.62 300	10.16 400
	- X05	2 x 05	10.16 400	12.70 500
	- X06	2 x 06	12.70 500	15.24 600
	- X07	2 x 07	15.24 600	17.78 700
	- X08	2 x 08	17.78 700	20.32 800
	- X09	2 x 09	20.32 800	22.86 900
76325	- X10	2 x 10	22.86 900	25.40 1,000
	- X11	2 x 11	25.40 1,000	27.94 1,100
	- X12	2 x 12	27.94 1,100	30.48 1,200
	- X13	2 x 13	30.48 1,200	33.02 1,300
	- X14	2 x 14	33.02 1,300	35.56 1,400
	- X15	2 x 15	35.56 1,400	38.10 1,500
	- X16	2 x 16	38.10 1,500	40.64 1,600
	- X17	2 x 17	40.64 1,600	43.18 1,700
	- X18	2 x 18	43.18 1,700	45.72 1,800
	- X19	2 x 19	45.72 1,800	48.26 1,900
76325	- X20	2 x 20	48.26 1,900	50.80 2,000
	- X21	2 x 21	50.80 2,000	53.34 2,100
	- X22	2 x 22	53.34 2,100	55.88 2,200
	- X23	2 x 23	55.88 2,200	58.42 2,300
	- X24	2 x 24	58.42 2,300	60.96 2,400
	- X25	2 x 25	60.96 2,400	63.50 2,500
	- X26	2 x 26	63.50 2,500	66.04 2,600
	- X27	2 x 27	66.04 2,600	68.58 2,700
	- X28	2 x 28	68.58 2,700	71.12 2,800
	- X29	2 x 29	71.12 2,800	73.66 2,900
76325	- X30	2 x 30	73.66 2,900	76.20 3,000

PRODUCT NO	NO OF POS	DIM. ('J')	DIM. ('K')
76325 - X31	2 x 31	78.28 3.000	78.75 3.100
- X32	2 x 32	78.75 3.100	81.28 3.200
- X33	2 x 33	81.28 3.200	83.82 3.300
- X34	2 x 34	83.82 3.300	86.36 3.400
- X35	2 x 35	86.36 3.400	88.90 3.500
- X36	2 x 36	88.90 3.500	91.44 3.600
- X37	2 x 37	91.44 3.600	93.98 3.700
- X38	2 x 38	93.98 3.700	96.52 3.800
- X39	2 x 39	96.52 3.800	99.06 3.900
76325 - X40	2 x 40	99.06 3.900	101.60 4.000
- X41	2 x 41	101.60 4.000	104.14 4.100
- X42	2 x 42	104.14 4.100	106.68 4.200
- X43	2 x 43	106.68 4.200	109.22 4.300
- X44	2 x 44	109.22 4.300	111.76 4.400
- X45	2 x 45	111.76 4.400	114.30 4.500
- X46	2 x 46	114.30 4.500	116.84 4.600
- X47	2 x 47	116.84 4.600	119.38 4.700
- X48	2 x 48	119.38 4.700	121.92 4.800
- X49	2 x 49	121.92 4.800	124.46 4.900
76325 X50	2 x 50	124.46 4.900	127.00 5.000

4	$\frac{1.9}{75} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM
3	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM
2	$\frac{1.0}{40} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM
X	PLATING THICKNESS	THICKNESS

CUSTOMER COPY FOR REFERENCE ONLY			
✓			
CONFIDENTIAL			
MATERIAL	DR	DATE	APP. <i>[Signature]</i>
SEE TABLE	A. OOSTERVELD	830303	<i>[Signature]</i>
MEAT TREAT	CHK. <i>M. L...</i>	DATE <i>Nov-83</i>	REL. EASD
	 NIPRO ELECTRONICS DIVISION 5 HERTOGHBOSCH HOLLAND		
PHASE			
SEE TABLE			
LAYOUT	POSNO.	SITE	DWG NO. 76325
	C		SHEET 213-2 of 2

PDMD Rev: B STATUS: Not Released Printed: Sep 2003 2005

76325

5

4

3




2

1

PRODUCT N° 76325-XXX

THIRD ANGLE
PROJECTION

DU PONT

This print is the property of and embodies proprietary designs of the BERG ELECTRONICS DIVISION of
DU PONT DE NEMOURS (NEDERLAND) B.V. No part of the design shown on this print may be used in
any way without the written consent of BERG ELECTRONICS DIVISION, s-Hertogenbosch, Holland.DIMENSIONS $\frac{\text{mm}}{\text{INCHES}}$
DO NOT SCALERECOMMENDED
PIN PATTERNRECOMMENDED
HOLE PATTERN

NOTES :

1. THICKNESS P.C. BOARD INCLUDING METAL FOIL 1.60 ± 0.20 (.063 ± .008)
2. TERMINALS CAN ONLY BE USED FOR P.C. BOARD APPLICATION WITH NON-PLATED THROUGH HOLES.
3. PRODUCT TO MATE WITH 0.635 ± 0.025 (.025 ± .001) SQUARE PIN OR ROUND PIN.

CUSTOMER COPY FOR REFERENCE ONLY

BERG ELECTRONICS DIVISION
DU PONT DE NEMOURS (NEDERLAND) B.V.
s-hertogenbosch holland

PART NO. MATERIAL PLATING

DR R. SCHELLEKENS DATE OCT 30 APP 21 NOV 30

CHK M. 40 DATE NOV 80 REL DATE

RELEASED 0670

SCALE 10:1

TITLE VERTICAL CARD CONNECTOR
double row.100x.100LOC SIZE NO 76325 REV
H B SHEET 215 1. OF 1.