



## RECOMMENDED PANEL MOUNTING

| PANEL THICKNESS | X    |
|-----------------|------|
| 0.75-1.25       | 19.2 |
| 1.25-2.00       | 19.4 |
| 2.00-3.00       | 19.6 |



## NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE:  $X.X = \pm 0.4$   
 $X.XX = \pm 0.25$
- MECHANICAL LIFE: 30,000
- ELECTRICAL LIFE: 10,000
- CONTACT RESISTANCE: 20 mILLI OHMS
- INSULATION RESISTANCE: 1000 MEGA OHMS
- OPERATING TEMPERATURE: -10°C TO 55°C
- CONTACT RATING: 15A-250 VAC, 125VAC UL APPROVED  
10A 250VAC, VDE APPROVED
- DIELECTRIC STRENGTH: 1500V FOR 1 MIN
- ▲ DENOTES CRITICAL PARAMETER
- 2002/95/EC (RoHS) COMPLIANT.
- OPERATING FORCE: 750 ± 100grams



|     |        |                 |         |    |
|-----|--------|-----------------|---------|----|
| B   | 17722  | ADDED NOTE # 12 | 9/27/07 | BF |
| A   | 16230  | New Release     | 7/10/06 | RC |
| REV | PCR NO | DESCRIPTION     | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PB1973ABLKBLKEF0

SCALE 1.5

DATE 9/27/2007

DR BF

DWG M197300

REV B